

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563336

Luminaire Tested: **SQ4-PP3-050U-100D-930-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563336
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-050U-100D-930-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9247.6 lumens
Efficiency: N/A
Efficacy: 96.9 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 95.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563336

CATALOG NUMBER: SQ4-PP3-050U-100D-930-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P563336

CATALOG NUMBER: SQ4-PP3-050U-100D-930-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66
1	102	97	93	90	95	92	88	85	81	79	76	72	70	68	63	61	60	56
2	93	85	79	74	87	80	75	70	72	67	64	63	60	57	56	53	51	47
3	85	75	68	62	79	71	64	59	63	58	54	56	52	49	49	46	44	40
4	78	67	59	52	73	63	56	50	56	51	46	50	46	42	44	41	38	35
5	71	60	51	45	67	56	49	43	51	44	40	45	40	36	40	36	33	30
6	66	54	45	39	62	51	43	38	46	39	35	41	36	32	36	32	29	26
7	61	48	40	35	57	46	39	33	41	35	31	37	32	28	33	29	26	23
8	57	44	36	31	53	42	35	30	38	32	27	34	29	25	30	26	23	21
9	53	40	33	27	50	38	31	27	35	29	25	31	26	23	28	24	21	19
10	49	37	30	25	47	35	29	24	32	26	22	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10951	10951	10951
5°	11031	10963	10925
10°	11012	10934	10886
15°	10940	10880	10820
20°	10867	10806	10724
25°	10738	10664	10558
30°	10539	10484	10350
35°	10264	10193	10064
40°	9935	9872	9760
45°	9664	9596	9501
50°	9317	9257	9168
55°	8835	8717	8651
60°	8042	7812	7774
65°	7085	6791	6768
70°	6117	5864	5864
75°	5265	5192	5117
80°	4644	4697	4588
85°	3636	3964	3964



TEST NUMBER: P563336

CATALOG NUMBER: SQ4-PP3-050U-100D-930-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	224.5	2.4
10°-20°	640.9	6.9
20°-30°	960.0	10.4
30°-40°	1126.0	12.2
40°-50°	1129.6	12.2
50°-60°	963.6	10.4
60°-70°	628.4	6.8
70°-80°	315.3	3.4
80°-90°	89.1	1.0
90°-100°	233.1	2.5
100°-110°	633.2	6.8
110°-120°	651.0	7.0
120°-130°	520.5	5.6
130°-140°	409.0	4.4
140°-150°	313.6	3.4
150°-160°	225.5	2.4
160°-170°	137.9	1.5
170°-180°	46.5	0.5
0°-30°	1825.4	19.7
0°-40°	2951.4	31.9
0°-60°	5044.6	54.6
0°-90°	6077.5	65.7
90°-120°	1517.2	16.4
90°-150°	2760.3	29.8
90°-180°	3170.0	34.3
0°-180°	9247.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2374	2374	2374	2374	2374	
5°	2382	2360	2368	2359	2359	226
15°	2291	2268	2278	2270	2266	646
25°	2110	2085	2095	2076	2074	970
35°	1822	1804	1810	1789	1787	1138
45°	1481	1471	1471	1456	1456	1141
55°	1098	1094	1084	1078	1076	976
65°	649	637	622	618	620	648
75°	295	295	291	289	287	321
85°	69	75	75	75	75	81
90°	2	6	11	14	14	5
95°	34	128	406	177	119	36
105°	112	175	696	1060	998	119
115°	200	243	557	1109	1263	197
125°	275	313	504	850	1002	245
135°	331	368	490	692	781	256
145°	382	410	484	588	632	240
155°	432	448	481	528	543	199
165°	468	474	482	503	504	132
175°	486	487	484	490	489	46
180°	486	486	486	486	486	

TEST NUMBER: P563336

CATALOG NUMBER: SQ4-PP3-050U-100D-930-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2373.8	2373.8	2373.8	2373.8	2373.8
2.5°	2388.8	2369.2	2373.8	2370.2	2360.5
5°	2382.1	2359.7	2367.5	2359.2	2359.2
7.5°	2365.9	2341.5	2349.2	2340.9	2340.5
10°	2350.9	2326.5	2334.3	2325.9	2323.9
12.5°	2329.3	2304.9	2314.3	2304.3	2303.9
15°	2290.6	2268.2	2278.1	2269.7	2265.6
17.5°	2246.9	2222.5	2234.4	2222.7	2221.1
20°	2213.6	2189.2	2201.1	2184.5	2184.5
22.5°	2173.7	2149.2	2162.8	2141.2	2141.2
25°	2109.6	2085.2	2095.0	2076.2	2074.2
27.5°	2033.4	2009.4	2019.7	1998.5	1998.1
30°	1978.5	1956.1	1968.1	1945.2	1943.1
32.5°	1918.6	1897.8	1906.5	1883.6	1881.6
35°	1822.5	1804.2	1810.0	1789.1	1787.1
37.5°	1721.4	1702.6	1709.3	1691.4	1690.6
40°	1649.8	1637.6	1639.4	1624.7	1620.7
42.5°	1583.2	1569.4	1571.2	1556.6	1555.8
45°	1481.3	1471.1	1470.9	1456.3	1456.3
47.5°	1373.1	1365.4	1363.1	1351.0	1350.6
50°	1298.2	1292.1	1289.9	1279.4	1277.4
52.5°	1220.0	1217.1	1210.0	1201.2	1200.8
55°	1098.5	1094.4	1083.9	1077.6	1075.6
57.5°	966.6	958.4	946.6	937.5	939.1
60°	871.7	863.6	846.7	842.6	842.6
62.5°	780.2	770.4	753.5	747.8	751.0
65°	649.1	636.9	622.1	617.9	620.0
67.5°	530.1	519.1	503.1	503.0	501.4
70°	453.5	447.4	434.8	434.8	434.8
72.5°	385.3	382.5	373.2	373.2	371.6
75°	295.4	295.4	291.3	289.1	287.1
77.5°	221.4	222.2	220.1	217.9	214.3
80°	174.8	178.8	176.8	174.7	172.7
82.5°	131.5	135.6	135.2	131.5	131.1
85°	68.7	74.8	74.9	74.9	74.9
87.5°	18.6	26.0	28.8	29.5	31.1
90°	1.6	6.1	10.9	14.1	14.1
92.5°	14.1	63.8	110.8	47.6	40.3
95°	34.3	127.5	405.9	176.7	118.7
97.5°	56.8	140.8	622.3	484.1	340.0
100°	71.8	149.7	688.5	697.9	563.6
102.5°	86.8	158.5	706.0	863.1	744.7
105°	112.4	175.0	696.3	1060.2	997.6
107.5°	138.9	194.2	656.0	1161.9	1179.3
110°	157.7	208.1	626.0	1182.0	1256.8



TEST NUMBER: P563336

CATALOG NUMBER: SQ4-PP3-050U-100D-930-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	173.9	221.8	596.1	1165.3	1278.0
115°	199.8	242.6	557.3	1108.8	1263.0
117.5°	224.2	265.1	532.7	1028.7	1202.4
120°	240.4	280.1	521.4	975.0	1147.5
122.5°	254.2	293.8	513.9	921.1	1087.5
125°	274.8	312.9	504.3	849.6	1002.3
127.5°	293.2	331.0	499.0	795.4	926.4
130°	304.4	341.1	496.5	761.4	878.9
132.5°	315.7	352.3	494.0	732.4	836.5
135°	331.0	367.6	490.2	692.1	780.6
137.5°	347.5	380.8	488.3	656.5	730.9
140°	357.5	389.6	487.1	633.8	701.0
142.5°	367.5	397.1	485.8	616.1	672.2
145°	382.5	410.0	484.0	588.0	632.3
147.5°	399.4	422.9	482.4	565.9	600.7
150°	410.6	430.4	482.4	553.3	580.8
152.5°	419.3	436.7	481.2	541.9	564.5
155°	432.4	447.7	480.8	528.0	543.3
157.5°	445.3	457.2	480.8	518.6	530.2
160°	452.7	463.4	480.8	512.3	521.4
162.5°	460.2	468.5	482.1	507.2	513.9
165°	468.4	474.5	482.4	502.7	504.3
167.5°	476.8	479.8	484.0	497.4	498.6
170°	479.3	482.3	484.0	494.9	494.9
172.5°	481.8	483.6	484.0	492.4	492.4
175°	485.5	487.1	484.0	490.2	488.7
177.5°	486.8	486.8	483.0	488.0	485.5
180°	485.5	485.5	485.5	485.5	485.5

(END OF REPORT)