

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563672

Luminaire Tested: **SQ4-PP3-125U-050D-930-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563672
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-125U-050D-930-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11061.7 lumens
Efficiency: N/A
Efficacy: 114.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 96.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563672
CATALOG NUMBER: SQ4-PP3-125U-050D-930-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P563672

CATALOG NUMBER: SQ4-PP3-125U-050D-930-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	93	89	85	82	83	80	77	74	62	60	58	47	45	44	32	31	31	24
2	85	78	72	67	76	70	65	61	55	51	48	41	39	37	28	27	26	20
3	77	68	61	56	69	61	55	51	48	44	41	36	34	31	25	23	22	17
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	22	21	19	15
5	65	54	46	40	58	48	42	37	38	33	30	29	26	23	20	18	17	13
6	60	48	40	35	53	43	37	32	34	29	26	26	23	20	18	16	15	11
7	55	43	36	30	49	39	32	28	31	26	23	24	20	18	17	15	13	10
8	51	39	32	26	45	35	29	24	28	23	20	22	18	16	15	13	12	9
9	47	35	28	23	42	32	26	22	26	21	18	20	16	14	14	12	10	8
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5592	5592	5592
5°	5633	5598	5579
10°	5623	5584	5558
15°	5586	5556	5525
20°	5549	5518	5476
25°	5483	5445	5391
30°	5382	5353	5285
35°	5241	5205	5139
40°	5073	5041	4984
45°	4935	4900	4851
50°	4757	4727	4681
55°	4511	4452	4417
60°	4107	3989	3969
65°	3618	3467	3456
70°	3124	2994	2994
75°	2690	2650	2613
80°	2370	2399	2343
85°	1858	2022	2022



TEST NUMBER: P563672

CATALOG NUMBER: SQ4-PP3-125U-050D-930-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.6	1.0
10°-20°	327.3	3.0
20°-30°	490.2	4.4
30°-40°	575.0	5.2
40°-50°	576.8	5.2
50°-60°	492.1	4.4
60°-70°	320.9	2.9
70°-80°	161.0	1.5
80°-90°	47.4	0.4
90°-100°	576.6	5.2
100°-110°	1553.1	14.0
110°-120°	1629.9	14.7
120°-130°	1322.7	12.0
130°-140°	1037.3	9.4
140°-150°	796.4	7.2
150°-160°	572.6	5.2
160°-170°	349.8	3.2
170°-180°	118.0	1.1
0°-30°	932.1	8.4
0°-40°	1507.1	13.6
0°-60°	2576.0	23.3
0°-90°	3105.3	28.1
90°-120°	3759.6	34.0
90°-150°	6916.0	62.5
90°-180°	7956.0	71.9
0°-180°	11061.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1212	1212	1212	1212	1212	
5°	1216	1205	1209	1205	1205	116
15°	1170	1158	1163	1159	1157	330
25°	1077	1065	1070	1060	1059	495
35°	931	921	924	914	913	581
45°	756	751	751	744	744	582
55°	561	559	554	550	549	498
65°	332	325	318	316	317	331
75°	151	151	149	148	147	164
85°	35	38	38	38	38	41
90°	3	9	19	20	20	7
95°	88	314	945	483	334	92
105°	287	447	1718	2570	2412	302
115°	507	621	1430	2764	3126	499
125°	692	795	1284	2171	2554	618
135°	834	930	1248	1751	1983	643
145°	964	1039	1232	1497	1608	605
155°	1094	1134	1222	1343	1386	504
165°	1187	1201	1226	1275	1281	335
175°	1234	1232	1228	1245	1242	117
180°	1232	1232	1232	1232	1232	



TEST NUMBER: P563672

CATALOG NUMBER: SQ4-PP3-125U-050D-930-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1212.1	1212.1	1212.1	1212.1	1212.1
2.5°	1219.8	1209.8	1212.1	1210.3	1205.3
5°	1216.4	1205.0	1208.9	1204.7	1204.7
7.5°	1208.1	1195.6	1199.6	1195.3	1195.1
10°	1200.5	1188.0	1192.0	1187.7	1186.6
12.5°	1189.4	1176.9	1181.8	1176.6	1176.4
15°	1169.6	1158.2	1163.3	1159.0	1156.9
17.5°	1147.3	1134.9	1141.0	1135.0	1134.2
20°	1130.3	1117.9	1124.0	1115.5	1115.5
22.5°	1109.9	1097.5	1104.4	1093.4	1093.4
25°	1077.2	1064.8	1069.8	1060.2	1059.2
27.5°	1038.3	1026.1	1031.3	1020.5	1020.3
30°	1010.3	998.9	1005.0	993.3	992.2
32.5°	979.7	969.1	973.5	961.8	960.8
35°	930.6	921.3	924.2	913.6	912.6
37.5°	879.0	869.4	872.8	863.7	863.3
40°	842.4	836.2	837.1	829.6	827.6
42.5°	808.4	801.4	802.3	794.8	794.4
45°	756.4	751.2	751.1	743.6	743.6
47.5°	701.1	697.2	696.0	689.9	689.7
50°	662.9	659.8	658.7	653.3	652.3
52.5°	623.0	621.5	617.9	613.4	613.2
55°	560.9	558.8	553.5	550.3	549.2
57.5°	493.6	489.4	483.4	478.7	479.5
60°	445.1	441.0	432.4	430.2	430.2
62.5°	398.4	393.4	384.8	381.8	383.5
65°	331.5	325.2	317.6	315.5	316.6
67.5°	270.7	265.1	256.9	256.9	256.0
70°	231.6	228.5	222.0	222.0	222.0
72.5°	196.7	195.3	190.6	190.6	189.7
75°	150.9	150.9	148.7	147.6	146.6
77.5°	113.0	113.4	112.4	111.3	109.4
80°	89.2	91.3	90.3	89.2	88.2
82.5°	67.1	69.2	69.1	67.1	66.9
85°	35.1	38.2	38.2	38.2	38.2
87.5°	10.0	14.5	17.4	17.7	18.5
90°	3.1	9.3	18.8	20.4	20.4
92.5°	38.3	135.3	267.5	128.8	89.5
95°	87.9	313.6	945.2	483.3	334.4
97.5°	140.4	359.0	1482.4	1238.4	933.9
100°	180.6	377.1	1653.3	1729.8	1435.0
102.5°	219.5	402.5	1709.8	2097.7	1855.8
105°	287.3	447.0	1717.6	2569.7	2411.6
107.5°	351.4	493.8	1644.5	2812.3	2853.1
110°	394.1	529.2	1577.9	2887.6	3036.5

TEST NUMBER: P563672

CATALOG NUMBER: SQ4-PP3-125U-050D-930-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	439.3	564.6	1513.8	2870.9	<i>3115.6</i>
115°	<i>507.1</i>	<i>620.7</i>	<i>1430.3</i>	<i>2763.7</i>	<i>3126.0</i>
117.5°	569.0	675.5	1365.6	2592.5	<i>2996.0</i>
120°	609.2	712.0	1333.0	2469.7	<i>2884.2</i>
122.5°	644.4	746.0	1309.1	2344.1	<i>2757.3</i>
125°	692.4	795.3	1284.3	2170.7	<i>2554.5</i>
127.5°	738.6	839.9	1268.6	2017.8	<i>2360.4</i>
130°	766.2	867.5	1262.3	1930.2	<i>2231.1</i>
132.5°	793.8	893.9	1256.0	1853.0	<i>2129.3</i>
135°	833.7	930.4	1248.2	1751.2	<i>1983.0</i>
137.5°	871.7	964.4	1244.1	1664.8	<i>1855.2</i>
140°	898.1	987.1	1240.3	1611.6	<i>1783.6</i>
142.5°	925.7	1008.6	1237.8	1562.0	<i>1707.0</i>
145°	964.0	1039.2	1232.5	1497.2	<i>1607.7</i>
147.5°	1005.5	1070.9	1227.2	1442.7	<i>1529.5</i>
150°	1033.1	1089.9	1224.6	1408.4	<i>1480.6</i>
152.5°	1058.2	1107.7	1223.4	1380.5	<i>1439.1</i>
155°	1094.3	1134.2	1221.5	1343.4	<i>1386.4</i>
157.5°	1126.0	1157.1	1221.8	1317.3	<i>1346.2</i>
160°	1146.1	1172.2	1223.1	1302.1	<i>1323.6</i>
162.5°	1163.7	1184.9	1224.3	1289.4	<i>1304.7</i>
165°	1187.0	1200.8	1226.2	1275.0	<i>1281.2</i>
167.5°	1205.8	1213.8	1227.8	1264.0	<i>1266.4</i>
170°	1218.4	1221.4	1227.8	1257.6	<i>1257.6</i>
172.5°	1225.9	1226.5	1229.0	1251.3	<i>1251.3</i>
175°	1234.1	1232.5	1227.8	1245.0	<i>1241.9</i>
177.5°	1237.5	1235.1	1228.7	1238.7	<i>1236.3</i>
180°	1232.5	1232.5	1232.5	1232.5	<i>1232.5</i>

(END OF REPORT)