

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563047

Luminaire Tested: **SQ4-PC3-125U-100D-930-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563047
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-125U-100D-930-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10569.7 lumens
Efficiency: N/A
Efficacy: 102.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 102.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563047
CATALOG NUMBER: SQ4-PC3-125U-100D-930-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563047

CATALOG NUMBER: SQ4-PC3-125U-100D-930-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44
1	96	92	88	85	88	84	81	78	70	68	66	57	55	54	44	43	42	37
2	88	80	74	69	80	74	69	64	61	58	54	50	47	45	39	37	36	31
3	80	71	63	58	73	65	59	54	54	49	46	44	41	38	35	32	30	26
4	73	62	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26	22
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	28	25	23	19
6	62	50	42	36	56	46	39	34	39	33	29	32	28	24	25	22	20	17
7	57	45	37	31	52	41	34	29	35	29	25	29	25	22	23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10368	10368	10368
5°	10446	10378	10339
10°	10420	10372	10342
15°	10365	10365	10356
20°	10297	10328	10328
25°	10200	10274	10242
30°	10076	10198	10153
35°	9926	10078	10008
40°	9762	9900	9800
45°	9585	9653	9503
50°	9334	9334	9184
55°	9038	8921	8787
60°	8601	8428	8294
65°	7949	7791	7722
70°	6962	7017	6988
75°	5601	6193	6231
80°	3981	5253	5306
85°	2421	4404	4404



TEST NUMBER: P563047

CATALOG NUMBER: SQ4-PC3-125U-100D-930-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.5	1.5
10°-20°	457.8	4.3
20°-30°	693.2	6.6
30°-40°	831.1	7.9
40°-50°	847.4	8.0
50°-60°	739.8	7.0
60°-70°	529.6	5.0
70°-80°	272.8	2.6
80°-90°	71.1	0.7
90°-100°	432.4	4.1
100°-110°	1164.8	11.0
110°-120°	1222.5	11.6
120°-130°	992.0	9.4
130°-140°	778.0	7.4
140°-150°	597.3	5.7
150°-160°	429.5	4.1
160°-170°	262.4	2.5
170°-180°	88.5	0.8
0°-30°	1310.5	12.4
0°-40°	2141.7	20.3
0°-60°	3728.9	35.3
0°-90°	4602.4	43.5
90°-120°	2819.7	26.7
90°-150°	5187.0	49.1
90°-180°	5967.0	56.5
0°-180°	10569.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1686	1686	1686	1686	1686	
5°	1692	1675	1681	1676	1675	161
15°	1628	1614	1628	1628	1626	459
25°	1503	1492	1514	1509	1509	692
35°	1322	1319	1342	1333	1333	827
45°	1102	1099	1110	1096	1092	848
55°	843	832	832	819	819	751
65°	546	534	535	531	531	540
75°	236	246	261	262	262	255
85°	34	53	62	64	62	47
90°	2	7	14	15	15	6
95°	66	235	709	362	251	69
105°	216	335	1288	1927	1809	227
115°	380	466	1073	2073	2344	374
125°	519	596	963	1628	1916	464
135°	625	698	936	1313	1487	483
145°	723	779	924	1123	1206	453
155°	821	851	916	1008	1040	378
165°	890	901	920	956	961	251
175°	926	924	921	934	931	88
180°	924	924	924	924	924	



TEST NUMBER: P563047

CATALOG NUMBER: SQ4-PC3-125U-100D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1685.6	1685.6	1685.6	1685.6	1685.6
2.5°	1695.6	1680.9	1685.6	1681.7	1675.6
5°	1691.8	1675.0	1680.9	1676.2	1674.6
7.5°	1679.6	1662.8	1670.6	1667.4	1665.9
10°	1668.4	1651.6	1660.6	1657.4	1655.9
12.5°	1653.4	1637.8	1648.1	1645.0	1644.7
15°	1627.8	1614.1	1627.8	1627.8	1626.3
17.5°	1595.7	1583.2	1597.9	1598.8	1597.9
20°	1573.2	1559.5	1577.9	1576.3	1577.9
22.5°	1545.7	1534.4	1554.2	1550.1	1551.7
25°	1503.0	1492.3	1513.9	1509.2	1509.2
27.5°	1452.4	1444.8	1468.3	1463.3	1463.3
30°	1418.7	1411.1	1435.8	1429.6	1429.6
32.5°	1381.2	1376.0	1399.6	1392.1	1392.1
35°	1321.9	1318.9	1342.2	1332.8	1332.8
37.5°	1260.7	1258.0	1279.2	1267.8	1264.2
40°	1215.8	1214.3	1233.0	1220.5	1220.5
42.5°	1170.8	1169.3	1185.5	1170.5	1170.5
45°	1101.9	1098.8	1109.7	1095.5	1092.5
47.5°	1026.6	1023.6	1030.4	1015.0	1013.5
50°	975.4	972.4	975.4	961.4	959.8
52.5°	923.0	917.5	918.0	904.0	903.6
55°	842.8	832.1	831.9	819.4	819.4
57.5°	757.9	743.8	745.1	734.4	732.9
60°	699.2	683.9	685.1	675.8	674.2
62.5°	641.8	624.1	627.7	617.1	616.8
65°	546.2	534.0	535.3	530.6	530.6
67.5°	454.5	443.2	451.4	447.6	447.3
70°	387.1	379.4	390.2	390.1	388.6
72.5°	324.6	324.3	337.7	337.8	338.7
75°	235.7	246.3	260.6	262.2	262.2
77.5°	157.3	176.2	192.0	192.6	192.3
80°	112.4	133.7	148.3	151.4	149.8
82.5°	76.2	98.7	110.8	113.9	112.4
85°	34.3	52.6	62.4	64.0	62.4
87.5°	10.5	22.4	27.8	28.0	25.5
90°	2.4	7.0	14.1	15.3	15.3
92.5°	28.7	101.5	200.7	96.6	67.1
95°	65.9	235.2	708.9	362.5	250.8
97.5°	105.3	269.2	1111.8	928.8	700.4
100°	135.4	282.8	1240.0	1297.3	1076.3
102.5°	164.6	301.9	1282.3	1573.3	1391.9
105°	215.5	335.2	1288.2	1927.3	1808.7
107.5°	263.5	370.4	1233.4	2109.2	2139.8
110°	295.6	396.9	1183.4	2165.7	2277.4



TEST NUMBER: P563047

CATALOG NUMBER: SQ4-PC3-125U-100D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	329.5	423.4	1135.4	2153.2	2336.7
115°	380.3	465.5	1072.7	2072.8	2344.5
117.5°	426.7	506.6	1024.2	1944.4	2247.0
120°	456.9	534.0	999.7	1852.3	2163.1
122.5°	483.3	559.5	981.8	1758.0	2068.0
125°	519.3	596.4	963.2	1628.0	1915.9
127.5°	553.9	629.9	951.5	1513.3	1770.3
130°	574.6	650.6	946.7	1447.6	1673.3
132.5°	595.4	670.4	942.0	1389.7	1597.0
135°	625.3	697.8	936.1	1313.4	1487.2
137.5°	653.8	723.3	933.1	1248.6	1391.4
140°	673.6	740.3	930.3	1208.7	1337.7
142.5°	694.3	756.5	928.4	1171.5	1280.2
145°	723.0	779.4	924.4	1122.9	1205.8
147.5°	754.1	803.1	920.4	1082.0	1147.2
150°	774.8	817.4	918.5	1056.3	1110.4
152.5°	793.7	830.7	917.5	1035.4	1079.3
155°	820.7	850.7	916.1	1007.5	1039.8
157.5°	844.5	867.8	916.4	988.0	1009.6
160°	859.6	879.2	917.3	976.5	992.7
162.5°	872.8	888.7	918.2	967.0	978.5
165°	890.2	900.6	919.7	956.3	960.9
167.5°	904.4	910.3	920.8	948.0	949.8
170°	913.8	916.1	920.8	943.2	943.2
172.5°	919.4	919.9	921.8	938.5	938.5
175°	925.5	924.4	920.8	933.7	931.4
177.5°	928.1	926.3	921.5	929.0	927.2
180°	924.4	924.4	924.4	924.4	924.4

(END OF REPORT)