

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563215

Luminaire Tested: **SQ4-PP3-025U-075D-930-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563215  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-025U-075D-930-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4583.4 lumens  
Efficiency: N/A  
Efficacy: 94.3 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 48.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563215  
CATALOG NUMBER: SQ4-PP3-025U-075D-930-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P563215

CATALOG NUMBER: SQ4-PP3-025U-075D-930-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79	75				
1	104	99	95	92	98	95	91	88	86	83	81	78	76	74	70	69	67	64				
2	95	87	81	76	90	83	77	73	76	71	67	69	65	62	62	60	57	54				
3	87	77	69	63	82	73	67	61	67	61	57	61	57	53	55	52	49	46				
4	79	68	60	54	75	65	58	52	60	54	49	54	49	45	50	46	42	39				
5	73	61	53	46	69	58	51	45	54	47	42	49	44	40	45	40	37	34				
6	67	55	46	40	64	53	45	39	48	42	37	44	39	35	41	36	33	30				
7	62	50	41	36	59	48	40	35	44	37	33	40	35	31	37	33	29	27				
8	58	45	37	32	55	44	36	31	40	34	29	37	32	28	34	29	26	24				
9	54	41	34	28	51	40	33	28	37	31	26	34	29	25	32	27	24	22				
10	51	38	31	26	48	37	30	25	34	28	24	32	26	23	29	25	21	20				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8241	8241	8241
5°	8302	8251	8222
10°	8288	8229	8192
15°	8233	8188	8143
20°	8179	8132	8071
25°	8082	8026	7946
30°	7932	7890	7790
35°	7724	7672	7574
40°	7477	7430	7345
45°	7273	7222	7150
50°	7012	6967	6899
55°	6649	6561	6510
60°	6052	5880	5851
65°	5333	5110	5094
70°	4604	4413	4413
75°	3964	3907	3852
80°	3493	3535	3454
85°	2738	2985	2985



TEST NUMBER: P563215

CATALOG NUMBER: SQ4-PP3-025U-075D-930-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	126.7	2.8
10°-20°	361.8	7.9
20°-30°	541.9	11.8
30°-40°	635.6	13.9
40°-50°	637.6	13.9
50°-60°	543.9	11.9
60°-70°	354.7	7.7
70°-80°	178.0	3.9
80°-90°	50.2	1.1
90°-100°	86.7	1.9
100°-110°	227.9	5.0
110°-120°	236.3	5.2
120°-130°	189.6	4.1
130°-140°	148.7	3.2
140°-150°	114.2	2.5
150°-160°	82.2	1.8
160°-170°	50.3	1.1
170°-180°	17.0	0.4
0°-30°	1030.4	22.5
0°-40°	1666.0	36.3
0°-60°	2847.5	62.1
0°-90°	3430.4	74.8
90°-120°	551.0	12.0
90°-150°	1003.4	21.9
90°-180°	1153.0	25.2
0°-180°	4583.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1340	1340	1340	1340	1340	
5°	1345	1332	1336	1332	1332	128
15°	1293	1280	1286	1281	1279	365
25°	1191	1177	1183	1172	1171	548
35°	1029	1018	1022	1010	1009	643
45°	836	830	830	822	822	644
55°	620	618	612	608	607	551
65°	366	360	351	349	350	366
75°	167	167	164	163	162	181
85°	39	42	42	42	42	46
90°	1	3	9	5	5	2
95°	11	45	149	77	52	13
105°	41	62	252	382	357	43
115°	73	89	202	403	460	72
125°	102	114	184	310	366	90
135°	121	133	178	250	284	94
145°	140	149	176	214	230	88
155°	158	163	176	193	198	73
165°	171	173	176	182	185	48
175°	178	178	177	179	179	17
180°	178	178	178	178	178	



TEST NUMBER: P563215

CATALOG NUMBER: SQ4-PP3-025U-075D-930-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1339.9	1339.9	1339.9	1339.9	1339.9
2.5°	1348.4	1337.3	1339.9	1337.9	1332.4
5°	1344.6	1332.0	1336.4	1331.7	1331.7
7.5°	1335.4	1321.7	1326.1	1321.4	1321.1
10°	1327.0	1313.2	1317.6	1312.9	1311.7
12.5°	1314.8	1301.0	1306.3	1300.7	1300.5
15°	1292.9	1280.3	1285.9	1281.1	1278.8
17.5°	1268.3	1254.5	1261.2	1254.6	1253.7
20°	1249.5	1235.7	1242.4	1233.0	1233.0
22.5°	1226.9	1213.2	1220.8	1208.6	1208.6
25°	1190.8	1177.0	1182.6	1172.0	1170.8
27.5°	1147.8	1134.2	1140.0	1128.1	1127.8
30°	1116.8	1104.2	1110.9	1098.0	1096.8
32.5°	1083.0	1071.3	1076.2	1063.2	1062.1
35°	1028.7	1018.4	1021.7	1009.9	1008.7
37.5°	971.6	961.1	964.8	954.7	954.3
40°	931.2	924.4	925.4	917.1	914.8
42.5°	893.7	885.9	886.9	878.6	878.2
45°	836.1	830.4	830.3	822.0	822.0
47.5°	775.1	770.7	769.4	762.6	762.4
50°	732.8	729.3	728.1	722.2	721.0
52.5°	688.6	687.0	683.0	678.1	677.8
55°	620.0	617.7	611.8	608.3	607.1
57.5°	545.6	541.0	534.3	529.2	530.1
60°	492.0	487.5	478.0	475.6	475.6
62.5°	440.4	434.9	425.3	422.1	423.9
65°	366.4	359.5	351.1	348.8	350.0
67.5°	299.2	293.0	284.0	283.9	283.0
70°	256.0	252.6	245.4	245.4	245.4
72.5°	217.5	215.9	210.7	210.7	209.7
75°	166.8	166.8	164.4	163.2	162.1
77.5°	124.9	125.4	124.2	123.0	121.0
80°	98.6	100.9	99.8	98.6	97.5
82.5°	74.2	76.5	76.3	74.2	74.0
85°	38.8	42.2	42.3	42.3	42.3
87.5°	10.6	14.7	16.9	16.0	16.9
90°	1.1	3.4	9.1	4.6	4.6
92.5°	4.8	23.1	51.1	22.6	14.6
95°	11.4	44.9	149.4	77.0	52.5
97.5°	19.8	49.3	223.5	177.7	130.9
100°	26.2	53.0	246.3	249.6	193.8
102.5°	31.7	56.7	252.7	310.9	263.2
105°	41.0	62.2	252.0	382.5	356.9
107.5°	50.6	70.3	237.6	419.8	426.0
110°	57.0	74.9	225.8	429.3	456.1



TEST NUMBER: P563215

CATALOG NUMBER: SQ4-PP3-025U-075D-930-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	63.4	80.3	214.8	423.3	464.3
115°	73.0	88.6	201.8	402.7	459.5
117.5°	82.3	96.6	192.9	374.1	437.2
120°	87.8	101.2	189.3	354.9	416.2
122.5°	93.3	106.7	186.5	335.7	396.1
125°	101.5	113.7	183.6	310.3	366.0
127.5°	108.1	120.6	181.1	289.8	336.8
130°	111.7	125.1	180.2	276.9	320.4
132.5°	115.4	128.8	179.2	265.9	304.9
135°	120.9	133.1	177.9	250.5	283.9
137.5°	126.6	138.6	177.7	238.9	266.4
140°	131.1	142.3	176.7	229.8	255.4
142.5°	134.8	145.0	176.7	223.3	245.4
145°	140.3	149.2	175.6	213.6	230.3
147.5°	145.7	154.4	175.6	205.6	219.4
150°	149.4	157.2	175.6	200.9	212.1
152.5°	153.0	159.0	175.6	197.2	205.7
155°	158.5	163.0	175.6	192.8	198.4
157.5°	162.6	166.8	175.6	188.9	192.9
160°	165.3	168.7	175.6	187.1	189.3
162.5°	168.1	170.5	175.6	185.2	187.5
165°	171.0	173.3	175.6	182.5	184.7
167.5°	173.8	174.9	176.7	181.3	182.2
170°	175.6	176.7	176.7	181.3	181.3
172.5°	176.5	176.7	176.7	180.4	179.5
175°	177.9	177.9	176.7	179.0	179.0
177.5°	177.9	177.9	177.0	178.8	177.9
180°	177.9	177.9	177.9	177.9	177.9

(END OF REPORT)