

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563287

Luminaire Tested: **SQ4-PP3-050U-050D-930-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563287  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-050U-050D-930-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4705.8 lumens  
Efficiency: N/A  
Efficacy: 105.0 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 44.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563287  
CATALOG NUMBER: SQ4-PP3-050U-050D-930-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P563287

CATALOG NUMBER: SQ4-PP3-050U-050D-930-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	49				
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	49	48	47	42				
2	89	82	76	71	82	76	71	66	64	60	57	54	51	48	44	42	40	36				
3	82	72	65	59	75	67	61	55	57	52	48	48	44	41	39	36	34	30				
4	75	64	56	50	69	59	52	47	51	45	41	42	38	35	35	32	30	26				
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	31	28	26	23				
6	63	51	43	37	58	48	40	35	41	35	31	34	30	27	28	25	23	20				
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18				
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16				
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14				
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5592	5592	5592
5°	5633	5598	5578
10°	5623	5584	5559
15°	5586	5556	5525
20°	5549	5518	5476
25°	5483	5445	5391
30°	5381	5353	5286
35°	5241	5205	5139
40°	5073	5041	4984
45°	4935	4900	4851
50°	4758	4727	4681
55°	4511	4451	4417
60°	4106	3989	3970
65°	3618	3467	3455
70°	3124	2994	2994
75°	2688	2650	2614
80°	2370	2398	2341
85°	1856	2025	2025



TEST NUMBER: P563287

CATALOG NUMBER: SQ4-PP3-050U-050D-930-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	86.0	1.8
10°-20°	245.5	5.2
20°-30°	367.7	7.8
30°-40°	431.2	9.2
40°-50°	432.6	9.2
50°-60°	369.0	7.8
60°-70°	240.7	5.1
70°-80°	120.7	2.6
80°-90°	34.8	0.7
90°-100°	174.8	3.7
100°-110°	474.9	10.1
110°-120°	488.2	10.4
120°-130°	390.4	8.3
130°-140°	306.7	6.5
140°-150°	235.2	5.0
150°-160°	169.1	3.6
160°-170°	103.4	2.2
170°-180°	34.8	0.7
0°-30°	699.1	14.9
0°-40°	1130.3	24.0
0°-60°	1931.9	41.1
0°-90°	2328.2	49.5
90°-120°	1137.9	24.2
90°-150°	2070.2	44.0
90°-180°	2378.0	50.5
0°-180°	4705.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	909	909	909	909	909	
5°	912	904	907	904	904	87
15°	877	869	872	869	868	247
25°	808	799	802	795	794	372
35°	698	691	693	685	684	436
45°	567	563	563	558	558	437
55°	421	419	415	413	412	374
65°	249	244	238	237	237	248
75°	113	113	112	111	110	123
85°	26	29	29	29	29	31
90°	1	5	8	10	10	3
95°	26	96	304	132	89	27
105°	84	131	522	795	748	90
115°	150	182	418	832	947	148
125°	206	235	378	637	752	184
135°	248	276	368	519	585	192
145°	287	308	363	441	474	180
155°	324	336	361	396	408	150
165°	351	356	362	377	378	99
175°	364	365	363	368	366	35
180°	364	364	364	364	364	

TEST NUMBER: P563287

CATALOG NUMBER: SQ4-PP3-050U-050D-930-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	909.1	909.1	909.1	909.1	909.1
2.5°	914.8	907.4	909.1	907.7	904.0
5°	912.3	903.7	906.7	903.5	903.5
7.5°	906.1	896.7	899.7	896.5	896.4
10°	900.3	891.0	894.0	890.8	890.0
12.5°	892.1	882.7	886.3	882.5	882.3
15°	877.2	868.7	872.5	869.2	867.7
17.5°	860.5	851.2	855.7	851.2	850.6
20°	847.8	838.4	843.0	836.6	836.6
22.5°	832.5	823.1	828.3	820.0	820.0
25°	807.9	798.6	802.3	795.1	794.4
27.5°	778.8	769.6	773.5	765.4	765.2
30°	757.7	749.1	753.7	745.0	744.2
32.5°	734.8	726.8	730.1	721.4	720.6
35°	698.0	690.9	693.2	685.2	684.4
37.5°	659.2	652.1	654.6	647.8	647.4
40°	631.8	627.2	627.8	622.2	620.7
42.5°	606.3	601.0	601.7	596.1	595.8
45°	567.3	563.4	563.3	557.7	557.7
47.5°	525.9	522.9	522.0	517.4	517.3
50°	497.2	494.8	494.0	490.0	489.2
52.5°	467.2	466.1	463.4	460.0	459.9
55°	420.7	419.1	415.1	412.7	411.9
57.5°	370.2	367.1	362.5	359.0	359.7
60°	333.8	330.7	324.3	322.7	322.7
62.5°	298.8	295.0	288.6	286.4	287.6
65°	248.6	243.9	238.2	236.7	237.4
67.5°	203.0	198.8	192.7	192.6	192.0
70°	173.7	171.4	166.5	166.5	166.5
72.5°	147.6	146.5	142.9	142.9	142.3
75°	113.1	113.1	111.5	110.7	110.0
77.5°	84.8	85.1	84.3	83.5	82.1
80°	66.9	68.5	67.7	66.9	66.1
82.5°	50.4	51.9	51.8	50.4	50.2
85°	26.3	28.6	28.7	28.7	28.7
87.5°	7.2	10.4	11.8	12.3	12.9
90°	1.2	4.6	8.2	10.5	10.5
92.5°	10.5	47.9	83.1	35.7	30.2
95°	25.8	95.6	304.4	132.5	89.0
97.5°	42.6	105.6	466.7	363.1	255.0
100°	53.9	112.2	516.4	523.4	422.7
102.5°	65.1	118.9	529.5	647.4	558.5
105°	84.3	131.2	522.2	795.1	748.2
107.5°	104.2	145.7	492.0	871.4	884.5
110°	118.3	156.0	469.5	886.5	942.6



TEST NUMBER: P563287

CATALOG NUMBER: SQ4-PP3-050U-050D-930-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	130.4	166.4	447.0	874.0	958.5
115°	149.9	181.9	418.0	831.6	947.2
117.5°	168.1	198.8	399.5	771.5	901.8
120°	180.3	210.1	391.1	731.2	860.6
122.5°	190.6	220.4	385.5	690.9	815.6
125°	206.1	234.7	378.2	637.2	751.7
127.5°	219.9	248.3	374.2	596.6	694.8
130°	228.3	255.8	372.3	571.1	659.2
132.5°	236.8	264.2	370.5	549.3	627.4
135°	248.2	275.7	367.7	519.0	585.4
137.5°	260.6	285.6	366.3	492.3	548.2
140°	268.1	292.2	365.3	475.4	525.7
142.5°	275.6	297.8	364.4	462.1	504.2
145°	286.9	307.5	363.0	441.0	474.2
147.5°	299.5	317.1	361.8	424.5	450.6
150°	307.9	322.8	361.8	415.0	435.6
152.5°	314.5	327.6	360.9	406.4	423.4
155°	324.3	335.8	360.6	396.0	407.5
157.5°	333.9	342.9	360.6	388.9	397.6
160°	339.6	347.6	360.6	384.2	391.1
162.5°	345.2	351.4	361.6	380.4	385.5
165°	351.3	355.8	361.8	377.1	378.2
167.5°	357.6	359.9	363.0	373.1	374.0
170°	359.5	361.8	363.0	371.2	371.2
172.5°	361.3	362.7	363.0	369.3	369.3
175°	364.1	365.3	363.0	367.6	366.5
177.5°	365.1	365.1	362.3	366.0	364.1
180°	364.1	364.1	364.1	364.1	364.1

(END OF REPORT)