

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P564008

Luminaire Tested: **SQ4-PR1-050U-100D-930-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564008
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-050U-100D-930-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9211.7 lumens
Efficiency: N/A
Efficacy: 96.6 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 95.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564008
CATALOG NUMBER: SQ4-PR1-050U-100D-930-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P564008

CATALOG NUMBER: SQ4-PR1-050U-100D-930-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70	66
1	102	97	94	90	95	92	88	85	81	79	76	72	70	68	63	62	60	56
2	93	85	79	74	87	81	75	71	72	68	64	63	60	57	56	53	51	48
3	85	76	68	62	80	71	65	60	64	58	54	56	52	49	50	47	44	41
4	78	67	59	53	73	64	56	51	57	51	47	51	46	42	45	41	38	35
5	72	60	52	46	67	57	50	44	51	45	40	46	41	37	40	37	34	31
6	66	54	46	40	62	51	44	38	46	40	35	41	36	33	37	33	30	27
7	61	49	41	35	58	47	39	34	42	36	31	38	33	29	34	30	26	24
8	57	45	37	31	54	42	35	30	38	32	28	34	30	26	31	27	24	22
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	29	24	21	19
10	50	37	30	25	47	36	29	24	33	27	23	29	25	21	26	22	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11145	11145	11145
5°	11246	11159	11101
10°	11210	11132	11073
15°	11161	11091	11031
20°	11105	11033	10951
25°	11026	10952	10825
30°	10907	10830	10674
35°	10746	10653	10500
40°	10501	10389	10201
45°	10074	9897	9693
50°	9319	9095	8916
55°	8134	7949	7782
60°	6854	6797	6662
65°	5928	5951	5905
70°	5445	5473	5473
75°	5229	5229	5267
80°	4920	4976	4920
85°	3964	4404	4404



TEST NUMBER: P564008

CATALOG NUMBER: SQ4-PR1-050U-100D-930-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	228.5	2.5
10°-20°	653.7	7.1
20°-30°	985.9	10.7
30°-40°	1174.7	12.8
40°-50°	1158.2	12.6
50°-60°	885.1	9.6
60°-70°	547.8	5.9
70°-80°	311.1	3.4
80°-90°	96.5	1.0
90°-100°	233.1	2.5
100°-110°	633.2	6.9
110°-120°	651.0	7.1
120°-130°	520.5	5.7
130°-140°	409.0	4.4
140°-150°	313.6	3.4
150°-160°	225.5	2.4
160°-170°	137.9	1.5
170°-180°	46.5	0.5
0°-30°	1868.1	20.3
0°-40°	3042.8	33.0
0°-60°	5086.1	55.2
0°-90°	6041.5	65.6
90°-120°	1517.2	16.5
90°-150°	2760.3	30.0
90°-180°	3170.0	34.4
0°-180°	9211.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2416	2416	2416	2416	2416	
5°	2428	2402	2410	2401	2397	230
15°	2337	2312	2322	2314	2310	659
25°	2166	2140	2152	2129	2127	997
35°	1908	1886	1892	1867	1864	1191
45°	1544	1524	1517	1490	1486	1183
55°	1011	995	988	972	968	906
65°	543	539	545	541	541	550
75°	293	293	293	296	296	310
85°	75	79	83	83	83	87
90°	2	6	11	14	14	5
95°	34	128	406	177	119	36
105°	112	175	696	1060	998	119
115°	200	243	557	1109	1263	197
125°	275	313	504	850	1002	245
135°	331	368	490	692	781	256
145°	382	410	484	588	632	240
155°	432	448	481	528	543	199
165°	468	474	482	503	504	132
175°	486	487	484	490	489	46
180°	486	486	486	486	486	



TEST NUMBER: P564008

CATALOG NUMBER: SQ4-PR1-050U-100D-930-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2416.0	2416.0	2416.0	2416.0	2416.0
2.5°	2430.9	2409.8	2416.0	2410.7	2399.3
5°	2428.5	2402.0	2409.7	2401.3	2397.2
7.5°	2409.7	2383.7	2391.4	2383.0	2380.6
10°	2393.1	2368.7	2376.4	2368.0	2363.9
12.5°	2374.8	2348.7	2358.1	2348.0	2344.0
15°	2336.9	2312.5	2322.3	2313.9	2309.8
17.5°	2295.3	2269.2	2279.0	2269.3	2264.1
20°	2262.0	2237.6	2247.4	2232.8	2230.8
22.5°	2225.4	2200.9	2210.8	2191.2	2190.8
25°	2166.3	2139.8	2151.7	2128.8	2126.7
27.5°	2095.9	2071.5	2081.4	2058.0	2055.5
30°	2047.6	2023.2	2033.1	2008.0	2003.9
32.5°	1992.7	1969.9	1978.1	1953.1	1950.7
35°	1908.2	1885.8	1891.6	1866.6	1864.5
37.5°	1812.1	1791.7	1795.0	1767.5	1765.5
40°	1743.8	1723.5	1725.1	1695.9	1693.9
42.5°	1668.9	1648.6	1646.9	1617.7	1615.6
45°	1544.1	1523.7	1517.0	1489.9	1485.8
47.5°	1401.7	1381.4	1368.8	1346.7	1343.9
50°	1298.5	1278.2	1267.3	1248.4	1242.3
52.5°	1187.0	1166.6	1157.4	1140.2	1134.1
55°	1011.3	995.1	988.4	971.7	967.6
57.5°	844.4	833.5	831.5	815.3	813.6
60°	742.9	736.8	736.7	722.1	722.1
62.5°	656.3	651.9	655.1	645.5	643.8
65°	543.1	539.1	545.2	541.0	541.0
67.5°	453.6	453.6	457.4	455.7	455.7
70°	403.7	403.7	405.8	405.8	405.8
72.5°	358.8	357.1	362.5	362.5	360.8
75°	293.4	293.4	293.4	295.5	295.5
77.5°	228.5	228.9	230.6	230.1	228.5
80°	185.2	187.2	187.3	185.2	185.2
82.5°	141.9	144.0	144.0	143.5	141.9
85°	74.9	79.0	83.2	83.2	83.2
87.5°	22.0	29.4	35.5	36.1	34.4
90°	1.6	6.1	10.9	14.1	14.1
92.5°	14.1	63.8	110.8	47.6	40.3
95°	34.3	127.5	405.9	176.7	118.7
97.5°	56.8	140.8	622.3	484.1	340.0
100°	71.8	149.7	688.5	697.9	563.6
102.5°	86.8	158.5	706.0	863.1	744.7
105°	112.4	175.0	696.3	1060.2	997.6
107.5°	138.9	194.2	656.0	1161.9	1179.3
110°	157.7	208.1	626.0	1182.0	1256.8

TEST NUMBER: P564008

CATALOG NUMBER: SQ4-PR1-050U-100D-930-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	173.9	221.8	596.1	1165.3	1278.0
115°	199.8	242.6	557.3	1108.8	1263.0
117.5°	224.2	265.1	532.7	1028.7	1202.4
120°	240.4	280.1	521.4	975.0	1147.5
122.5°	254.2	293.8	513.9	921.1	1087.5
125°	274.8	312.9	504.3	849.6	1002.3
127.5°	293.2	331.0	499.0	795.4	926.4
130°	304.4	341.1	496.5	761.4	878.9
132.5°	315.7	352.3	494.0	732.4	836.5
135°	331.0	367.6	490.2	692.1	780.6
137.5°	347.5	380.8	488.3	656.5	730.9
140°	357.5	389.6	487.1	633.8	701.0
142.5°	367.5	397.1	485.8	616.1	672.2
145°	382.5	410.0	484.0	588.0	632.3
147.5°	399.4	422.9	482.4	565.9	600.7
150°	410.6	430.4	482.4	553.3	580.8
152.5°	419.3	436.7	481.2	541.9	564.5
155°	432.4	447.7	480.8	528.0	543.3
157.5°	445.3	457.2	480.8	518.6	530.2
160°	452.7	463.4	480.8	512.3	521.4
162.5°	460.2	468.5	482.1	507.2	513.9
165°	468.4	474.5	482.4	502.7	504.3
167.5°	476.8	479.8	484.0	497.4	498.6
170°	479.3	482.3	484.0	494.9	494.9
172.5°	481.8	483.6	484.0	492.4	492.4
175°	485.5	487.1	484.0	490.2	488.7
177.5°	486.8	486.8	483.0	488.0	485.5
180°	485.5	485.5	485.5	485.5	485.5

(END OF REPORT)