

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564224

Luminaire Tested: **SQ4-PR1-0U-125D-930-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564224
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-0U-125D-930-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7707.4 lumens
Efficiency: N/A
Efficacy: 84.6 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Direct

Input Watts (W): 91.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564224
CATALOG NUMBER: SQ4-PR1-0U-125D-930-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P564224

CATALOG NUMBER: SQ4-PR1-0U-125D-930-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	105	101	98	107	103	99	96	99	96	93	95	92	90	91	89	87	85		
2	100	93	86	81	98	91	85	80	87	82	78	84	80	76	81	78	75	72		
3	92	82	74	68	90	80	73	68	78	71	66	75	70	65	72	68	64	62		
4	85	73	65	58	82	72	64	58	69	63	57	67	61	56	65	60	56	54		
5	78	66	57	51	76	65	57	50	63	55	50	61	54	49	59	53	49	47		
6	72	59	51	45	70	58	50	44	57	49	44	55	49	44	53	48	43	41		
7	67	54	46	40	65	53	45	39	52	44	39	50	44	39	49	43	39	37		
8	63	49	41	35	61	49	41	35	47	40	35	46	40	35	45	39	35	33		
9	58	45	37	32	57	45	37	32	44	37	32	43	36	32	42	36	31	30		
10	55	42	34	29	54	41	34	29	40	34	29	40	33	29	39	33	29	27		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14223	14223	14223
5°	14351	14240	14166
10°	14305	14206	14131
15°	14242	14154	14078
20°	14171	14079	13975
25°	14071	13976	13814
30°	13919	13820	13622
35°	13713	13594	13400
40°	13401	13257	13017
45°	12855	12630	12370
50°	11893	11606	11378
55°	10380	10145	9931
60°	8746	8674	8502
65°	7566	7595	7536
70°	6949	6984	6984
75°	6673	6673	6721
80°	6277	6349	6277
85°	5060	5621	5621



TEST NUMBER: P564224

CATALOG NUMBER: SQ4-PR1-0U-125D-930-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	291.6	3.8
10°-20°	834.2	10.8
20°-30°	1258.2	16.3
30°-40°	1499.1	19.5
40°-50°	1478.0	19.2
50°-60°	1129.6	14.7
60°-70°	699.0	9.1
70°-80°	397.0	5.2
80°-90°	120.8	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2383.9	30.9
0°-40°	3883.0	50.4
0°-60°	6490.6	84.2
0°-90°	7707.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7707.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3083	3083	3083	3083	3083	
5°	3099	3065	3075	3064	3059	294
15°	2982	2951	2964	2953	2948	842
25°	2764	2731	2746	2717	2714	1272
35°	2435	2407	2414	2382	2379	1520
45°	1970	1944	1936	1901	1896	1510
55°	1291	1270	1261	1240	1235	1156
65°	693	688	696	690	690	702
75°	374	374	374	377	377	395
85°	96	101	106	106	106	115
90°	0	0	0	0	0	



TEST NUMBER: P564224

CATALOG NUMBER: SQ4-PR1-0U-125D-930-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3083.1	3083.1	3083.1	3083.1	3083.1
2.5°	3102.2	3075.2	3083.1	3076.4	3061.9
5°	3099.0	3065.3	3075.1	3064.4	3059.2
7.5°	3075.1	3041.9	3051.8	3041.1	3038.0
10°	3053.9	3022.7	3032.6	3021.9	3016.7
12.5°	3030.5	2997.3	3009.3	2996.4	2991.2
15°	2982.2	2951.0	2963.6	2952.9	2947.7
17.5°	2929.1	2895.8	2908.4	2896.0	2889.2
20°	2886.6	2855.4	2868.0	2849.3	2846.8
22.5°	2839.8	2808.7	2821.3	2796.3	2795.8
25°	2764.4	2730.7	2745.8	2716.6	2714.0
27.5°	2674.7	2643.5	2656.1	2626.3	2623.2
30°	2613.1	2581.9	2594.5	2562.5	2557.3
32.5°	2543.0	2513.9	2524.4	2492.4	2489.3
35°	2435.1	2406.6	2413.9	2382.0	2379.4
37.5°	2312.5	2286.5	2290.7	2255.6	2253.0
40°	2225.4	2199.4	2201.5	2164.2	2161.6
42.5°	2129.8	2103.8	2101.6	2064.4	2061.8
45°	1970.4	1944.5	1935.9	1901.3	1896.1
47.5°	1788.8	1762.8	1746.8	1718.6	1715.0
50°	1657.1	1631.1	1617.2	1593.2	1585.4
52.5°	1514.7	1488.8	1477.0	1455.1	1447.3
55°	1290.6	1269.8	1261.4	1240.0	1234.8
57.5°	1077.6	1063.6	1061.2	1040.4	1038.3
60°	948.0	940.2	940.1	921.5	921.5
62.5°	837.6	831.8	836.0	823.7	821.6
65°	693.1	687.9	695.8	690.4	690.4
67.5°	578.9	578.9	583.7	581.6	581.6
70°	515.2	515.2	517.8	517.8	517.8
72.5°	457.8	455.7	462.6	462.6	460.5
75°	374.4	374.4	374.4	377.1	377.1
77.5°	291.6	292.1	294.2	293.7	291.6
80°	236.3	238.9	239.0	236.3	236.3
82.5°	181.1	183.7	183.8	183.2	181.1
85°	95.6	100.8	106.2	106.2	106.2
87.5°	27.6	35.9	42.5	42.4	40.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)