

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563455

Luminaire Tested: **SQ4-PP3-075U-125D-930-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563455
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-075U-125D-930-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9389.8 lumens
Efficiency: N/A
Efficacy: 96.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 97.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563455
CATALOG NUMBER: SQ4-PP3-075U-125D-930-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563455

CATALOG NUMBER: SQ4-PP3-075U-125D-930-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	96	93	89	94	90	87	84	79	77	75	69	67	66	60	58	57	53
2	92	84	78	73	86	79	74	69	70	66	62	61	58	55	53	51	49	45
3	84	74	67	61	78	70	63	58	62	57	52	54	50	47	47	44	42	38
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	39	36	33
5	71	59	51	45	66	56	48	43	49	43	39	43	39	35	38	34	31	28
6	65	53	45	39	61	50	43	37	44	38	34	39	34	31	34	31	28	25
7	60	48	40	34	56	45	38	33	40	34	30	36	31	27	31	28	25	22
8	56	44	36	30	52	41	34	29	37	31	27	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20	18
10	49	37	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13975	13975	13975
5°	14077	13991	13942
10°	14053	13953	13892
15°	13960	13884	13808
20°	13867	13790	13685
25°	13703	13608	13473
30°	13449	13379	13209
35°	13097	13007	12843
40°	12678	12599	12454
45°	12332	12246	12124
50°	11889	11813	11699
55°	11275	11125	11039
60°	10263	9969	9920
65°	9042	8665	8636
70°	7807	7485	7485
75°	6721	6626	6531
80°	5926	5997	5855
85°	4637	5060	5060



TEST NUMBER: P563455

CATALOG NUMBER: SQ4-PP3-075U-125D-930-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.8	2.3
10°-20°	613.4	6.5
20°-30°	918.8	9.8
30°-40°	1077.7	11.5
40°-50°	1081.1	11.5
50°-60°	922.3	9.8
60°-70°	601.5	6.4
70°-80°	301.8	3.2
80°-90°	84.9	0.9
90°-100°	258.7	2.8
100°-110°	711.8	7.6
110°-120°	734.7	7.8
120°-130°	588.6	6.3
130°-140°	462.3	4.9
140°-150°	354.3	3.8
150°-160°	254.7	2.7
160°-170°	155.8	1.7
170°-180°	52.5	0.6
0°-30°	1747.1	18.6
0°-40°	2824.8	30.1
0°-60°	4828.2	51.4
0°-90°	5816.4	61.9
90°-120°	1705.2	18.2
90°-150°	3110.5	33.1
90°-180°	3573.0	38.1
0°-180°	9389.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2272	2272	2272	2272	2272	
5°	2280	2258	2266	2258	2258	217
15°	2192	2171	2180	2172	2168	618
25°	2019	1996	2005	1987	1985	928
35°	1744	1727	1732	1712	1710	1090
45°	1418	1408	1408	1394	1394	1092
55°	1051	1048	1037	1031	1029	934
65°	621	610	595	591	593	620
75°	283	283	279	277	275	307
85°	66	72	72	72	72	77
90°	1	5	8	10	10	5
95°	38	141	458	196	125	41
105°	127	196	784	1194	1115	134
115°	225	274	629	1253	1422	222
125°	310	354	571	965	1131	277
135°	375	416	554	781	884	289
145°	433	463	546	665	717	272
155°	490	506	543	598	615	225
165°	530	537	545	567	571	149
175°	548	550	546	553	552	52
180°	548	548	548	548	548	

TEST NUMBER: P563455

CATALOG NUMBER: SQ4-PP3-075U-125D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2272.0	2272.0	2272.0	2272.0	2272.0
2.5°	2286.3	2267.6	2272.0	2268.6	2259.2
5°	2279.9	2258.5	2266.0	2258.0	2258.0
7.5°	2264.4	2241.0	2248.5	2240.5	2240.1
10°	2250.1	2226.7	2234.1	2226.1	2224.2
12.5°	2229.3	2206.0	2215.0	2205.4	2205.1
15°	2192.3	2170.9	2180.4	2172.3	2168.4
17.5°	2150.5	2127.1	2138.5	2127.4	2125.8
20°	2118.6	2095.3	2106.7	2090.8	2090.8
22.5°	2080.4	2057.0	2070.0	2049.3	2049.3
25°	2019.1	1995.7	2005.1	1987.2	1985.2
27.5°	1946.2	1923.2	1933.1	1912.7	1912.3
30°	1893.6	1872.2	1883.7	1861.7	1859.8
32.5°	1836.3	1816.4	1824.7	1802.8	1800.8
35°	1744.3	1726.8	1732.3	1712.4	1710.4
37.5°	1647.5	1629.6	1636.0	1618.8	1618.0
40°	1579.0	1567.3	1569.1	1555.0	1551.1
42.5°	1515.3	1502.1	1503.8	1489.8	1489.0
45°	1417.7	1408.0	1407.8	1393.8	1393.8
47.5°	1314.2	1306.8	1304.6	1293.1	1292.7
50°	1242.5	1236.7	1234.5	1224.5	1222.6
52.5°	1167.6	1164.9	1158.1	1149.7	1149.3
55°	1051.4	1047.5	1037.4	1031.4	1029.4
57.5°	925.1	917.3	906.0	897.3	898.8
60°	834.3	826.5	810.4	806.4	806.4
62.5°	746.7	737.4	721.2	715.7	718.8
65°	621.3	609.6	595.4	591.4	593.4
67.5°	507.4	496.8	481.5	481.4	479.9
70°	434.1	428.2	416.2	416.2	416.2
72.5°	368.8	366.0	357.2	357.2	355.6
75°	282.8	282.8	278.8	276.7	274.8
77.5°	211.9	212.6	210.7	208.6	205.1
80°	167.3	171.2	169.3	167.2	165.3
82.5°	125.8	129.7	129.4	125.8	125.4
85°	65.7	71.6	71.7	71.7	71.7
87.5°	17.8	24.7	27.1	27.6	29.2
90°	1.2	4.6	8.2	10.5	10.5
92.5°	16.1	68.8	119.3	45.8	37.6
95°	38.5	141.2	457.5	195.6	124.9
97.5°	62.8	156.6	698.2	537.9	379.5
100°	80.5	166.1	773.8	781.0	637.2
102.5°	97.3	177.4	793.4	969.0	837.0
105°	127.2	195.7	784.3	1194.5	1114.6
107.5°	155.7	218.2	739.7	1304.9	1328.6
110°	176.2	233.3	706.1	1332.4	1414.5

TEST NUMBER: P563455

CATALOG NUMBER: SQ4-PP3-075U-125D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	194.9	250.1	672.5	1314.7	1439.7
115°	225.2	274.3	629.1	1252.6	1421.5
117.5°	254.2	299.4	601.5	1165.6	1356.6
120°	271.9	315.3	589.4	1100.4	1297.8
122.5°	287.8	331.2	581.0	1043.2	1230.6
125°	310.4	353.8	570.7	965.4	1130.9
127.5°	331.9	373.2	563.9	900.6	1045.7
130°	343.1	385.3	560.2	862.0	994.4
132.5°	356.2	398.4	557.4	828.1	947.7
135°	374.6	415.7	554.4	780.8	883.5
137.5°	391.9	430.0	551.8	742.6	827.2
140°	405.0	440.4	550.9	717.2	793.6
142.5°	416.2	448.8	549.0	694.5	760.0
145°	433.0	462.7	546.2	665.2	716.6
147.5°	451.0	476.5	544.8	639.3	680.4
150°	462.2	485.0	543.9	625.1	657.1
152.5°	472.4	493.4	542.9	612.9	639.3
155°	490.2	506.2	542.7	597.9	615.1
157.5°	503.0	516.0	542.7	585.7	597.6
160°	512.4	522.6	542.7	579.1	588.2
162.5°	519.8	528.3	543.6	573.4	580.7
165°	529.9	536.7	545.0	567.3	570.7
167.5°	536.9	542.1	546.2	562.1	563.0
170°	541.5	545.0	546.2	560.2	560.2
172.5°	545.3	546.9	546.2	557.4	556.5
175°	548.5	549.7	546.2	553.2	552.0
177.5°	549.5	549.5	545.7	551.3	549.5
180°	548.5	548.5	548.5	548.5	548.5

(END OF REPORT)