

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564368

Luminaire Tested: **SQ4-PR1-125U-075D-930-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P564368  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PR1-125U-075D-930-1D-UNV-STD-W-8  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 12504.9 lumens  
Efficiency: N/A  
Efficacy: 107.8 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35  
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 116  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P564368  
CATALOG NUMBER: SQ4-PR1-125U-075D-930-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P564368

CATALOG NUMBER: SQ4-PR1-125U-075D-930-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36
1	95	91	87	84	86	82	79	76	67	64	62	52	51	49	39	38	37	31
2	87	79	74	69	78	72	67	63	59	55	52	46	44	42	34	33	32	26
3	79	70	63	57	71	64	58	53	52	48	44	41	38	35	31	29	27	23
4	72	62	54	49	65	56	50	45	46	41	38	36	33	30	28	25	24	19
5	66	55	47	42	60	50	44	38	41	36	32	33	29	26	25	22	21	17
6	61	49	42	36	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	56	45	37	31	51	41	34	29	34	29	25	27	23	20	21	18	16	13
8	52	40	33	28	47	37	30	26	31	26	22	25	21	18	19	16	14	12
9	49	37	30	25	44	34	27	23	28	23	20	23	19	16	17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8388	8388	8388
5°	8464	8398	8355
10°	8437	8378	8334
15°	8400	8347	8302
20°	8357	8303	8242
25°	8299	8243	8147
30°	8209	8150	8034
35°	8088	8017	7903
40°	7903	7818	7677
45°	7581	7448	7295
50°	7014	6845	6710
55°	6121	5983	5857
60°	5158	5115	5014
65°	4462	4479	4445
70°	4098	4119	4119
75°	3935	3935	3964
80°	3703	3746	3703
85°	2985	3313	3313



TEST NUMBER: P564368

CATALOG NUMBER: SQ4-PR1-125U-075D-930-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	171.9	1.4
10°-20°	492.0	3.9
20°-30°	742.0	5.9
30°-40°	884.1	7.1
40°-50°	871.7	7.0
50°-60°	666.2	5.3
60°-70°	412.3	3.3
70°-80°	234.2	1.9
80°-90°	74.1	0.6
90°-100°	576.6	4.6
100°-110°	1553.1	12.4
110°-120°	1629.9	13.0
120°-130°	1322.7	10.6
130°-140°	1037.3	8.3
140°-150°	796.4	6.4
150°-160°	572.6	4.6
160°-170°	349.8	2.8
170°-180°	118.0	0.9
0°-30°	1405.9	11.2
0°-40°	2290.1	18.3
0°-60°	3827.9	30.6
0°-90°	4548.4	36.4
90°-120°	3759.6	30.1
90°-150°	6916.0	55.3
90°-180°	7956.0	63.6
0°-180°	12504.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1818	1818	1818	1818	1818	
5°	1828	1808	1814	1807	1804	173
15°	1759	1740	1748	1742	1738	496
25°	1630	1610	1619	1602	1601	750
35°	1436	1419	1424	1405	1403	896
45°	1162	1147	1142	1121	1118	890
55°	761	749	744	731	728	682
65°	409	406	410	407	407	414
75°	221	221	221	222	222	233
85°	56	59	63	63	63	66
90°	3	9	19	20	20	8
95°	88	314	945	483	334	92
105°	287	447	1718	2570	2412	302
115°	507	621	1430	2764	3126	499
125°	692	795	1284	2171	2554	618
135°	834	930	1248	1751	1983	643
145°	964	1039	1232	1497	1608	605
155°	1094	1134	1222	1343	1386	504
165°	1187	1201	1226	1275	1281	335
175°	1234	1232	1228	1245	1242	117
180°	1232	1232	1232	1232	1232	

TEST NUMBER: P564368

CATALOG NUMBER: SQ4-PR1-125U-075D-930-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1818.3	1818.3	1818.3	1818.3	1818.3
2.5°	1829.6	1813.6	1818.3	1814.3	1805.8
5°	1827.7	1807.8	1813.6	1807.3	1804.2
7.5°	1813.6	1794.0	1799.8	1793.5	1791.7
10°	1801.1	1782.7	1788.5	1782.2	1779.1
12.5°	1787.3	1767.7	1774.8	1767.2	1764.1
15°	1758.8	1740.4	1747.8	1741.5	1738.4
17.5°	1727.5	1707.9	1715.2	1707.9	1704.0
20°	1702.4	1684.0	1691.4	1680.4	1678.9
22.5°	1674.8	1656.5	1663.9	1649.1	1648.8
25°	1630.4	1610.4	1619.4	1602.1	1600.6
27.5°	1577.4	1559.0	1566.5	1548.9	1547.0
30°	1541.1	1522.7	1530.1	1511.3	1508.2
32.5°	1499.7	1482.6	1488.8	1469.9	1468.1
35°	1436.2	1419.3	1423.6	1404.8	1403.3
37.5°	1363.8	1348.5	1351.0	1330.2	1328.7
40°	1312.4	1297.1	1298.3	1276.4	1274.8
42.5°	1256.0	1240.7	1239.4	1217.5	1216.0
45°	1162.1	1146.8	1141.7	1121.3	1118.2
47.5°	1055.0	1039.6	1030.2	1013.6	1011.4
50°	977.3	962.0	953.8	939.6	935.0
52.5°	893.3	878.0	871.1	858.1	853.5
55°	761.1	748.9	743.9	731.3	728.3
57.5°	635.5	627.3	625.8	613.6	612.4
60°	559.1	554.5	554.4	543.5	543.5
62.5°	494.0	490.6	493.0	485.8	484.6
65°	408.8	405.7	410.3	407.2	407.2
67.5°	341.4	341.4	344.2	343.0	343.0
70°	303.8	303.8	305.4	305.4	305.4
72.5°	270.0	268.8	272.8	272.8	271.6
75°	220.8	220.8	220.8	222.4	222.4
77.5°	172.0	172.3	173.5	173.2	172.0
80°	139.4	140.9	141.0	139.4	139.4
82.5°	106.8	108.3	108.4	108.0	106.8
85°	56.4	59.4	62.6	62.6	62.6
87.5°	16.9	23.0	28.8	29.1	27.9
90°	3.1	9.3	18.8	20.4	20.4
92.5°	38.3	135.3	267.5	128.8	89.5
95°	87.9	313.6	945.2	483.3	334.4
97.5°	140.4	359.0	1482.4	1238.4	933.9
100°	180.6	377.1	1653.3	1729.8	1435.0
102.5°	219.5	402.5	1709.8	2097.7	1855.8
105°	287.3	447.0	1717.6	2569.7	2411.6
107.5°	351.4	493.8	1644.5	2812.3	2853.1
110°	394.1	529.2	1577.9	2887.6	3036.5

TEST NUMBER: P564368

CATALOG NUMBER: SQ4-PR1-125U-075D-930-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	439.3	564.6	1513.8	2870.9	<i>3115.6</i>
115°	<i>507.1</i>	<i>620.7</i>	<i>1430.3</i>	<i>2763.7</i>	<i>3126.0</i>
117.5°	569.0	675.5	1365.6	2592.5	<i>2996.0</i>
120°	609.2	712.0	1333.0	2469.7	<i>2884.2</i>
122.5°	644.4	746.0	1309.1	2344.1	<i>2757.3</i>
125°	692.4	795.3	1284.3	2170.7	<i>2554.5</i>
127.5°	738.6	839.9	1268.6	2017.8	<i>2360.4</i>
130°	766.2	867.5	1262.3	1930.2	<i>2231.1</i>
132.5°	793.8	893.9	1256.0	1853.0	<i>2129.3</i>
135°	833.7	930.4	1248.2	1751.2	<i>1983.0</i>
137.5°	871.7	964.4	1244.1	1664.8	<i>1855.2</i>
140°	898.1	987.1	1240.3	1611.6	<i>1783.6</i>
142.5°	925.7	1008.6	1237.8	1562.0	<i>1707.0</i>
145°	964.0	1039.2	1232.5	1497.2	<i>1607.7</i>
147.5°	1005.5	1070.9	1227.2	1442.7	<i>1529.5</i>
150°	1033.1	1089.9	1224.6	1408.4	<i>1480.6</i>
152.5°	1058.2	1107.7	1223.4	1380.5	<i>1439.1</i>
155°	1094.3	1134.2	1221.5	1343.4	<i>1386.4</i>
157.5°	1126.0	1157.1	1221.8	1317.3	<i>1346.2</i>
160°	1146.1	1172.2	1223.1	1302.1	<i>1323.6</i>
162.5°	1163.7	1184.9	1224.3	1289.4	<i>1304.7</i>
165°	1187.0	1200.8	1226.2	1275.0	<i>1281.2</i>
167.5°	1205.8	1213.8	1227.8	1264.0	<i>1266.4</i>
170°	1218.4	1221.4	1227.8	1257.6	<i>1257.6</i>
172.5°	1225.9	1226.5	1229.0	1251.3	<i>1251.3</i>
175°	1234.1	1232.5	1227.8	1245.0	<i>1241.9</i>
177.5°	1237.5	1235.1	1228.7	1238.7	<i>1236.3</i>
180°	1232.5	1232.5	1232.5	1232.5	<i>1232.5</i>

(END OF REPORT)