

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564608

Luminaire Tested: **SQ4-PW1-025U-125D-930-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564608
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-025U-125D-930-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9207.1 lumens
Efficiency: N/A
Efficacy: 90.6 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 101.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564608
CATALOG NUMBER: SQ4-PW1-025U-125D-930-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P564608

CATALOG NUMBER: SQ4-PW1-025U-125D-930-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	115	115	115	115	110	110	110	110	102	102	102	94	94	94	87	87	87	83
1	105	101	97	93	101	97	93	90	90	87	84	83	81	79	77	75	74	71
2	96	88	82	77	92	85	79	74	79	74	70	73	69	66	68	65	62	59
3	88	78	70	64	84	75	68	62	70	64	59	65	60	56	60	56	53	50
4	81	69	61	54	77	67	59	53	62	56	51	58	53	48	54	50	46	43
5	74	62	53	47	71	60	52	46	56	49	44	52	46	42	49	44	40	38
6	68	56	47	41	65	54	46	40	50	44	39	47	41	37	44	39	35	33
7	63	51	42	36	61	49	41	36	46	39	34	43	37	33	40	35	31	29
8	59	46	38	32	57	45	37	32	42	35	31	40	34	29	37	32	28	26
9	55	42	34	29	53	41	34	29	39	32	28	36	31	27	34	29	26	24
10	52	39	31	26	50	38	31	26	36	29	25	34	28	24	32	27	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13904	13904	13904
5°	13994	13883	13822
10°	13882	13770	13696
15°	13735	13583	13532
20°	13571	13362	13336
25°	13382	13138	13098
30°	13098	12901	12816
35°	12727	12547	12472
40°	12329	12138	12090
45°	11850	11694	11642
50°	11359	11263	11187
55°	10829	10829	10657
60°	10168	10364	9997
65°	9304	9768	9073
70°	8202	8990	7987
75°	7005	8046	6816
80°	5433	6772	5502
85°	3515	5203	4637



TEST NUMBER: P564608

CATALOG NUMBER: SQ4-PW1-025U-125D-930-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	283.8	3.1
10°-20°	801.3	8.7
20°-30°	1188.6	12.9
30°-40°	1390.8	15.1
40°-50°	1384.6	15.0
50°-60°	1195.6	13.0
60°-70°	860.6	9.3
70°-80°	451.3	4.9
80°-90°	113.2	1.2
90°-100°	115.6	1.3
100°-110°	303.9	3.3
110°-120°	315.1	3.4
120°-130°	252.8	2.7
130°-140°	198.3	2.2
140°-150°	152.2	1.7
150°-160°	109.6	1.2
160°-170°	67.1	0.7
170°-180°	22.7	0.2
0°-30°	2273.7	24.7
0°-40°	3664.5	39.8
0°-60°	6244.7	67.8
0°-90°	7669.8	83.3
90°-120°	734.6	8.0
90°-150°	1337.9	14.5
90°-180°	1537.0	16.7
0°-180°	9207.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3014	3014	3014	3014	3014	
5°	3022	2988	2998	2990	2985	286
15°	2876	2840	2844	2839	2834	811
25°	2629	2585	2581	2565	2573	1209
35°	2260	2229	2228	2207	2215	1413
45°	1816	1801	1792	1787	1784	1401
55°	1346	1344	1346	1328	1325	1201
65°	852	878	895	860	831	845
75°	393	429	451	421	382	421
85°	66	87	98	93	88	88
90°	2	4	12	6	6	4
95°	15	60	199	103	70	17
105°	55	83	336	510	476	58
115°	97	118	269	537	613	96
125°	135	152	245	414	488	120
135°	161	178	237	334	379	125
145°	187	199	234	285	307	117
155°	211	217	234	257	264	97
165°	228	231	234	243	246	64
175°	237	237	236	239	239	23
180°	237	237	237	237	237	



TEST NUMBER: P564608

CATALOG NUMBER: SQ4-PW1-025U-125D-930-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3014.1	3014.1	3014.1	3014.1	3014.1
2.5°	3031.1	3006.1	3014.1	3007.4	2992.8
5°	3022.0	2988.3	2998.1	2990.0	2984.9
7.5°	2991.2	2960.1	2967.3	2958.8	2955.6
10°	2963.6	2932.4	2939.7	2929.0	2923.8
12.5°	2931.7	2898.5	2905.7	2895.0	2891.9
15°	2876.0	2839.6	2844.1	2838.7	2833.5
17.5°	2811.2	2774.3	2775.1	2766.5	2765.5
20°	2764.4	2725.5	2721.9	2711.4	2716.6
22.5°	2713.5	2672.4	2668.8	2654.1	2661.4
25°	2629.0	2584.9	2581.2	2565.4	2573.2
27.5°	2531.3	2487.7	2487.7	2465.6	2473.9
30°	2459.0	2417.5	2421.9	2395.6	2405.9
32.5°	2382.6	2345.2	2347.5	2321.2	2331.6
35°	2259.9	2228.7	2228.0	2206.9	2214.7
37.5°	2134.5	2107.0	2102.7	2090.5	2092.6
40°	2047.4	2024.1	2015.6	2007.6	2007.6
42.5°	1956.1	1934.8	1926.3	1920.5	1918.4
45°	1816.4	1800.8	1792.5	1787.1	1784.5
47.5°	1678.3	1663.8	1656.5	1652.8	1650.2
50°	1582.7	1572.3	1569.4	1561.4	1558.8
52.5°	1487.1	1480.9	1478.1	1467.9	1465.3
55°	1346.4	1343.8	1346.4	1327.7	1325.1
57.5°	1199.8	1203.9	1212.5	1187.4	1181.2
60°	1102.1	1112.4	1123.3	1093.9	1083.5
62.5°	1002.2	1018.8	1034.1	1000.3	985.7
65°	852.4	878.4	894.9	859.8	831.2
67.5°	708.0	740.2	760.0	722.1	689.9
70°	608.1	644.5	666.5	628.5	592.2
72.5°	521.0	561.5	579.4	543.6	507.2
75°	393.0	429.4	451.4	421.3	382.4
77.5°	278.8	313.1	331.4	305.2	273.0
80°	204.5	240.8	254.9	233.1	207.1
82.5°	145.0	175.1	184.8	171.7	154.0
85°	66.4	87.2	98.3	92.8	87.6
87.5°	17.3	32.4	42.8	41.6	43.7
90°	1.5	4.5	12.2	6.1	6.1
92.5°	6.4	30.8	68.1	30.2	19.5
95°	15.2	59.8	199.2	102.6	69.9
97.5°	26.5	65.7	298.0	237.0	174.5
100°	35.0	70.6	328.4	332.8	258.5
102.5°	42.3	75.6	336.9	414.5	350.9
105°	54.7	83.0	336.0	510.1	475.9
107.5°	67.5	93.7	316.8	559.7	568.0
110°	76.0	99.8	301.0	572.5	608.1



TEST NUMBER: P564608

CATALOG NUMBER: SQ4-PW1-025U-125D-930-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	84.5	107.1	286.4	564.4	619.1
115°	97.3	118.1	269.1	536.9	612.7
117.5°	109.8	128.8	257.2	498.8	582.9
120°	117.1	134.9	252.4	473.2	554.9
122.5°	124.4	142.2	248.7	447.6	528.2
125°	135.3	151.7	244.8	413.7	488.0
127.5°	144.1	160.8	241.4	386.4	449.1
130°	149.0	166.8	240.2	369.2	427.2
132.5°	153.9	171.7	239.0	354.5	406.5
135°	161.2	177.5	237.2	334.0	378.6
137.5°	168.8	184.8	236.9	318.6	355.2
140°	174.8	189.7	235.7	306.4	340.6
142.5°	179.7	193.4	235.7	297.7	327.2
145°	187.0	198.9	234.1	284.8	307.1
147.5°	194.3	205.9	234.1	274.1	292.5
150°	199.2	209.6	234.1	267.9	282.8
152.5°	204.0	212.1	234.1	263.0	274.3
155°	211.3	217.3	234.1	257.1	264.5
157.5°	216.8	222.5	234.1	251.9	257.2
160°	220.5	224.9	234.1	249.4	252.4
162.5°	224.1	227.4	234.1	247.0	249.9
165°	228.1	231.0	234.1	243.3	246.3
167.5°	231.7	233.2	235.7	241.8	243.0
170°	234.1	235.6	235.7	241.7	241.7
172.5°	235.3	235.6	235.7	240.5	239.3
175°	237.2	237.2	235.7	238.7	238.7
177.5°	237.2	237.2	236.0	238.4	237.2
180°	237.2	237.2	237.2	237.2	237.2

(END OF REPORT)