

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563623

Luminaire Tested: **SQ4-PP3-100U-100D-930-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563623
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-100U-100D-930-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9352.3 lumens
Efficiency: N/A
Efficacy: 100.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 92.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563623
CATALOG NUMBER: SQ4-PP3-100U-100D-930-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563623

CATALOG NUMBER: SQ4-PP3-100U-100D-930-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49					49			
1	98	93	90	86	90	86	83	80	73	70	68	60	59	57	49	48	47					41				
2	89	82	76	71	82	76	70	66	64	60	57	53	50	48	43	41	40					35				
3	81	72	65	59	75	67	60	55	57	52	48	47	44	41	38	36	34					30				
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	32	29					26				
5	68	57	49	43	63	53	46	40	45	40	35	38	34	30	31	28	26					22				
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	28	25	23					20				
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	22	20					17				
8	54	42	34	29	50	39	32	27	34	28	24	28	24	21	24	20	18					16				
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16					14				
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15					13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10950	10950	10950
5°	11031	10964	10925
10°	11012	10934	10886
15°	10939	10880	10820
20°	10867	10805	10724
25°	10738	10664	10558
30°	10539	10484	10351
35°	10264	10193	10064
40°	9935	9872	9760
45°	9664	9596	9501
50°	9316	9257	9167
55°	8835	8717	8651
60°	8043	7813	7773
65°	7085	6789	6768
70°	6118	5864	5864
75°	5266	5190	5117
80°	4644	4697	4587
85°	3634	3966	3966



TEST NUMBER: P563623

CATALOG NUMBER: SQ4-PP3-100U-100D-930-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.3	1.8
10°-20°	480.7	5.1
20°-30°	720.0	7.7
30°-40°	844.5	9.0
40°-50°	847.2	9.1
50°-60°	722.7	7.7
60°-70°	471.3	5.0
70°-80°	236.5	2.5
80°-90°	67.0	0.7
90°-100°	345.5	3.7
100°-110°	953.9	10.2
110°-120°	983.8	10.5
120°-130°	790.5	8.5
130°-140°	621.3	6.6
140°-150°	476.5	5.1
150°-160°	342.5	3.7
160°-170°	209.4	2.2
170°-180°	70.6	0.8
0°-30°	1369.1	14.6
0°-40°	2213.6	23.7
0°-60°	3783.5	40.5
0°-90°	4558.2	48.7
90°-120°	2283.2	24.4
90°-150°	4171.5	44.6
90°-180°	4794.0	51.3
0°-180°	9352.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1780	1780	1780	1780	1780	
5°	1787	1770	1776	1769	1769	170
15°	1718	1701	1709	1702	1699	485
25°	1582	1564	1571	1557	1556	728
35°	1367	1353	1358	1342	1340	854
45°	1111	1103	1103	1092	1092	855
55°	824	821	813	808	807	732
65°	487	478	466	464	465	486
75°	222	222	218	217	215	240
85°	52	56	56	56	56	61
90°	2	5	9	11	12	6
95°	51	187	627	258	168	54
105°	170	262	1050	1602	1509	181
115°	305	368	845	1673	1903	299
125°	418	476	766	1297	1522	372
135°	503	557	745	1050	1184	389
145°	583	624	736	894	962	365
155°	658	680	730	802	828	303
165°	712	721	733	762	767	201
175°	738	739	734	745	742	70
180°	738	738	738	738	738	

TEST NUMBER: P563623

CATALOG NUMBER: SQ4-PP3-100U-100D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1780.3	1780.3	1780.3	1780.3	1780.3
2.5°	1791.6	1776.9	1780.3	1777.7	1770.4
5°	1786.6	1769.8	1775.7	1769.4	1769.4
7.5°	1774.4	1756.1	1761.9	1755.7	1755.4
10°	1763.2	1744.9	1750.7	1744.4	1742.9
12.5°	1747.0	1728.6	1735.7	1728.2	1727.9
15°	1717.9	1701.1	1708.6	1702.3	1699.2
17.5°	1685.2	1666.9	1675.8	1667.0	1665.8
20°	1660.2	1641.9	1650.8	1638.4	1638.4
22.5°	1630.2	1611.9	1622.1	1605.9	1605.9
25°	1582.2	1563.9	1571.3	1557.2	1555.7
27.5°	1525.1	1507.1	1514.8	1498.9	1498.5
30°	1483.9	1467.1	1476.1	1458.9	1457.4
32.5°	1438.9	1423.4	1429.9	1412.7	1411.2
35°	1366.9	1353.1	1357.5	1341.9	1340.3
37.5°	1291.0	1277.0	1282.0	1268.5	1267.9
40°	1237.3	1228.2	1229.5	1218.6	1215.5
42.5°	1187.4	1177.0	1178.4	1167.4	1166.8
45°	1111.0	1103.3	1103.2	1092.2	1092.2
47.5°	1029.8	1024.0	1022.3	1013.3	1013.0
50°	973.6	969.1	967.4	959.6	958.0
52.5°	915.0	912.8	907.5	900.9	900.6
55°	823.9	820.8	812.9	808.2	806.7
57.5°	724.9	718.8	710.0	703.1	704.3
60°	653.8	647.7	635.1	631.9	631.9
62.5°	585.1	577.8	565.2	560.8	563.3
65°	486.8	477.7	466.5	463.5	465.0
67.5°	397.6	389.3	377.3	377.3	376.0
70°	340.2	335.6	326.1	326.1	326.1
72.5°	289.0	286.8	279.9	279.9	278.7
75°	221.6	221.6	218.4	216.9	215.3
77.5°	166.0	166.6	165.1	163.5	160.7
80°	131.1	134.1	132.6	131.0	129.5
82.5°	98.6	101.7	101.4	98.6	98.3
85°	51.5	56.1	56.2	56.2	56.2
87.5°	14.2	19.5	21.9	22.1	23.6
90°	2.4	4.7	9.4	10.7	11.8
92.5°	21.2	88.2	157.7	57.6	44.9
95°	50.8	187.0	626.9	257.7	167.6
97.5°	84.1	209.4	928.6	714.9	517.8
100°	108.6	222.9	1040.0	1047.4	851.2
102.5°	132.2	238.2	1061.8	1294.1	1108.0
105°	170.0	262.3	1049.5	1602.2	1508.7
107.5°	210.1	292.3	990.9	1750.8	1784.9
110°	238.5	312.3	945.6	1782.7	1893.6



TEST NUMBER: P563623

CATALOG NUMBER: SQ4-PP3-100U-100D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	264.0	335.1	903.1	1757.5	1920.9
115°	304.6	368.1	845.3	1673.3	1903.0
117.5°	340.0	403.2	807.2	1554.8	1816.1
120°	363.6	425.9	792.1	1474.6	1737.7
122.5°	386.3	445.8	779.9	1399.6	1649.0
125°	417.9	475.6	766.2	1296.6	1521.7
127.5°	444.8	502.5	758.1	1209.5	1403.6
130°	462.8	520.5	754.4	1156.2	1332.8
132.5°	479.8	534.7	750.6	1111.4	1271.4
135°	502.9	557.2	744.9	1050.2	1184.1
137.5°	528.9	578.3	742.1	998.7	1113.0
140°	543.0	591.5	740.2	964.4	1064.8
142.5°	559.1	603.9	738.3	933.9	1022.3
145°	583.2	623.6	735.5	894.0	962.1
147.5°	606.3	641.6	732.9	860.4	913.3
150°	623.3	652.2	731.9	840.3	883.0
152.5°	636.5	663.5	731.0	823.2	858.5
155°	657.6	679.5	729.6	802.2	827.5
157.5°	676.9	693.8	729.8	786.9	804.2
160°	688.2	703.2	730.7	778.3	790.9
162.5°	697.7	710.8	731.7	770.6	780.6
165°	711.9	721.1	733.1	761.6	767.3
167.5°	722.7	728.3	734.3	756.0	757.9
170°	728.4	733.0	734.3	753.2	753.2
172.5°	733.1	735.9	734.3	749.4	748.5
175°	737.8	739.0	734.3	744.9	742.5
177.5°	739.7	738.8	734.0	740.6	738.8
180°	737.8	737.8	737.8	737.8	737.8

(END OF REPORT)