

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564896

Luminaire Tested: **SQ4-PW1-0U-125D-930-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564896
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-0U-125D-930-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7668.5 lumens
Efficiency: N/A
Efficacy: 84.2 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Direct

Input Watts (W): 91.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564896
CATALOG NUMBER: SQ4-PW1-0U-125D-930-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P564896

CATALOG NUMBER: SQ4-PW1-0U-125D-930-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	101	97	107	102	99	95	98	95	92	94	92	89	91	89	87	85
2	100	92	85	80	97	90	84	79	86	81	77	83	79	75	80	76	73	71
3	91	81	73	67	89	79	72	66	76	70	65	74	68	64	71	66	63	60
4	84	72	63	57	81	71	63	56	68	61	56	66	60	55	64	58	54	52
5	77	64	56	49	75	63	55	49	61	54	48	59	53	48	57	52	47	45
6	71	58	49	43	69	57	49	43	55	48	42	54	47	42	52	46	42	40
7	66	53	44	38	64	52	44	38	50	43	38	49	42	37	48	42	37	35
8	62	48	40	34	60	48	40	34	46	39	34	45	38	34	44	38	33	31
9	58	44	36	31	56	44	36	31	43	35	31	42	35	30	41	35	30	28
10	54	41	33	28	53	40	33	28	39	33	28	39	32	28	38	32	28	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13904	13904	13904
5°	13994	13883	13822
10°	13882	13770	13696
15°	13735	13583	13532
20°	13571	13362	13336
25°	13382	13138	13098
30°	13098	12901	12816
35°	12727	12547	12472
40°	12329	12138	12090
45°	11850	11694	11642
50°	11359	11263	11187
55°	10829	10829	10657
60°	10168	10364	9997
65°	9304	9768	9073
70°	8202	8990	7987
75°	7005	8046	6816
80°	5433	6772	5502
85°	3515	5203	4637



TEST NUMBER: P564896

CATALOG NUMBER: SQ4-PW1-0U-125D-930-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	283.8	3.7
10°-20°	801.3	10.4
20°-30°	1188.6	15.5
30°-40°	1390.8	18.1
40°-50°	1384.6	18.1
50°-60°	1195.6	15.6
60°-70°	860.6	11.2
70°-80°	451.3	5.9
80°-90°	111.9	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2273.7	29.6
0°-40°	3664.5	47.8
0°-60°	6244.7	81.4
0°-90°	7668.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7668.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3014	3014	3014	3014	3014	
5°	3022	2988	2998	2990	2985	286
15°	2876	2840	2844	2839	2834	811
25°	2629	2585	2581	2565	2573	1209
35°	2260	2229	2228	2207	2215	1413
45°	1816	1801	1792	1787	1784	1401
55°	1346	1344	1346	1328	1325	1201
65°	852	878	895	860	831	845
75°	393	429	451	421	382	421
85°	66	87	98	93	88	90
90°	0	0	0	0	0	



TEST NUMBER: P564896

CATALOG NUMBER: SQ4-PW1-0U-125D-930-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3014.1	3014.1	3014.1	3014.1	3014.1
2.5°	3031.1	3006.1	3014.1	3007.4	2992.8
5°	3022.0	2988.3	2998.1	2990.0	2984.9
7.5°	2991.2	2960.1	2967.3	2958.8	2955.6
10°	2963.6	2932.4	2939.7	2929.0	2923.8
12.5°	2931.7	2898.5	2905.7	2895.0	2891.9
15°	2876.0	2839.6	2844.1	2838.7	2833.5
17.5°	2811.2	2774.3	2775.1	2766.5	2765.5
20°	2764.4	2725.5	2721.9	2711.4	2716.6
22.5°	2713.5	2672.4	2668.8	2654.1	2661.4
25°	2629.0	2584.9	2581.2	2565.4	2573.2
27.5°	2531.3	2487.7	2487.7	2465.6	2473.9
30°	2459.0	2417.5	2421.9	2395.6	2405.9
32.5°	2382.6	2345.2	2347.5	2321.2	2331.6
35°	2259.9	2228.7	2228.0	2206.9	2214.7
37.5°	2134.5	2107.0	2102.7	2090.5	2092.6
40°	2047.4	2024.1	2015.6	2007.6	2007.6
42.5°	1956.1	1934.8	1926.3	1920.5	1918.4
45°	1816.4	1800.8	1792.5	1787.1	1784.5
47.5°	1678.3	1663.8	1656.5	1652.8	1650.2
50°	1582.7	1572.3	1569.4	1561.4	1558.8
52.5°	1487.1	1480.9	1478.1	1467.9	1465.3
55°	1346.4	1343.8	1346.4	1327.7	1325.1
57.5°	1199.8	1203.9	1212.5	1187.4	1181.2
60°	1102.1	1112.4	1123.3	1093.9	1083.5
62.5°	1002.2	1018.8	1034.1	1000.3	985.7
65°	852.4	878.4	894.9	859.8	831.2
67.5°	708.0	740.2	760.0	722.1	689.9
70°	608.1	644.5	666.5	628.5	592.2
72.5°	521.0	561.5	579.4	543.6	507.2
75°	393.0	429.4	451.4	421.3	382.4
77.5°	278.8	313.1	331.4	305.2	273.0
80°	204.5	240.8	254.9	233.1	207.1
82.5°	145.0	175.1	184.8	171.7	154.0
85°	66.4	87.2	98.3	92.8	87.6
87.5°	17.0	31.5	40.4	40.4	42.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)