

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519703

Luminaire Tested: **SQ4-075U-0D-930-1D-UNV-STD-W-12**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519703
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-075U-0D-930-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7147.0 lumens
Efficiency: N/A
Efficacy: 132.4 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Indirect

Input Watts (W): 54
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519703
CATALOG NUMBER: SQ4-075U-0D-930-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P519703

CATALOG NUMBER: SQ4-075U-0D-930-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20	
RC	80								50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	2717	32287	8815
100°	2853	27409	22572
105°	3023	18639	26487
110°	3170	12698	25438
115°	3278	9155	20689
120°	3345	7251	15965
125°	3329	6120	12127
130°	3284	5361	9515
135°	3259	4822	7685
140°	3252	4423	6372
145°	3251	4101	5381
150°	3282	3863	4667
155°	3327	3683	4174
160°	3354	3552	3850
165°	3374	3471	3634
170°	3382	3411	3499
175°	3387	3372	3409



TEST NUMBER: P519703

CATALOG NUMBER: SQ4-075U-0D-930-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	517.4	7.2
100°-110°	1423.6	19.9
110°-120°	1469.4	20.6
120°-130°	1177.3	16.5
130°-140°	924.7	12.9
140°-150°	708.6	9.9
150°-160°	509.5	7.1
160°-170°	311.5	4.4
170°-180°	105.0	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	3410.4	47.7
90°-150°	6220.9	87.0
90°-180°	7147.0	100.0
0°-180°	7147.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	2	9	16	21	21	
95°	77	282	915	391	250	86
105°	254	391	1569	2389	2229	268
115°	450	549	1258	2505	2843	445
125°	621	708	1141	1931	2262	554
135°	749	831	1109	1562	1767	578
145°	866	925	1092	1330	1433	543
155°	980	1012	1085	1196	1230	450
165°	1060	1073	1090	1135	1141	299
175°	1097	1099	1092	1106	1104	104
180°	1097	1097	1097	1097	1097	



TEST NUMBER: P519703

CATALOG NUMBER: SQ4-075U-0D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	2.3	9.2	16.3	21.0	21.0
92.5°	32.2	137.7	238.6	91.6	75.2
95°	77.0	282.4	915.0	391.3	249.8
97.5°	125.6	313.2	1396.3	1075.9	759.1
100°	161.1	332.2	1547.6	1562.0	1274.5
102.5°	194.7	354.9	1586.8	1937.9	1674.1
105°	254.4	391.4	1568.6	2388.9	2229.1
107.5°	311.4	436.5	1479.4	2609.8	2657.2
110°	352.5	466.6	1412.2	2664.7	2829.0
112.5°	389.8	500.3	1345.0	2629.3	2879.5
115°	450.5	548.6	1258.1	2505.3	2843.0
117.5°	508.4	598.8	1203.0	2331.2	2713.3
120°	543.9	630.6	1178.8	2200.8	2595.6
122.5°	575.6	662.3	1162.0	2086.4	2461.2
125°	620.9	707.6	1141.4	1930.9	2261.8
127.5°	663.8	746.5	1127.9	1801.1	2091.4
130°	686.3	770.7	1120.4	1724.0	1988.7
132.5°	712.4	796.8	1114.8	1656.2	1895.4
135°	749.3	831.4	1108.7	1561.6	1767.0
137.5°	783.8	860.0	1103.6	1485.1	1654.5
140°	810.0	880.7	1101.7	1434.3	1587.2
142.5°	832.4	897.6	1098.0	1389.0	1520.0
145°	866.0	925.3	1092.4	1330.5	1433.2
147.5°	901.9	953.1	1089.6	1278.7	1360.8
150°	924.3	970.0	1087.7	1250.2	1314.1
152.5°	944.9	986.9	1085.9	1225.7	1278.7
155°	980.4	1012.3	1085.4	1195.9	1230.1
157.5°	1006.0	1032.1	1085.4	1171.4	1195.1
160°	1024.7	1045.2	1085.4	1158.2	1176.4
162.5°	1039.6	1056.5	1087.3	1146.9	1161.5
165°	1059.7	1073.4	1090.1	1134.6	1141.4
167.5°	1073.7	1084.2	1092.4	1124.2	1126.0
170°	1083.1	1089.9	1092.4	1120.4	1120.4
172.5°	1090.5	1093.7	1092.4	1114.8	1112.9
175°	1097.1	1099.3	1092.4	1106.4	1104.1
177.5°	1098.9	1098.9	1091.5	1102.6	1098.9
180°	1097.1	1097.1	1097.1	1097.1	1097.1

(END OF REPORT)