

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519727

Luminaire Tested: **SQ4-100U-0D-930-1D-UNV-STD-W-12**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519727
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-100U-0D-930-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9588.0 lumens
Efficiency: N/A
Efficacy: 129.6 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Indirect

Input Watts (W): 74
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519727
CATALOG NUMBER: SQ4-100U-0D-930-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P519727

CATALOG NUMBER: SQ4-100U-0D-930-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20
RC	80								50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	3582	44238	11831
100°	3847	36840	30149
105°	4040	24941	35854
110°	4288	17005	34053
115°	4432	12302	27696
120°	4473	9745	21377
125°	4481	8216	16318
130°	4428	7218	12753
135°	4374	6480	10300
140°	4360	5943	8550
145°	4379	5522	7225
150°	4427	5198	6272
155°	4463	4951	5616
160°	4505	4783	5177
165°	4533	4668	4886
170°	4549	4586	4704
175°	4556	4534	4585



TEST NUMBER: P519727

CATALOG NUMBER: SQ4-100U-0D-930-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	691.1	7.2
100°-110°	1907.8	19.9
110°-120°	1967.5	20.5
120°-130°	1581.1	16.5
130°-140°	1242.6	13.0
140°-150°	953.0	9.9
150°-160°	684.9	7.1
160°-170°	418.9	4.4
170°-180°	141.2	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	4566.4	47.6
90°-150°	8343.0	87.0
90°-180°	9588.0	100.0
0°-180°	9588.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	5	9	19	21	24	
95°	102	374	1254	515	335	115
105°	340	525	2099	3204	3017	362
115°	609	736	1690	3347	3806	599
125°	836	951	1532	2593	3043	744
135°	1006	1114	1490	2100	2368	778
145°	1166	1247	1471	1788	1924	730
155°	1315	1359	1459	1604	1655	606
165°	1424	1442	1466	1523	1535	401
175°	1476	1478	1469	1490	1485	140
180°	1476	1476	1476	1476	1476	



TEST NUMBER: P519727

CATALOG NUMBER: SQ4-100U-0D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	4.7	9.3	18.9	21.3	23.6
92.5°	42.5	176.4	315.4	115.1	89.7
95°	101.5	373.9	1253.7	515.3	335.3
97.5°	168.1	418.8	1857.2	1429.9	1035.6
100°	217.2	445.8	2080.1	2094.8	1702.3
102.5°	264.4	476.4	2123.5	2588.2	2216.1
105°	340.0	524.7	2099.0	3204.4	3017.4
107.5°	420.3	584.6	1981.9	3501.6	3569.9
110°	476.9	624.7	1891.2	3565.5	3787.1
112.5°	527.9	670.1	1806.2	3515.0	3841.9
115°	609.1	736.1	1690.5	3346.6	3806.0
117.5°	680.0	806.5	1614.5	3109.6	3632.2
120°	727.2	851.9	1584.3	2949.1	3475.5
122.5°	772.5	891.7	1559.7	2799.3	3297.9
125°	835.8	951.2	1532.3	2593.2	3043.4
127.5°	889.6	1005.1	1516.3	2419.0	2807.3
130°	925.5	1041.0	1508.7	2312.4	2665.6
132.5°	959.5	1069.4	1501.2	2222.9	2542.8
135°	1005.8	1114.3	1489.8	2100.3	2368.1
137.5°	1057.7	1156.6	1484.2	1997.4	2226.0
140°	1086.1	1183.0	1480.4	1928.8	2129.7
142.5°	1118.2	1207.8	1476.6	1867.8	2044.7
145°	1166.4	1247.2	1470.9	1788.0	1924.3
147.5°	1212.6	1283.3	1465.7	1720.8	1826.5
150°	1246.6	1304.3	1463.8	1680.6	1766.1
152.5°	1273.1	1327.1	1462.0	1646.3	1717.0
155°	1315.1	1359.0	1459.1	1604.3	1655.1
157.5°	1353.8	1387.5	1459.6	1573.7	1608.3
160°	1376.5	1406.5	1461.5	1556.5	1581.9
162.5°	1395.4	1421.7	1463.4	1541.3	1561.1
165°	1423.7	1442.2	1466.2	1523.1	1534.7
167.5°	1445.4	1456.5	1468.6	1512.1	1515.8
170°	1456.8	1466.0	1468.6	1506.3	1506.3
172.5°	1466.2	1471.7	1468.6	1498.7	1496.9
175°	1475.7	1478.0	1468.6	1489.7	1485.1
177.5°	1479.4	1477.6	1468.1	1481.2	1477.5
180°	1475.7	1475.7	1475.7	1475.7	1475.7

(END OF REPORT)