

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564391

Luminaire Tested: **SQ4-PR1-125U-100D-930-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564391
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-125U-100D-930-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10499.2 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 102.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564391
CATALOG NUMBER: SQ4-PR1-125U-100D-930-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P564391

CATALOG NUMBER: SQ4-PR1-125U-100D-930-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50	43	43	43
1	96	92	89	85	88	85	81	78	70	68	66	57	55	54	44	43	43	37	37	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	39	38	36	31	31	31
3	80	71	64	59	73	65	59	54	55	50	46	44	41	39	35	33	31	27	27	27
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	31	29	27	23	23	23
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	28	26	24	20	20	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18	18	18
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	19	16	16	16
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17	14	14	14
9	50	38	30	25	45	35	28	24	30	25	21	25	21	18	20	17	15	13	13	13
10	46	35	27	23	42	32	26	21	27	22	19	23	19	16	19	16	14	12	12	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11145	11145	11145
5°	11245	11159	11101
10°	11210	11132	11074
15°	11161	11091	11032
20°	11105	11033	10951
25°	11026	10952	10825
30°	10907	10830	10675
35°	10747	10653	10500
40°	10502	10388	10200
45°	10073	9897	9693
50°	9319	9095	8915
55°	8134	7949	7782
60°	6854	6797	6663
65°	5928	5951	5906
70°	5445	5472	5472
75°	5231	5231	5266
80°	4920	4977	4920
85°	3966	4404	4404



TEST NUMBER: P564391

CATALOG NUMBER: SQ4-PR1-125U-100D-930-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.4	1.6
10°-20°	490.2	4.7
20°-30°	739.5	7.0
30°-40°	881.1	8.4
40°-50°	868.6	8.3
50°-60°	663.9	6.3
60°-70°	410.8	3.9
70°-80°	233.3	2.2
80°-90°	73.1	0.7
90°-100°	432.4	4.1
100°-110°	1164.8	11.1
110°-120°	1222.5	11.6
120°-130°	992.0	9.4
130°-140°	778.0	7.4
140°-150°	597.3	5.7
150°-160°	429.5	4.1
160°-170°	262.4	2.5
170°-180°	88.5	0.8
0°-30°	1401.1	13.3
0°-40°	2282.1	21.7
0°-60°	3814.6	36.3
0°-90°	4531.9	43.2
90°-120°	2819.7	26.9
90°-150°	5187.0	49.4
90°-180°	5967.0	56.8
0°-180°	10499.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1812	1812	1812	1812	1812	
5°	1821	1802	1807	1801	1798	173
15°	1753	1734	1742	1735	1732	495
25°	1625	1605	1614	1597	1595	748
35°	1431	1414	1419	1400	1398	893
45°	1158	1143	1138	1117	1114	887
55°	758	746	741	729	726	680
65°	407	404	409	406	406	413
75°	220	220	220	222	222	232
85°	56	59	62	62	62	65
90°	2	7	14	15	15	7
95°	66	235	709	362	251	69
105°	216	335	1288	1927	1809	227
115°	380	466	1073	2073	2344	374
125°	519	596	963	1628	1916	464
135°	625	698	936	1313	1487	483
145°	723	779	924	1123	1206	453
155°	821	851	916	1008	1040	378
165°	890	901	920	956	961	251
175°	926	924	921	934	931	88
180°	924	924	924	924	924	

TEST NUMBER: P564391

CATALOG NUMBER: SQ4-PR1-125U-100D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1812.0	1812.0	1812.0	1812.0	1812.0
2.5°	1823.2	1807.3	1812.0	1808.0	1799.5
5°	1821.3	1801.5	1807.3	1801.0	1797.9
7.5°	1807.3	1787.8	1793.6	1787.3	1785.4
10°	1794.8	1776.5	1782.3	1776.0	1773.0
12.5°	1781.1	1761.5	1768.6	1761.0	1758.0
15°	1752.7	1734.4	1741.7	1735.4	1732.4
17.5°	1721.5	1701.9	1709.3	1702.0	1698.0
20°	1696.5	1678.2	1685.6	1674.6	1673.1
22.5°	1669.0	1650.7	1658.1	1643.4	1643.1
25°	1624.7	1604.9	1613.8	1596.6	1595.0
27.5°	1571.9	1553.6	1561.0	1543.5	1541.7
30°	1535.7	1517.4	1524.8	1506.0	1503.0
32.5°	1494.5	1477.4	1483.6	1464.8	1463.0
35°	1431.2	1414.4	1418.7	1399.9	1398.4
37.5°	1359.1	1343.8	1346.3	1325.6	1324.1
40°	1307.9	1292.6	1293.8	1271.9	1270.4
42.5°	1251.7	1236.4	1235.1	1213.3	1211.7
45°	1158.0	1142.8	1137.8	1117.4	1114.3
47.5°	1051.3	1036.0	1026.6	1010.0	1007.9
50°	973.9	958.6	950.5	936.3	931.7
52.5°	890.2	875.0	868.1	855.2	850.6
55°	758.5	746.3	741.3	728.8	725.7
57.5°	633.3	625.1	623.7	611.5	610.2
60°	557.2	552.6	552.5	541.6	541.6
62.5°	492.2	488.9	491.3	484.1	482.9
65°	407.3	404.3	408.9	405.8	405.8
67.5°	340.2	340.2	343.0	341.8	341.8
70°	302.8	302.8	304.3	304.3	304.3
72.5°	269.1	267.8	271.9	271.8	270.6
75°	220.1	220.1	220.1	221.6	221.6
77.5°	171.4	171.7	172.9	172.6	171.4
80°	138.9	140.4	140.5	138.9	138.9
82.5°	106.4	108.0	108.0	107.7	106.4
85°	56.2	59.2	62.4	62.4	62.4
87.5°	16.7	22.5	27.8	28.0	26.8
90°	2.4	7.0	14.1	15.3	15.3
92.5°	28.7	101.5	200.7	96.6	67.1
95°	65.9	235.2	708.9	362.5	250.8
97.5°	105.3	269.2	1111.8	928.8	700.4
100°	135.4	282.8	1240.0	1297.3	1076.3
102.5°	164.6	301.9	1282.3	1573.3	1391.9
105°	215.5	335.2	1288.2	1927.3	1808.7
107.5°	263.5	370.4	1233.4	2109.2	2139.8
110°	295.6	396.9	1183.4	2165.7	2277.4



TEST NUMBER: P564391

CATALOG NUMBER: SQ4-PR1-125U-100D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	329.5	423.4	1135.4	2153.2	2336.7
115°	380.3	465.5	1072.7	2072.8	2344.5
117.5°	426.7	506.6	1024.2	1944.4	2247.0
120°	456.9	534.0	999.7	1852.3	2163.1
122.5°	483.3	559.5	981.8	1758.0	2068.0
125°	519.3	596.4	963.2	1628.0	1915.9
127.5°	553.9	629.9	951.5	1513.3	1770.3
130°	574.6	650.6	946.7	1447.6	1673.3
132.5°	595.4	670.4	942.0	1389.7	1597.0
135°	625.3	697.8	936.1	1313.4	1487.2
137.5°	653.8	723.3	933.1	1248.6	1391.4
140°	673.6	740.3	930.3	1208.7	1337.7
142.5°	694.3	756.5	928.4	1171.5	1280.2
145°	723.0	779.4	924.4	1122.9	1205.8
147.5°	754.1	803.1	920.4	1082.0	1147.2
150°	774.8	817.4	918.5	1056.3	1110.4
152.5°	793.7	830.7	917.5	1035.4	1079.3
155°	820.7	850.7	916.1	1007.5	1039.8
157.5°	844.5	867.8	916.4	988.0	1009.6
160°	859.6	879.2	917.3	976.5	992.7
162.5°	872.8	888.7	918.2	967.0	978.5
165°	890.2	900.6	919.7	956.3	960.9
167.5°	904.4	910.3	920.8	948.0	949.8
170°	913.8	916.1	920.8	943.2	943.2
172.5°	919.4	919.9	921.8	938.5	938.5
175°	925.5	924.4	920.8	933.7	931.4
177.5°	928.1	926.3	921.5	929.0	927.2
180°	924.4	924.4	924.4	924.4	924.4

(END OF REPORT)