

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519751

Luminaire Tested: **SQ4-125U-0D-930-1D-UNV-STD-W-12**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519751
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-125U-0D-930-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11934.7 lumens
Efficiency: N/A
Efficacy: 128.3 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Indirect

Input Watts (W): 93
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519751
CATALOG NUMBER: SQ4-125U-0D-930-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P519751

CATALOG NUMBER: SQ4-125U-0D-930-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20				20
RC	80								50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10				0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10				0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8				0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7				0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6				0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5				0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4				0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4				0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3				0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3				0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3				0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2				0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	4654	50029	17700
100°	4796	43920	38122
105°	5121	30615	42984
110°	5315	21283	40955
115°	5536	15613	34122
120°	5621	12299	26610
125°	5569	10330	20545
130°	5499	9059	16012
135°	5439	8143	12937
140°	5408	7469	10741
145°	5429	6941	9054
150°	5503	6523	7886
155°	5570	6218	7056
160°	5627	6004	6497
165°	5669	5856	6118
170°	5707	5751	5891
175°	5715	5686	5751



TEST NUMBER: P519751

CATALOG NUMBER: SQ4-125U-0D-930-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	864.9	7.2
100°-110°	2329.7	19.5
110°-120°	2444.9	20.5
120°-130°	1984.0	16.6
130°-140°	1556.0	13.0
140°-150°	1194.6	10.0
150°-160°	858.9	7.2
160°-170°	524.8	4.4
170°-180°	177.0	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	5639.5	47.3
90°-150°	10374.1	86.9
90°-180°	11935.0	100.0
0°-180°	11934.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	5	14	28	31	31	
95°	132	470	1418	725	502	146
105°	431	670	2576	3855	3617	453
115°	761	931	2146	4146	4689	749
125°	1039	1193	1926	3256	3832	927
135°	1251	1396	1872	2627	2974	965
145°	1446	1559	1849	2246	2412	907
155°	1642	1701	1832	2015	2080	756
165°	1780	1801	1839	1912	1922	502
175°	1851	1849	1842	1868	1863	176
180°	1849	1849	1849	1849	1849	



TEST NUMBER: P519751

CATALOG NUMBER: SQ4-125U-0D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	4.7	13.9	28.3	30.6	30.6
92.5°	57.5	203.0	401.3	193.2	134.2
95°	131.9	470.4	1417.8	725.0	501.6
97.5°	210.5	538.5	2223.7	1857.7	1400.8
100°	270.8	565.6	2479.9	2594.7	2152.5
102.5°	329.2	603.7	2564.7	3146.6	2783.7
105°	431.0	670.5	2576.5	3854.6	3617.4
107.5°	527.1	740.8	2466.7	4218.4	4279.7
110°	591.1	793.8	2366.9	4331.4	4554.7
112.5°	659.0	846.9	2270.8	4306.4	4673.4
115°	760.7	931.1	2145.5	4145.5	4689.0
117.5°	853.5	1013.3	2048.5	3888.8	4494.0
120°	913.8	1068.1	1999.5	3704.5	4326.3
122.5°	966.5	1119.0	1963.7	3516.1	4136.0
125°	1038.6	1192.9	1926.5	3256.0	3831.7
127.5°	1107.8	1259.8	1902.9	3026.7	3540.6
130°	1149.3	1301.3	1893.5	2895.2	3346.6
132.5°	1190.7	1340.9	1884.1	2779.5	3194.0
135°	1250.6	1395.6	1872.3	2626.8	2974.5
137.5°	1307.5	1446.6	1866.2	2497.2	2782.8
140°	1347.1	1480.7	1860.5	2417.5	2675.4
142.5°	1388.6	1512.9	1856.7	2343.1	2560.4
145°	1446.0	1558.9	1848.7	2245.8	2411.6
147.5°	1508.2	1606.3	1840.7	2164.0	2294.3
150°	1549.6	1634.8	1837.0	2112.6	2220.8
152.5°	1587.3	1661.5	1835.1	2070.7	2158.7
155°	1641.5	1701.4	1832.3	2015.1	2079.5
157.5°	1689.1	1735.6	1832.7	1976.0	2019.2
160°	1719.2	1758.4	1834.6	1953.1	1985.3
162.5°	1745.6	1777.4	1836.5	1934.0	1957.1
165°	1780.4	1801.2	1839.3	1912.5	1921.7
167.5°	1808.7	1820.7	1841.7	1895.9	1899.6
170°	1827.5	1832.2	1841.7	1886.4	1886.4
172.5°	1838.9	1839.8	1843.6	1877.0	1877.0
175°	1851.1	1848.8	1841.7	1867.5	1862.9
177.5°	1856.3	1852.6	1843.1	1858.1	1854.4
180°	1848.7	1848.7	1848.7	1848.7	1848.7

(END OF REPORT)