

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564511

Luminaire Tested: **SQ4-PR1-150U-125D-930-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564511
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-150U-125D-930-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12973.3 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 127.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564511
CATALOG NUMBER: SQ4-PR1-150U-125D-930-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P564511

CATALOG NUMBER: SQ4-PR1-150U-125D-930-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45				
1	97	93	89	85	89	85	82	79	71	68	66	58	56	55	46	45	44	38				
2	88	81	75	70	81	75	69	65	62	59	55	51	48	46	40	39	37	32				
3	81	72	64	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28				
4	74	63	56	50	68	58	52	47	49	44	40	40	37	34	32	30	28	24				
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	29	26	24	21				
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	21	18				
7	58	46	38	33	53	42	35	31	36	31	27	30	26	23	24	21	19	16				
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	22	19	17	15				
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	15	13				
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14222	14222	14222
5°	14351	14240	14166
10°	14305	14206	14131
15°	14242	14154	14077
20°	14170	14079	13975
25°	14071	13976	13814
30°	13919	13820	13622
35°	13714	13594	13399
40°	13401	13257	13017
45°	12855	12629	12369
50°	11892	11606	11377
55°	10379	10145	9931
60°	8746	8673	8502
65°	7565	7594	7536
70°	6949	6985	6985
75°	6673	6673	6721
80°	6280	6347	6280
85°	5060	5625	5625



TEST NUMBER: P564511

CATALOG NUMBER: SQ4-PR1-150U-125D-930-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	218.7	1.7
10°-20°	625.6	4.8
20°-30°	943.6	7.3
30°-40°	1124.3	8.7
40°-50°	1108.5	8.5
50°-60°	847.2	6.5
60°-70°	524.3	4.0
70°-80°	297.8	2.3
80°-90°	92.9	0.7
90°-100°	518.3	4.0
100°-110°	1401.4	10.8
110°-120°	1473.3	11.4
120°-130°	1196.7	9.2
130°-140°	938.7	7.2
140°-150°	720.5	5.6
150°-160°	518.2	4.0
160°-170°	316.5	2.4
170°-180°	106.7	0.8
0°-30°	1787.9	13.8
0°-40°	2912.3	22.4
0°-60°	4867.9	37.5
0°-90°	5782.9	44.6
90°-120°	3393.0	26.2
90°-150°	6249.0	48.2
90°-180°	7190.0	55.4
0°-180°	12973.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2312	2312	2312	2312	2312	
5°	2324	2299	2306	2298	2294	221
15°	2237	2213	2223	2215	2211	631
25°	2073	2048	2059	2037	2036	954
35°	1826	1805	1810	1786	1784	1140
45°	1478	1458	1452	1426	1422	1132
55°	968	952	946	930	926	867
65°	520	516	522	518	518	527
75°	281	281	281	283	283	297
85°	72	76	80	80	80	83
90°	2	7	16	17	16	8
95°	80	282	862	446	265	84
105°	260	402	1555	2293	2199	274
115°	459	561	1289	2496	2818	453
125°	628	719	1162	1961	2304	560
135°	753	842	1131	1583	1792	582
145°	875	941	1115	1355	1459	547
155°	988	1027	1106	1216	1256	456
165°	1076	1086	1110	1154	1160	303
175°	1116	1115	1112	1126	1124	106
180°	1115	1115	1115	1115	1115	

TEST NUMBER: P564511

CATALOG NUMBER: SQ4-PR1-150U-125D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2312.3	2312.3	2312.3	2312.3	2312.3
2.5°	2326.7	2306.4	2312.3	2307.3	2296.4
5°	2324.3	2299.0	2306.3	2298.3	2294.4
7.5°	2306.3	2281.4	2288.8	2280.8	2278.5
10°	2290.4	2267.0	2274.5	2266.4	2262.5
12.5°	2272.9	2248.0	2257.0	2247.3	2243.4
15°	2236.6	2213.3	2222.7	2214.6	2210.7
17.5°	2196.8	2171.9	2181.3	2172.0	2166.9
20°	2164.9	2141.6	2151.0	2137.0	2135.1
22.5°	2129.9	2106.5	2115.9	2097.2	2096.8
25°	2073.3	2048.0	2059.4	2037.4	2035.5
27.5°	2006.0	1982.6	1992.1	1969.7	1967.4
30°	1959.8	1936.4	1945.9	1921.9	1918.0
32.5°	1907.2	1885.4	1893.3	1869.3	1867.0
35°	1826.4	1804.9	1810.4	1786.5	1784.5
37.5°	1734.3	1714.9	1718.0	1691.7	1689.7
40°	1669.0	1649.5	1651.1	1623.2	1621.2
42.5°	1597.3	1577.8	1576.2	1548.3	1546.3
45°	1477.8	1458.3	1451.9	1425.9	1422.0
47.5°	1341.6	1322.1	1310.1	1288.9	1286.2
50°	1242.8	1223.3	1212.9	1194.9	1189.0
52.5°	1136.0	1116.6	1107.8	1091.3	1085.5
55°	967.9	952.4	946.0	930.0	926.1
57.5°	808.2	797.7	795.9	780.3	778.7
60°	711.0	705.2	705.0	691.1	691.1
62.5°	628.2	623.9	627.0	617.8	616.2
65°	519.8	515.9	521.8	517.8	517.8
67.5°	434.2	434.2	437.8	436.2	436.2
70°	386.4	386.4	388.4	388.4	388.4
72.5°	343.4	341.8	346.9	346.9	345.4
75°	280.8	280.8	280.8	282.8	282.8
77.5°	218.7	219.1	220.7	220.2	218.7
80°	177.3	179.2	179.2	177.3	177.3
82.5°	135.8	137.8	137.8	137.4	135.8
85°	71.7	75.6	79.7	79.7	79.7
87.5°	21.2	28.4	35.0	35.2	33.4
90°	2.4	7.1	15.6	16.8	15.6
92.5°	34.1	124.2	245.1	106.4	77.1
95°	80.4	282.3	861.9	446.1	265.3
97.5°	129.2	323.8	1343.6	1111.9	816.6
100°	165.7	340.6	1493.4	1557.4	1259.3
102.5°	199.3	363.8	1546.2	1895.3	1672.3
105°	260.5	402.5	1554.6	2293.2	2199.3
107.5°	317.2	446.8	1486.7	2541.4	2572.6
110°	361.3	478.7	1426.2	2608.0	2740.7



TEST NUMBER: P564511

CATALOG NUMBER: SQ4-PR1-150U-125D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	400.7	510.6	1370.5	2594.7	2817.5
115°	458.6	560.7	1289.3	2495.9	2817.5
117.5°	515.2	611.0	1235.8	2344.9	2709.5
120°	549.8	643.7	1204.1	2236.5	2608.6
122.5°	582.5	674.5	1184.9	2120.4	2495.3
125°	627.8	719.4	1162.1	1961.0	2303.7
127.5°	669.6	759.5	1148.6	1830.9	2132.3
130°	692.7	785.4	1142.9	1750.5	2022.8
132.5°	716.7	808.5	1137.1	1678.0	1928.7
135°	752.7	841.9	1130.8	1583.4	1792.3
137.5°	789.0	873.2	1125.6	1506.6	1676.8
140°	813.9	892.6	1123.6	1457.2	1608.6
142.5°	837.9	911.9	1119.8	1412.6	1545.3
145°	875.1	940.9	1115.2	1355.3	1458.6
147.5°	909.0	967.2	1110.0	1303.4	1382.7
150°	934.0	985.6	1108.0	1275.1	1338.5
152.5°	957.0	1002.1	1107.1	1249.0	1301.1
155°	988.0	1026.7	1105.6	1215.8	1255.7
157.5°	1020.2	1047.2	1105.9	1192.7	1219.0
160°	1038.4	1060.7	1106.8	1178.1	1196.9
162.5°	1052.8	1071.4	1107.8	1166.5	1180.5
165°	1075.6	1086.2	1110.4	1153.8	1159.7
167.5°	1091.2	1098.5	1110.7	1142.9	1145.7
170°	1100.8	1104.4	1111.6	1138.1	1138.1
172.5°	1108.5	1109.2	1111.6	1132.3	1131.3
175°	1116.4	1115.3	1111.6	1126.0	1123.6
177.5°	1119.1	1116.3	1111.4	1120.9	1118.1
180°	1115.2	1115.2	1115.2	1115.2	1115.2

(END OF REPORT)