

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564559

Luminaire Tested: **SQ4-PW1-025U-075D-930-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564559
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-025U-075D-930-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4545.9 lumens
Efficiency: N/A
Efficacy: 93.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 48.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564559
CATALOG NUMBER: SQ4-PW1-025U-075D-930-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P564559

CATALOG NUMBER: SQ4-PW1-025U-075D-930-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	79	79	79	75
1	103	99	95	91	98	94	91	88	86	83	80	77	75	73	70	68	67	63
2	94	87	80	75	89	83	77	72	75	71	67	68	65	62	62	59	57	53
3	86	76	69	63	82	73	66	60	66	61	56	60	56	52	55	51	48	45
4	79	68	59	53	75	65	57	51	59	53	48	54	49	45	49	45	42	39
5	73	61	52	46	69	58	50	44	53	47	42	48	43	39	44	40	36	34
6	67	54	46	40	64	52	44	39	48	41	37	44	38	34	40	36	32	30
7	62	49	41	35	59	47	40	34	44	37	32	40	35	30	37	32	29	26
8	58	45	37	31	55	43	36	31	40	33	29	37	31	27	34	29	26	23
9	54	41	33	28	51	40	32	27	37	30	26	34	28	25	31	27	23	21
10	50	38	30	25	48	37	30	25	34	28	24	31	26	22	29	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8200	8200	8200
5°	8253	8188	8152
10°	8187	8121	8077
15°	8100	8011	7981
20°	8004	7881	7865
25°	7892	7748	7725
30°	7725	7608	7558
35°	7506	7400	7356
40°	7271	7158	7130
45°	6988	6897	6866
50°	6699	6643	6598
55°	6386	6386	6285
60°	5997	6113	5895
65°	5487	5760	5352
70°	4838	5302	4710
75°	4130	4746	4019
80°	3202	3995	3245
85°	2075	3070	2738



TEST NUMBER: P564559

CATALOG NUMBER: SQ4-PW1-025U-075D-930-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.5	2.8
10°-20°	354.4	7.8
20°-30°	525.7	11.6
30°-40°	615.2	13.5
40°-50°	612.4	13.5
50°-60°	528.8	11.6
60°-70°	380.7	8.4
70°-80°	199.6	4.4
80°-90°	50.5	1.1
90°-100°	86.7	1.9
100°-110°	227.9	5.0
110°-120°	236.3	5.2
120°-130°	189.6	4.2
130°-140°	148.7	3.3
140°-150°	114.2	2.5
150°-160°	82.2	1.8
160°-170°	50.3	1.1
170°-180°	17.0	0.4
0°-30°	1005.7	22.1
0°-40°	1620.9	35.7
0°-60°	2762.2	60.8
0°-90°	3392.9	74.6
90°-120°	551.0	12.1
90°-150°	1003.4	22.1
90°-180°	1153.0	25.4
0°-180°	4545.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1333	1333	1333	1333	1333	
5°	1337	1322	1326	1323	1320	127
15°	1272	1256	1258	1256	1253	359
25°	1163	1143	1142	1135	1138	535
35°	1000	986	986	976	980	625
45°	803	796	793	790	789	620
55°	596	594	596	587	586	531
65°	377	388	396	380	368	374
75°	174	190	200	186	169	186
85°	29	39	44	41	39	39
90°	1	3	9	5	5	2
95°	11	45	149	77	52	13
105°	41	62	252	382	357	43
115°	73	89	202	403	460	72
125°	102	114	184	310	366	90
135°	121	133	178	250	284	94
145°	140	149	176	214	230	88
155°	158	163	176	193	198	73
165°	171	173	176	182	185	48
175°	178	178	177	179	179	17
180°	178	178	178	178	178	

TEST NUMBER: P564559

CATALOG NUMBER: SQ4-PW1-025U-075D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1333.2	1333.2	1333.2	1333.2	1333.2
2.5°	1340.7	1329.7	1333.2	1330.2	1323.8
5°	1336.7	1321.8	1326.1	1322.6	1320.3
7.5°	1323.1	1309.3	1312.5	1308.7	1307.3
10°	1310.9	1297.1	1300.3	1295.5	1293.2
12.5°	1296.8	1282.1	1285.3	1280.5	1279.1
15°	1272.1	1256.0	1258.0	1255.6	1253.3
17.5°	1243.4	1227.1	1227.5	1223.7	1223.2
20°	1222.8	1205.5	1204.0	1199.3	1201.6
22.5°	1200.2	1182.1	1180.5	1174.0	1177.2
25°	1162.9	1143.3	1141.7	1134.8	1138.2
27.5°	1119.6	1100.3	1100.4	1090.6	1094.3
30°	1087.7	1069.3	1071.2	1059.6	1064.2
32.5°	1053.9	1037.3	1038.4	1026.7	1031.3
35°	999.6	985.8	985.5	976.2	979.6
37.5°	944.2	932.0	930.1	924.7	925.6
40°	905.6	895.3	891.5	888.0	888.0
42.5°	865.2	855.8	852.1	849.5	848.5
45°	803.4	796.5	792.9	790.5	789.3
47.5°	742.4	735.9	732.7	731.1	729.9
50°	700.1	695.5	694.2	690.6	689.5
52.5°	657.8	655.0	653.8	649.3	648.1
55°	595.5	594.4	595.5	587.3	586.1
57.5°	530.7	532.5	536.3	525.2	522.5
60°	487.5	492.1	496.9	483.8	479.2
62.5°	443.3	450.6	457.4	442.4	436.0
65°	377.0	388.5	395.8	380.3	367.7
67.5°	313.2	327.4	336.2	319.4	305.2
70°	269.0	285.1	294.8	278.0	261.9
72.5°	230.5	248.4	256.3	240.4	224.4
75°	173.8	189.9	199.7	186.4	169.1
77.5°	123.3	138.5	146.6	135.0	120.7
80°	90.4	106.5	112.8	103.1	91.6
82.5°	64.1	77.5	81.8	75.9	68.1
85°	29.4	38.6	43.5	41.1	38.8
87.5°	7.7	14.6	19.7	18.8	19.7
90°	1.1	3.4	9.1	4.6	4.6
92.5°	4.8	23.1	51.1	22.6	14.6
95°	11.4	44.9	149.4	77.0	52.5
97.5°	19.8	49.3	223.5	177.7	130.9
100°	26.2	53.0	246.3	249.6	193.8
102.5°	31.7	56.7	252.7	310.9	263.2
105°	41.0	62.2	252.0	382.5	356.9
107.5°	50.6	70.3	237.6	419.8	426.0
110°	57.0	74.9	225.8	429.3	456.1

TEST NUMBER: P564559

CATALOG NUMBER: SQ4-PW1-025U-075D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	63.4	80.3	214.8	423.3	464.3
115°	73.0	88.6	201.8	402.7	459.5
117.5°	82.3	96.6	192.9	374.1	437.2
120°	87.8	101.2	189.3	354.9	416.2
122.5°	93.3	106.7	186.5	335.7	396.1
125°	101.5	113.7	183.6	310.3	366.0
127.5°	108.1	120.6	181.1	289.8	336.8
130°	111.7	125.1	180.2	276.9	320.4
132.5°	115.4	128.8	179.2	265.9	304.9
135°	120.9	133.1	177.9	250.5	283.9
137.5°	126.6	138.6	177.7	238.9	266.4
140°	131.1	142.3	176.7	229.8	255.4
142.5°	134.8	145.0	176.7	223.3	245.4
145°	140.3	149.2	175.6	213.6	230.3
147.5°	145.7	154.4	175.6	205.6	219.4
150°	149.4	157.2	175.6	200.9	212.1
152.5°	153.0	159.0	175.6	197.2	205.7
155°	158.5	163.0	175.6	192.8	198.4
157.5°	162.6	166.8	175.6	188.9	192.9
160°	165.3	168.7	175.6	187.1	189.3
162.5°	168.1	170.5	175.6	185.2	187.5
165°	171.0	173.3	175.6	182.5	184.7
167.5°	173.8	174.9	176.7	181.3	182.2
170°	175.6	176.7	176.7	181.3	181.3
172.5°	176.5	176.7	176.7	180.4	179.5
175°	177.9	177.9	176.7	179.0	179.0
177.5°	177.9	177.9	177.0	178.8	177.9
180°	177.9	177.9	177.9	177.9	177.9

(END OF REPORT)