

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564631

Luminaire Tested: **SQ4-PW1-050U-050D-930-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P564631  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PW1-050U-050D-930-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4680.4 lumens  
Efficiency: N/A  
Efficacy: 104.5 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 44.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P564631  
CATALOG NUMBER: SQ4-PW1-050U-050D-930-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P564631

CATALOG NUMBER: SQ4-PW1-050U-050D-930-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49						
1	98	93	90	86	90	86	83	80	73	70	68	60	59	57	49	48	47	42						
2	89	82	76	70	82	75	70	66	64	60	57	53	50	48	43	41	40	35						
3	81	72	65	59	75	66	60	55	56	52	48	47	44	41	38	36	34	30						
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	32	29	26						
5	68	57	49	43	63	53	45	40	45	39	35	38	33	30	31	28	25	22						
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22	19						
7	58	46	38	32	53	43	36	31	37	31	27	31	27	23	26	22	20	17						
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18	15						
9	50	38	31	26	46	35	29	24	31	25	21	26	22	19	22	19	16	14						
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13						

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5563	5563	5563
5°	5599	5556	5531
10°	5555	5510	5480
15°	5496	5435	5415
20°	5430	5347	5337
25°	5355	5257	5241
30°	5242	5162	5128
35°	5092	5020	4991
40°	4933	4857	4838
45°	4742	4679	4658
50°	4545	4507	4476
55°	4333	4333	4265
60°	4068	4147	4000
65°	3723	3909	3630
70°	3282	3597	3196
75°	2802	3220	2728
80°	2175	2710	2203
85°	1404	2082	1856



TEST NUMBER: P564631

CATALOG NUMBER: SQ4-PW1-050U-050D-930-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	85.2	1.8
10°-20°	240.5	5.1
20°-30°	356.7	7.6
30°-40°	417.4	8.9
40°-50°	415.5	8.9
50°-60°	358.8	7.7
60°-70°	258.3	5.5
70°-80°	135.4	2.9
80°-90°	35.0	0.7
90°-100°	174.8	3.7
100°-110°	474.9	10.1
110°-120°	488.2	10.4
120°-130°	390.4	8.3
130°-140°	306.7	6.6
140°-150°	235.2	5.0
150°-160°	169.1	3.6
160°-170°	103.4	2.2
170°-180°	34.8	0.7
0°-30°	682.4	14.6
0°-40°	1099.7	23.5
0°-60°	1874.1	40.0
0°-90°	2302.8	49.2
90°-120°	1137.9	24.3
90°-150°	2070.2	44.2
90°-180°	2378.0	50.8
0°-180°	4680.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	904	904	904	904	904	
5°	907	897	900	897	896	86
15°	863	852	854	852	850	243
25°	789	776	775	770	772	363
35°	678	669	669	662	665	424
45°	545	540	538	536	536	421
55°	404	403	404	398	398	361
65°	256	264	269	258	249	254
75°	118	129	136	126	115	126
85°	20	26	30	28	26	26
90°	1	5	8	10	10	2
95°	26	96	304	132	89	27
105°	84	131	522	795	748	90
115°	150	182	418	832	947	148
125°	206	235	378	637	752	184
135°	248	276	368	519	585	192
145°	287	308	363	441	474	180
155°	324	336	361	396	408	150
165°	351	356	362	377	378	99
175°	364	365	363	368	366	35
180°	364	364	364	364	364	



TEST NUMBER: P564631

CATALOG NUMBER: SQ4-PW1-050U-050D-930-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	904.5	904.5	904.5	904.5	904.5
2.5°	909.6	902.2	904.5	902.5	898.2
5°	906.9	896.8	899.8	897.3	895.8
7.5°	897.7	888.3	890.5	887.9	887.0
10°	889.4	880.0	882.2	879.0	877.4
12.5°	879.8	869.9	872.0	868.8	867.9
15°	863.1	852.2	853.5	851.9	850.3
17.5°	843.6	832.6	832.8	830.3	829.9
20°	829.6	817.9	816.9	813.7	815.3
22.5°	814.3	802.0	800.9	796.5	798.7
25°	789.0	775.7	774.6	769.9	772.2
27.5°	759.7	746.6	746.6	739.9	742.4
30°	738.0	725.5	726.8	718.9	722.0
32.5°	715.0	703.8	704.5	696.6	699.7
35°	678.2	668.9	668.6	662.3	664.7
37.5°	640.6	632.3	631.0	627.4	628.0
40°	614.4	607.4	604.9	602.5	602.5
42.5°	587.0	580.6	578.1	576.3	575.7
45°	545.1	540.4	537.9	536.3	535.5
47.5°	503.7	499.3	497.1	496.0	495.2
50°	475.0	471.9	471.0	468.6	467.8
52.5°	446.3	444.4	443.6	440.5	439.8
55°	404.1	403.3	404.1	398.5	397.7
57.5°	360.1	361.3	363.9	356.4	354.5
60°	330.7	333.9	337.1	328.3	325.2
62.5°	300.8	305.8	310.3	300.2	295.8
65°	255.8	263.6	268.6	258.0	249.4
67.5°	212.5	222.1	228.1	216.7	207.0
70°	182.5	193.4	200.0	188.6	177.7
72.5°	156.4	168.5	173.9	163.1	152.2
75°	117.9	128.9	135.5	126.4	114.8
77.5°	83.7	94.0	99.5	91.6	81.9
80°	61.4	72.3	76.5	70.0	62.2
82.5°	43.5	52.6	55.5	51.5	46.2
85°	19.9	26.2	29.5	27.9	26.3
87.5°	5.3	10.4	13.8	14.2	14.9
90°	1.2	4.6	8.2	10.5	10.5
92.5°	10.5	47.9	83.1	35.7	30.2
95°	25.8	95.6	304.4	132.5	89.0
97.5°	42.6	105.6	466.7	363.1	255.0
100°	53.9	112.2	516.4	523.4	422.7
102.5°	65.1	118.9	529.5	647.4	558.5
105°	84.3	131.2	522.2	795.1	748.2
107.5°	104.2	145.7	492.0	871.4	884.5
110°	118.3	156.0	469.5	886.5	942.6



TEST NUMBER: P564631

CATALOG NUMBER: SQ4-PW1-050U-050D-930-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	130.4	166.4	447.0	874.0	958.5
115°	149.9	181.9	418.0	831.6	947.2
117.5°	168.1	198.8	399.5	771.5	901.8
120°	180.3	210.1	391.1	731.2	860.6
122.5°	190.6	220.4	385.5	690.9	815.6
125°	206.1	234.7	378.2	637.2	751.7
127.5°	219.9	248.3	374.2	596.6	694.8
130°	228.3	255.8	372.3	571.1	659.2
132.5°	236.8	264.2	370.5	549.3	627.4
135°	248.2	275.7	367.7	519.0	585.4
137.5°	260.6	285.6	366.3	492.3	548.2
140°	268.1	292.2	365.3	475.4	525.7
142.5°	275.6	297.8	364.4	462.1	504.2
145°	286.9	307.5	363.0	441.0	474.2
147.5°	299.5	317.1	361.8	424.5	450.6
150°	307.9	322.8	361.8	415.0	435.6
152.5°	314.5	327.6	360.9	406.4	423.4
155°	324.3	335.8	360.6	396.0	407.5
157.5°	333.9	342.9	360.6	388.9	397.6
160°	339.6	347.6	360.6	384.2	391.1
162.5°	345.2	351.4	361.6	380.4	385.5
165°	351.3	355.8	361.8	377.1	378.2
167.5°	357.6	359.9	363.0	373.1	374.0
170°	359.5	361.8	363.0	371.2	371.2
172.5°	361.3	362.7	363.0	369.3	369.3
175°	364.1	365.3	363.0	367.6	366.5
177.5°	365.1	365.1	362.3	366.0	364.1
180°	364.1	364.1	364.1	364.1	364.1

(END OF REPORT)