

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564823

Luminaire Tested: **SQ4-PW1-0U-050D-930-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564823
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-0U-050D-930-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2301.4 lumens
Efficiency: N/A
Efficacy: 86.2 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Direct

Input Watts (W): 26.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564823
CATALOG NUMBER: SQ4-PW1-0U-050D-930-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P564823

CATALOG NUMBER: SQ4-PW1-0U-050D-930-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	101	97	107	102	99	95	98	95	92	94	92	89	91	89	87	85
2	100	92	85	80	97	90	84	79	86	81	77	83	79	75	80	76	73	71
3	91	81	73	67	89	79	72	66	76	70	65	74	68	64	71	66	63	60
4	84	72	63	57	81	71	63	56	68	61	56	66	60	55	64	58	54	52
5	77	64	56	49	75	63	55	49	61	54	48	59	53	48	57	52	47	45
6	71	58	49	43	69	57	49	43	55	48	42	54	47	42	52	46	42	40
7	66	53	44	38	64	52	44	38	50	43	38	49	42	37	48	42	37	35
8	62	48	40	34	60	48	40	34	46	39	34	45	38	34	44	38	33	31
9	58	44	36	31	56	44	36	31	43	35	31	42	35	30	41	35	30	28
10	54	41	33	28	53	40	33	28	39	33	28	39	32	28	38	32	28	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5563	5563	5563
5°	5599	5556	5531
10°	5555	5510	5480
15°	5496	5435	5415
20°	5430	5347	5337
25°	5355	5257	5241
30°	5242	5162	5128
35°	5092	5020	4991
40°	4933	4857	4838
45°	4742	4679	4658
50°	4545	4507	4476
55°	4333	4333	4265
60°	4068	4147	4000
65°	3723	3909	3630
70°	3282	3597	3196
75°	2802	3220	2728
80°	2175	2710	2203
85°	1404	2082	1856



TEST NUMBER: P564823

CATALOG NUMBER: SQ4-PW1-0U-050D-930-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.2	3.7
10°-20°	240.5	10.4
20°-30°	356.7	15.5
30°-40°	417.4	18.1
40°-50°	415.5	18.1
50°-60°	358.8	15.6
60°-70°	258.3	11.2
70°-80°	135.4	5.9
80°-90°	33.6	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	682.4	29.6
0°-40°	1099.7	47.8
0°-60°	1874.1	81.4
0°-90°	2301.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2301.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	904	904	904	904	904	
5°	907	897	900	897	896	86
15°	863	852	854	852	850	243
25°	789	776	775	770	772	363
35°	678	669	669	662	665	424
45°	545	540	538	536	536	421
55°	404	403	404	398	398	361
65°	256	264	269	258	249	254
75°	118	129	136	126	115	126
85°	20	26	30	28	26	27
90°	0	0	0	0	0	



TEST NUMBER: P564823

CATALOG NUMBER: SQ4-PW1-0U-050D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	904.5	904.5	904.5	904.5	904.5
2.5°	909.6	902.2	904.5	902.5	898.2
5°	906.9	896.8	899.8	897.3	895.8
7.5°	897.7	888.3	890.5	887.9	887.0
10°	889.4	880.0	882.2	879.0	877.4
12.5°	879.8	869.9	872.0	868.8	867.9
15°	863.1	852.2	853.5	851.9	850.3
17.5°	843.6	832.6	832.8	830.3	829.9
20°	829.6	817.9	816.9	813.7	815.3
22.5°	814.3	802.0	800.9	796.5	798.7
25°	789.0	775.7	774.6	769.9	772.2
27.5°	759.7	746.6	746.6	739.9	742.4
30°	738.0	725.5	726.8	718.9	722.0
32.5°	715.0	703.8	704.5	696.6	699.7
35°	678.2	668.9	668.6	662.3	664.7
37.5°	640.6	632.3	631.0	627.4	628.0
40°	614.4	607.4	604.9	602.5	602.5
42.5°	587.0	580.6	578.1	576.3	575.7
45°	545.1	540.4	537.9	536.3	535.5
47.5°	503.7	499.3	497.1	496.0	495.2
50°	475.0	471.9	471.0	468.6	467.8
52.5°	446.3	444.4	443.6	440.5	439.8
55°	404.1	403.3	404.1	398.5	397.7
57.5°	360.1	361.3	363.9	356.4	354.5
60°	330.7	333.9	337.1	328.3	325.2
62.5°	300.8	305.8	310.3	300.2	295.8
65°	255.8	263.6	268.6	258.0	249.4
67.5°	212.5	222.1	228.1	216.7	207.0
70°	182.5	193.4	200.0	188.6	177.7
72.5°	156.4	168.5	173.9	163.1	152.2
75°	117.9	128.9	135.5	126.4	114.8
77.5°	83.7	94.0	99.5	91.6	81.9
80°	61.4	72.3	76.5	70.0	62.2
82.5°	43.5	52.6	55.5	51.5	46.2
85°	19.9	26.2	29.5	27.9	26.3
87.5°	5.1	9.5	12.1	12.1	12.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)