

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562541

Luminaire Tested: **SQ4-PC3-025U-075D-930-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562541
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-025U-075D-930-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9232.2 lumens
Efficiency: N/A
Efficacy: 97.4 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 94.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562541

CATALOG NUMBER: SQ4-PC3-025U-075D-930-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P562541

CATALOG NUMBER: SQ4-PC3-025U-075D-930-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79	75				
1	103	99	95	91	98	94	91	88	86	83	80	78	75	73	70	69	67	63				
2	94	87	80	75	89	83	77	72	75	70	67	68	65	61	62	59	57	53				
3	86	76	68	62	81	73	66	60	66	61	56	60	56	52	55	51	48	45				
4	79	67	59	53	75	64	57	51	59	53	48	54	49	45	49	45	41	38				
5	72	60	52	45	69	58	50	44	53	46	41	48	43	39	44	40	36	33				
6	67	54	46	39	63	52	44	38	48	41	36	44	38	34	40	35	32	29				
7	62	49	41	35	59	47	39	34	43	37	32	40	34	30	36	32	28	26				
8	57	45	36	31	55	43	35	30	39	33	28	36	31	27	33	29	25	23				
9	54	41	33	28	51	39	32	27	36	30	26	33	28	24	31	26	23	21				
10	50	38	30	25	48	36	29	24	33	27	23	31	26	22	29	24	21	19				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7803	7803	7803
5°	7862	7811	7782
10°	7842	7806	7784
15°	7801	7801	7794
20°	7750	7773	7773
25°	7677	7732	7709
30°	7583	7675	7642
35°	7470	7585	7532
40°	7347	7451	7375
45°	7213	7265	7152
50°	7025	7025	6913
55°	6802	6714	6613
60°	6473	6343	6242
65°	5983	5864	5812
70°	5239	5281	5260
75°	4215	4661	4690
80°	2995	3953	3994
85°	1824	3317	3317



TEST NUMBER: P562541

CATALOG NUMBER: SQ4-PC3-025U-075D-930-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	240.1	2.6
10°-20°	689.1	7.5
20°-30°	1043.5	11.3
30°-40°	1251.0	13.6
40°-50°	1275.6	13.8
50°-60°	1113.5	12.1
60°-70°	797.2	8.6
70°-80°	410.6	4.4
80°-90°	105.7	1.1
90°-100°	173.4	1.9
100°-110°	455.8	4.9
110°-120°	472.7	5.1
120°-130°	379.1	4.1
130°-140°	297.5	3.2
140°-150°	228.3	2.5
150°-160°	164.5	1.8
160°-170°	100.6	1.1
170°-180°	34.0	0.4
0°-30°	1972.7	21.4
0°-40°	3223.7	34.9
0°-60°	5612.8	60.8
0°-90°	6926.3	75.0
90°-120°	1101.9	11.9
90°-150°	2006.9	21.7
90°-180°	2306.0	25.0
0°-180°	9232.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2537	2537	2537	2537	2537	
5°	2547	2521	2530	2523	2521	242
15°	2450	2430	2450	2450	2448	691
25°	2262	2246	2279	2272	2272	1041
35°	1990	1985	2020	2006	2006	1244
45°	1658	1654	1670	1649	1644	1277
55°	1269	1252	1252	1233	1233	1131
65°	822	804	806	799	799	813
75°	355	371	392	395	395	383
85°	52	79	94	96	94	70
90°	2	7	18	9	9	4
95°	23	90	299	154	105	25
105°	82	124	504	765	714	87
115°	146	177	404	805	919	144
125°	203	228	367	621	732	180
135°	242	266	356	501	568	187
145°	280	298	351	427	461	176
155°	317	326	351	386	397	146
165°	342	346	351	365	369	97
175°	356	356	354	358	358	34
180°	356	356	356	356	356	

TEST NUMBER: P562541

CATALOG NUMBER: SQ4-PC3-025U-075D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2537.2	2537.2	2537.2	2537.2	2537.2
2.5°	2552.2	2530.1	2537.2	2531.3	2522.1
5°	2546.6	2521.3	2530.1	2523.0	2520.7
7.5°	2528.2	2503.0	2514.6	2509.9	2507.6
10°	2511.3	2486.0	2499.6	2494.8	2492.5
12.5°	2488.8	2465.3	2480.8	2476.1	2475.6
15°	2450.2	2429.6	2450.2	2450.2	2447.9
17.5°	2401.8	2383.0	2405.1	2406.5	2405.1
20°	2368.0	2347.3	2375.1	2372.8	2375.1
22.5°	2326.7	2309.7	2339.4	2333.3	2335.6
25°	2262.3	2246.2	2278.7	2271.7	2271.7
27.5°	2186.2	2174.7	2210.1	2202.6	2202.6
30°	2135.4	2124.0	2161.3	2151.9	2151.9
32.5°	2079.1	2071.2	2106.8	2095.5	2095.5
35°	1989.8	1985.2	2020.3	2006.2	2006.2
37.5°	1897.7	1893.6	1925.4	1908.4	1902.9
40°	1830.0	1827.7	1855.9	1837.1	1837.1
42.5°	1762.4	1760.1	1784.5	1761.9	1761.9
45°	1658.5	1654.0	1670.3	1649.0	1644.5
47.5°	1545.3	1540.7	1551.0	1527.9	1525.6
50°	1468.3	1463.7	1468.3	1447.1	1444.8
52.5°	1389.3	1381.1	1381.8	1360.7	1360.2
55°	1268.6	1252.5	1252.1	1233.3	1233.3
57.5°	1140.8	1119.6	1121.5	1105.5	1103.2
60°	1052.4	1029.5	1031.3	1017.2	1014.9
62.5°	966.0	939.4	944.9	928.9	928.4
65°	822.2	803.8	805.8	798.7	798.7
67.5°	684.1	667.1	679.4	673.7	673.3
70°	582.6	571.1	587.3	587.3	585.0
72.5°	488.6	488.2	508.4	508.4	509.8
75°	354.7	370.8	392.3	394.7	394.7
77.5°	236.8	265.3	289.0	289.9	289.4
80°	169.1	201.3	223.2	227.8	225.5
82.5°	114.6	148.6	166.8	171.4	169.1
85°	51.7	79.2	94.0	96.3	94.0
87.5°	15.5	32.9	41.2	39.3	35.7
90°	2.3	6.7	18.2	9.1	9.1
92.5°	9.6	46.1	102.2	45.2	29.2
95°	22.8	89.7	298.7	154.0	104.9
97.5°	39.7	98.5	447.0	355.5	261.8
100°	52.5	106.0	492.6	499.2	387.7
102.5°	63.4	113.3	505.4	621.8	526.3
105°	82.1	124.5	504.0	765.1	713.8
107.5°	101.3	140.5	475.3	839.5	852.0
110°	114.0	149.7	451.5	858.7	912.2

TEST NUMBER: P562541

CATALOG NUMBER: SQ4-PC3-025U-075D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	126.8	160.7	429.7	846.6	928.6
115°	146.0	177.2	403.7	805.3	919.1
117.5°	164.7	193.2	385.9	748.1	874.4
120°	175.6	202.4	378.6	709.7	832.4
122.5°	186.5	213.3	373.1	671.4	792.3
125°	203.0	227.5	367.2	620.6	732.0
127.5°	216.2	241.2	362.1	579.6	673.7
130°	223.5	250.2	360.3	553.9	640.8
132.5°	230.8	257.5	358.5	531.8	609.8
135°	241.7	266.3	355.8	501.0	567.9
137.5°	253.1	277.2	355.3	477.9	532.7
140°	262.3	284.6	353.5	459.6	510.8
142.5°	269.6	290.1	353.5	446.6	490.8
145°	280.5	298.3	351.2	427.2	460.7
147.5°	291.5	308.8	351.2	411.1	438.8
150°	298.7	314.4	351.2	401.9	424.2
152.5°	306.0	318.1	351.2	394.5	411.4
155°	317.0	325.9	351.2	385.7	396.8
157.5°	325.2	333.7	351.2	377.8	385.9
160°	330.7	337.4	351.2	374.1	378.6
162.5°	336.1	341.1	351.2	370.5	374.9
165°	342.1	346.5	351.2	365.0	369.4
167.5°	347.6	349.8	353.5	362.6	364.4
170°	351.2	353.4	353.5	362.6	362.6
172.5°	353.0	353.5	353.5	360.7	359.0
175°	355.8	355.8	353.5	358.0	358.0
177.5°	355.8	355.8	353.9	357.5	355.8
180°	355.8	355.8	355.8	355.8	355.8

(END OF REPORT)