

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564871

Luminaire Tested: **SQ4-PW1-0U-100D-930-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564871
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-0U-100D-930-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4506.9 lumens
Efficiency: N/A
Efficacy: 81.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Direct

Input Watts (W): 55.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564871
CATALOG NUMBER: SQ4-PW1-0U-100D-930-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P564871

CATALOG NUMBER: SQ4-PW1-0U-100D-930-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	105	101	97	107	102	99	95	98	95	92		94	92	89		91	89	87	85
2	100	92	85	80	97	90	84	79	86	81	77		83	79	75		80	76	73	71
3	91	81	73	67	89	79	72	66	76	70	65		74	68	64		71	66	63	60
4	84	72	63	57	81	71	63	56	68	61	56		66	60	55		64	58	54	52
5	77	64	56	49	75	63	55	49	61	54	48		59	53	48		57	52	47	45
6	71	58	49	43	69	57	49	43	55	48	42		54	47	42		52	46	42	40
7	66	53	44	38	64	52	44	38	50	43	38		49	42	37		48	42	37	35
8	62	48	40	34	60	48	40	34	46	39	34		45	38	34		44	38	33	31
9	58	44	36	31	56	44	36	31	43	35	31		42	35	30		41	35	30	28
10	54	41	33	28	53	40	33	28	39	33	28		39	32	28		38	32	28	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10896	10896	10896
5°	10966	10879	10831
10°	10878	10791	10732
15°	10763	10644	10604
20°	10635	10471	10451
25°	10486	10295	10263
30°	10264	10109	10043
35°	9973	9832	9773
40°	9662	9512	9474
45°	9286	9164	9123
50°	8901	8826	8766
55°	8486	8486	8352
60°	7968	8122	7834
65°	7292	7655	7110
70°	6427	7044	6258
75°	5490	6305	5340
80°	4258	5306	4311
85°	2752	4072	3634



TEST NUMBER: P564871

CATALOG NUMBER: SQ4-PW1-0U-100D-930-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.8	3.7
10°-20°	470.9	10.4
20°-30°	698.6	15.5
30°-40°	817.4	18.1
40°-50°	813.7	18.1
50°-60°	702.7	15.6
60°-70°	505.8	11.2
70°-80°	265.2	5.9
80°-90°	65.8	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1336.3	29.6
0°-40°	2153.7	47.8
0°-60°	3670.1	81.4
0°-90°	4506.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4506.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1771	1771	1771	1771	1771	
5°	1776	1756	1762	1757	1754	168
15°	1690	1669	1672	1668	1665	476
25°	1545	1519	1517	1508	1512	710
35°	1328	1310	1309	1297	1302	830
45°	1068	1058	1054	1050	1049	824
55°	791	790	791	780	779	706
65°	501	516	526	505	488	496
75°	231	252	265	248	225	248
85°	39	51	58	55	52	53
90°	0	0	0	0	0	



TEST NUMBER: P564871

CATALOG NUMBER: SQ4-PW1-0U-100D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1771.4	1771.4	1771.4	1771.4	1771.4
2.5°	1781.4	1766.7	1771.4	1767.5	1758.9
5°	1776.1	1756.2	1762.0	1757.3	1754.2
7.5°	1758.0	1739.7	1743.9	1738.9	1737.1
10°	1741.7	1723.4	1727.7	1721.4	1718.3
12.5°	1723.0	1703.5	1707.7	1701.4	1699.6
15°	1690.2	1668.9	1671.5	1668.3	1665.3
17.5°	1652.2	1630.5	1630.9	1625.9	1625.3
20°	1624.7	1601.8	1599.7	1593.6	1596.6
22.5°	1594.7	1570.6	1568.5	1559.9	1564.1
25°	1545.1	1519.2	1517.0	1507.7	1512.3
27.5°	1487.7	1462.0	1462.1	1449.1	1454.0
30°	1445.2	1420.8	1423.4	1407.9	1414.0
32.5°	1400.3	1378.3	1379.7	1364.2	1370.3
35°	1328.2	1309.8	1309.4	1297.1	1301.6
37.5°	1254.5	1238.3	1235.8	1228.6	1229.8
40°	1203.3	1189.6	1184.6	1179.9	1179.9
42.5°	1149.6	1137.1	1132.1	1128.7	1127.5
45°	1067.5	1058.4	1053.5	1050.3	1048.8
47.5°	986.4	977.8	973.6	971.3	969.8
50°	930.2	924.1	922.4	917.7	916.1
52.5°	874.0	870.3	868.7	862.7	861.2
55°	791.3	789.8	791.3	780.3	778.8
57.5°	705.1	707.6	712.6	697.9	694.2
60°	647.7	653.8	660.2	642.9	636.8
62.5°	589.0	598.8	607.7	587.9	579.3
65°	501.0	516.2	526.0	505.3	488.5
67.5°	416.1	435.0	446.7	424.4	405.5
70°	357.4	378.8	391.7	369.4	348.0
72.5°	306.2	330.0	340.5	319.5	298.1
75°	231.0	252.3	265.3	247.6	224.7
77.5°	163.9	184.0	194.8	179.4	160.4
80°	120.2	141.5	149.8	137.0	121.7
82.5°	85.2	102.9	108.6	100.9	90.5
85°	39.0	51.2	57.7	54.6	51.5
87.5°	10.0	18.5	23.7	23.8	25.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)