

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P565183

Luminaire Tested: **SQ4-PW1-150U-125D-930-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P565183
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-150U-125D-930-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12944.1 lumens
Efficiency: N/A
Efficacy: 101.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 127.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P565183
CATALOG NUMBER: SQ4-PW1-150U-125D-930-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P565183

CATALOG NUMBER: SQ4-PW1-150U-125D-930-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	97	92	89	85	88	85	82	79	70	68	66	57	56	54	45	44	43	38
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	40	38	37	32
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	35	33	31	27
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	62	52	45	39	43	38	34	36	32	29	29	26	23	20
6	62	50	42	36	57	46	39	34	39	34	30	32	28	25	26	23	21	18
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	50	37	30	25	45	35	28	24	30	24	21	25	21	18	20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	19	23	19	16	19	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13904	13904	13904
5°	13994	13884	13822
10°	13882	13770	13696
15°	13735	13583	13532
20°	13571	13363	13337
25°	13382	13138	13098
30°	13099	12901	12816
35°	12727	12547	12473
40°	12330	12138	12090
45°	11850	11694	11642
50°	11358	11264	11187
55°	10829	10829	10657
60°	10167	10364	9996
65°	9304	9769	9073
70°	8202	8990	7987
75°	7006	8047	6816
80°	5434	6773	5504
85°	3515	5201	4637



TEST NUMBER: P565183

CATALOG NUMBER: SQ4-PW1-150U-125D-930-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	212.9	1.6
10°-20°	601.0	4.6
20°-30°	891.4	6.9
30°-40°	1043.1	8.1
40°-50°	1038.4	8.0
50°-60°	896.7	6.9
60°-70°	645.5	5.0
70°-80°	338.5	2.6
80°-90°	86.3	0.7
90°-100°	518.3	4.0
100°-110°	1401.4	10.8
110°-120°	1473.3	11.4
120°-130°	1196.7	9.2
130°-140°	938.7	7.3
140°-150°	720.5	5.6
150°-160°	518.2	4.0
160°-170°	316.5	2.4
170°-180°	106.7	0.8
0°-30°	1705.3	13.2
0°-40°	2748.4	21.2
0°-60°	4683.5	36.2
0°-90°	5753.8	44.5
90°-120°	3393.0	26.2
90°-150°	6249.0	48.3
90°-180°	7190.0	55.5
0°-180°	12944.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2260	2260	2260	2260	2260	
5°	2266	2241	2249	2242	2239	215
15°	2157	2130	2133	2129	2125	608
25°	1972	1939	1936	1924	1930	907
35°	1695	1672	1671	1655	1661	1060
45°	1362	1351	1344	1340	1338	1051
55°	1010	1008	1010	996	994	901
65°	639	659	671	645	623	634
75°	295	322	339	316	287	316
85°	50	65	74	70	66	66
90°	2	7	16	17	16	7
95°	80	282	862	446	265	84
105°	260	402	1555	2293	2199	274
115°	459	561	1289	2496	2818	453
125°	628	719	1162	1961	2304	560
135°	753	842	1131	1583	1792	582
145°	875	941	1115	1355	1459	547
155°	988	1027	1106	1216	1256	456
165°	1076	1086	1110	1154	1160	303
175°	1116	1115	1112	1126	1124	106
180°	1115	1115	1115	1115	1115	



TEST NUMBER: P565183

CATALOG NUMBER: SQ4-PW1-150U-125D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2260.5	2260.5	2260.5	2260.5	2260.5
2.5°	2273.3	2254.6	2260.5	2255.5	2244.6
5°	2266.5	2241.2	2248.6	2242.5	2238.6
7.5°	2243.4	2220.0	2225.5	2219.1	2216.7
10°	2222.7	2199.3	2204.8	2196.7	2192.8
12.5°	2198.8	2173.9	2179.3	2171.3	2168.9
15°	2157.0	2129.7	2133.1	2129.0	2125.1
17.5°	2108.4	2080.7	2081.3	2074.9	2074.1
20°	2073.3	2044.1	2041.5	2033.6	2037.5
22.5°	2035.1	2004.3	2001.6	1990.6	1996.1
25°	1971.8	1938.6	1935.9	1924.1	1929.9
27.5°	1898.5	1865.7	1865.8	1849.2	1855.4
30°	1844.3	1813.1	1816.4	1796.7	1804.5
32.5°	1786.9	1758.9	1760.6	1740.9	1748.7
35°	1694.9	1671.5	1671.0	1655.2	1661.1
37.5°	1600.9	1580.3	1577.0	1567.9	1569.4
40°	1535.6	1518.1	1511.7	1505.7	1505.7
42.5°	1467.1	1451.1	1444.8	1440.3	1438.8
45°	1362.3	1350.6	1344.4	1340.4	1338.4
47.5°	1258.7	1247.8	1242.4	1239.6	1237.6
50°	1187.0	1179.2	1177.1	1171.1	1169.1
52.5°	1115.3	1110.7	1108.6	1101.0	1099.0
55°	1009.8	1007.8	1009.8	995.8	993.8
57.5°	899.8	903.0	909.4	890.6	885.9
60°	826.5	834.3	842.5	820.4	812.6
62.5°	751.7	764.1	775.6	750.2	739.3
65°	639.3	658.8	671.2	644.8	623.4
67.5°	531.0	555.1	570.0	541.6	517.4
70°	456.1	483.4	499.9	471.4	444.1
72.5°	390.8	421.1	434.6	407.7	380.4
75°	294.8	322.0	338.6	316.0	286.8
77.5°	209.1	234.8	248.6	228.9	204.7
80°	153.4	180.6	191.2	174.8	155.4
82.5°	108.7	131.3	138.6	128.8	115.5
85°	49.8	65.4	73.7	69.6	65.7
87.5°	13.2	25.1	33.4	33.7	35.0
90°	2.4	7.1	15.6	16.8	15.6
92.5°	34.1	124.2	245.1	106.4	77.1
95°	80.4	282.3	861.9	446.1	265.3
97.5°	129.2	323.8	1343.6	1111.9	816.6
100°	165.7	340.6	1493.4	1557.4	1259.3
102.5°	199.3	363.8	1546.2	1895.3	1672.3
105°	260.5	402.5	1554.6	2293.2	2199.3
107.5°	317.2	446.8	1486.7	2541.4	2572.6
110°	361.3	478.7	1426.2	2608.0	2740.7



TEST NUMBER: P565183

CATALOG NUMBER: SQ4-PW1-150U-125D-930-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	400.7	510.6	1370.5	2594.7	2817.5
115°	458.6	560.7	1289.3	2495.9	2817.5
117.5°	515.2	611.0	1235.8	2344.9	2709.5
120°	549.8	643.7	1204.1	2236.5	2608.6
122.5°	582.5	674.5	1184.9	2120.4	2495.3
125°	627.8	719.4	1162.1	1961.0	2303.7
127.5°	669.6	759.5	1148.6	1830.9	2132.3
130°	692.7	785.4	1142.9	1750.5	2022.8
132.5°	716.7	808.5	1137.1	1678.0	1928.7
135°	752.7	841.9	1130.8	1583.4	1792.3
137.5°	789.0	873.2	1125.6	1506.6	1676.8
140°	813.9	892.6	1123.6	1457.2	1608.6
142.5°	837.9	911.9	1119.8	1412.6	1545.3
145°	875.1	940.9	1115.2	1355.3	1458.6
147.5°	909.0	967.2	1110.0	1303.4	1382.7
150°	934.0	985.6	1108.0	1275.1	1338.5
152.5°	957.0	1002.1	1107.1	1249.0	1301.1
155°	988.0	1026.7	1105.6	1215.8	1255.7
157.5°	1020.2	1047.2	1105.9	1192.7	1219.0
160°	1038.4	1060.7	1106.8	1178.1	1196.9
162.5°	1052.8	1071.4	1107.8	1166.5	1180.5
165°	1075.6	1086.2	1110.4	1153.8	1159.7
167.5°	1091.2	1098.5	1110.7	1142.9	1145.7
170°	1100.8	1104.4	1111.6	1138.1	1138.1
172.5°	1108.5	1109.2	1111.6	1132.3	1131.3
175°	1116.4	1115.3	1111.6	1126.0	1123.6
177.5°	1119.1	1116.3	1111.4	1120.9	1118.1
180°	1115.2	1115.2	1115.2	1115.2	1115.2

(END OF REPORT)