

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563285

Luminaire Tested: **SQ4-PP3-050U-050D-930-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563285
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-050U-050D-930-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9411.7 lumens
Efficiency: N/A
Efficacy: 118.2 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 79.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563285
CATALOG NUMBER: SQ4-PP3-050U-050D-930-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P563285

CATALOG NUMBER: SQ4-PP3-050U-050D-930-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20		
RC	80					70					50					0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	49
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	49	48	47	42
2	89	82	76	71	82	76	71	66	64	60	57	54	51	48	44	42	40	36
3	82	72	65	59	75	67	61	55	57	52	48	48	44	41	39	36	34	30
4	75	64	56	50	69	59	52	47	51	45	41	42	38	35	35	32	30	26
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	31	28	26	23
6	63	51	43	37	58	48	40	35	41	35	31	34	30	27	28	25	23	20
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5592	5592	5592
5°	5633	5598	5578
10°	5623	5583	5559
15°	5586	5556	5525
20°	5549	5518	5476
25°	5483	5445	5391
30°	5381	5353	5285
35°	5241	5205	5139
40°	5073	5041	4984
45°	4935	4900	4852
50°	4758	4727	4681
55°	4511	4451	4417
60°	4107	3989	3970
65°	3618	3467	3456
70°	3124	2994	2994
75°	2689	2651	2613
80°	2371	2398	2343
85°	1856	2025	2025



TEST NUMBER: P563285

CATALOG NUMBER: SQ4-PP3-050U-050D-930-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.9	1.8
10°-20°	490.9	5.2
20°-30°	735.3	7.8
30°-40°	862.5	9.2
40°-50°	865.2	9.2
50°-60°	738.1	7.8
60°-70°	481.4	5.1
70°-80°	241.5	2.6
80°-90°	69.6	0.7
90°-100°	349.6	3.7
100°-110°	949.7	10.1
110°-120°	976.5	10.4
120°-130°	780.7	8.3
130°-140°	613.5	6.5
140°-150°	470.4	5.0
150°-160°	338.3	3.6
160°-170°	206.9	2.2
170°-180°	69.7	0.7
0°-30°	1398.2	14.9
0°-40°	2260.6	24.0
0°-60°	3863.9	41.1
0°-90°	4656.4	49.5
90°-120°	2275.9	24.2
90°-150°	4140.4	44.0
90°-180°	4755.0	50.5
0°-180°	9411.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1818	1818	1818	1818	1818	
5°	1825	1807	1813	1807	1807	173
15°	1754	1737	1745	1738	1735	495
25°	1616	1597	1605	1590	1589	743
35°	1396	1382	1386	1370	1369	872
45°	1135	1127	1127	1116	1116	874
55°	841	838	830	825	824	748
65°	497	488	476	473	475	496
75°	226	226	223	222	220	246
85°	53	57	57	57	57	62
90°	2	9	16	21	21	6
95°	52	191	609	265	178	55
105°	169	262	1044	1590	1496	179
115°	300	364	836	1663	1894	296
125°	412	469	756	1274	1503	367
135°	496	551	735	1038	1171	384
145°	574	615	726	882	948	360
155°	649	672	721	792	815	299
165°	702	712	724	754	756	198
175°	728	731	726	735	733	69
180°	728	728	728	728	728	

TEST NUMBER: P563285

CATALOG NUMBER: SQ4-PP3-050U-050D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1818.2	1818.2	1818.2	1818.2	1818.2
2.5°	1829.7	1814.7	1818.2	1815.5	1808.0
5°	1824.6	1807.4	1813.4	1807.0	1807.0
7.5°	1812.1	1793.5	1799.4	1793.0	1792.7
10°	1800.7	1782.0	1787.9	1781.5	1780.0
12.5°	1784.1	1765.4	1772.6	1765.0	1764.7
15°	1754.5	1737.3	1744.9	1738.5	1735.3
17.5°	1721.0	1702.3	1711.4	1702.5	1701.2
20°	1695.5	1676.8	1685.9	1673.2	1673.2
22.5°	1664.9	1646.2	1656.6	1640.0	1640.0
25°	1615.8	1597.1	1604.7	1590.3	1588.7
27.5°	1557.5	1539.1	1547.0	1530.7	1530.4
30°	1515.4	1498.3	1507.5	1489.9	1488.3
32.5°	1469.5	1453.6	1460.3	1442.7	1441.2
35°	1395.9	1381.9	1386.4	1370.4	1368.8
37.5°	1318.5	1304.1	1309.2	1295.5	1294.9
40°	1263.7	1254.3	1255.7	1244.5	1241.4
42.5°	1212.7	1202.1	1203.4	1192.3	1191.6
45°	1134.6	1126.8	1126.6	1115.5	1115.5
47.5°	1051.7	1045.8	1044.1	1034.8	1034.5
50°	994.4	989.7	988.0	980.0	978.4
52.5°	934.4	932.3	926.8	920.1	919.8
55°	841.4	838.3	830.2	825.4	823.8
57.5°	740.3	734.1	725.1	718.1	719.3
60°	667.7	661.5	648.6	645.4	645.4
62.5°	597.6	590.1	577.2	572.8	575.3
65°	497.2	487.8	476.5	473.3	474.9
67.5°	406.0	397.6	385.3	385.3	384.0
70°	347.4	342.7	333.0	333.0	333.0
72.5°	295.1	292.9	285.9	285.8	284.6
75°	226.3	226.3	223.1	221.5	219.9
77.5°	169.6	170.2	168.6	166.9	164.1
80°	133.9	137.0	135.4	133.8	132.3
82.5°	100.7	103.8	103.6	100.7	100.4
85°	52.6	57.3	57.4	57.4	57.4
87.5°	14.5	20.9	23.7	24.6	25.9
90°	2.3	9.2	16.4	21.1	21.1
92.5°	21.1	95.7	166.3	71.4	60.4
95°	51.5	191.2	608.9	265.0	178.0
97.5°	85.2	211.2	933.4	726.2	510.0
100°	107.7	224.5	1032.7	1046.9	845.4
102.5°	130.2	237.8	1059.0	1294.7	1117.0
105°	168.6	262.5	1044.4	1590.3	1496.4
107.5°	208.4	291.3	984.0	1742.9	1769.0
110°	236.5	312.1	939.1	1772.9	1885.1



TEST NUMBER: P563285

CATALOG NUMBER: SQ4-PP3-050U-050D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	260.9	332.8	894.1	1748.0	1917.0
115°	299.7	363.9	836.0	1663.2	1894.5
117.5°	336.3	397.6	799.0	1543.1	1803.6
120°	360.6	420.2	782.2	1462.5	1721.2
122.5°	381.2	440.8	770.9	1381.7	1631.3
125°	412.2	469.4	756.4	1274.4	1503.4
127.5°	439.8	496.6	748.4	1193.2	1389.6
130°	456.6	511.6	744.7	1142.1	1318.4
132.5°	473.5	528.5	740.9	1098.6	1254.7
135°	496.5	551.4	735.3	1038.1	1170.9
137.5°	521.3	571.2	732.5	984.7	1096.4
140°	536.3	584.4	730.6	950.7	1051.5
142.5°	551.3	595.7	728.8	924.1	1008.4
145°	573.7	615.0	726.0	882.0	948.4
147.5°	599.0	634.3	723.6	848.9	901.1
150°	615.9	645.7	723.6	829.9	871.1
152.5°	629.0	655.1	721.7	812.9	846.8
155°	648.7	671.6	721.3	792.0	814.9
157.5°	667.9	685.7	721.3	777.9	795.3
160°	679.1	695.1	721.3	768.4	782.2
162.5°	690.4	702.7	723.1	760.8	770.9
165°	702.5	711.7	723.6	754.1	756.4
167.5°	715.2	719.8	726.0	746.1	748.0
170°	718.9	723.5	726.0	742.3	742.3
172.5°	722.7	725.4	726.0	738.6	738.6
175°	728.3	730.6	726.0	735.3	733.0
177.5°	730.2	730.2	724.5	732.0	728.3
180°	728.3	728.3	728.3	728.3	728.3

(END OF REPORT)