

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563381

Luminaire Tested: **SQ4-PP3-075U-050D-930-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563381  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-075U-050D-930-1D-UNV-STD-W-12  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 11803.4 lumens  
Efficiency: N/A  
Efficacy: 109.9 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 107.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563381  
CATALOG NUMBER: SQ4-PP3-075U-050D-930-1D-UNV-STD-W-12

### Luminous Intensity Polar Plot





TEST NUMBER: P563381

CATALOG NUMBER: SQ4-PP3-075U-050D-930-1D-UNV-STD-W-12

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39				
1	96	91	88	84	87	83	80	77	68	66	64	54	53	51	41	40	40	34				
2	87	80	74	69	79	73	68	64	60	56	53	48	45	43	36	35	33	28				
3	80	70	63	58	72	64	58	53	53	48	45	42	39	37	32	30	29	24				
4	73	62	55	49	66	57	50	45	47	42	38	38	34	31	29	27	25	21				
5	67	55	47	42	60	51	44	39	42	37	33	34	30	27	26	24	22	18				
6	61	50	42	36	56	46	39	34	38	33	29	30	27	24	24	21	19	16				
7	57	45	37	32	51	41	34	29	34	29	25	28	24	21	22	19	17	14				
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	20	17	15	13				
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	16	14	11				
10	46	34	27	22	42	31	25	21	26	21	18	21	18	15	17	14	12	10				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5592	5592	5592
5°	5633	5598	5578
10°	5623	5583	5559
15°	5586	5556	5525
20°	5549	5518	5476
25°	5483	5445	5391
30°	5381	5353	5285
35°	5241	5205	5139
40°	5073	5041	4984
45°	4935	4900	4852
50°	4758	4727	4681
55°	4511	4451	4417
60°	4107	3989	3970
65°	3618	3467	3456
70°	3124	2994	2994
75°	2689	2651	2613
80°	2371	2398	2343
85°	1856	2025	2025



TEST NUMBER: P563381

CATALOG NUMBER: SQ4-PP3-075U-050D-930-1D-UNV-STD-W-12

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	171.9	1.5
10°-20°	490.9	4.2
20°-30°	735.3	6.2
30°-40°	862.5	7.3
40°-50°	865.2	7.3
50°-60°	738.1	6.3
60°-70°	481.4	4.1
70°-80°	241.5	2.0
80°-90°	69.6	0.6
90°-100°	517.4	4.4
100°-110°	1423.6	12.1
110°-120°	1469.4	12.4
120°-130°	1177.3	10.0
130°-140°	924.7	7.8
140°-150°	708.6	6.0
150°-160°	509.5	4.3
160°-170°	311.5	2.6
170°-180°	105.0	0.9
0°-30°	1398.2	11.8
0°-40°	2260.6	19.2
0°-60°	3863.9	32.7
0°-90°	4656.4	39.4
90°-120°	3410.4	28.9
90°-150°	6220.9	52.7
90°-180°	7147.0	60.6
0°-180°	11803.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1818	1818	1818	1818	1818	
5°	1825	1807	1813	1807	1807	173
15°	1754	1737	1745	1738	1735	495
25°	1616	1597	1605	1590	1589	743
35°	1396	1382	1386	1370	1369	872
45°	1135	1127	1127	1116	1116	874
55°	841	838	830	825	824	748
65°	497	488	476	473	475	496
75°	226	226	223	222	220	246
85°	53	57	57	57	57	62
90°	2	9	16	21	21	7
95°	77	282	915	391	250	81
105°	254	391	1569	2389	2229	268
115°	450	549	1258	2505	2843	445
125°	621	708	1141	1931	2262	554
135°	749	831	1109	1562	1767	578
145°	866	925	1092	1330	1433	543
155°	980	1012	1085	1196	1230	450
165°	1060	1073	1090	1135	1141	299
175°	1097	1099	1092	1106	1104	104
180°	1097	1097	1097	1097	1097	



TEST NUMBER: P563381

CATALOG NUMBER: SQ4-PP3-075U-050D-930-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1818.2	1818.2	1818.2	1818.2	1818.2
2.5°	1829.7	1814.7	1818.2	1815.5	1808.0
5°	1824.6	1807.4	1813.4	1807.0	1807.0
7.5°	1812.1	1793.5	1799.4	1793.0	1792.7
10°	1800.7	1782.0	1787.9	1781.5	1780.0
12.5°	1784.1	1765.4	1772.6	1765.0	1764.7
15°	1754.5	1737.3	1744.9	1738.5	1735.3
17.5°	1721.0	1702.3	1711.4	1702.5	1701.2
20°	1695.5	1676.8	1685.9	1673.2	1673.2
22.5°	1664.9	1646.2	1656.6	1640.0	1640.0
25°	1615.8	1597.1	1604.7	1590.3	1588.7
27.5°	1557.5	1539.1	1547.0	1530.7	1530.4
30°	1515.4	1498.3	1507.5	1489.9	1488.3
32.5°	1469.5	1453.6	1460.3	1442.7	1441.2
35°	1395.9	1381.9	1386.4	1370.4	1368.8
37.5°	1318.5	1304.1	1309.2	1295.5	1294.9
40°	1263.7	1254.3	1255.7	1244.5	1241.4
42.5°	1212.7	1202.1	1203.4	1192.3	1191.6
45°	1134.6	1126.8	1126.6	1115.5	1115.5
47.5°	1051.7	1045.8	1044.1	1034.8	1034.5
50°	994.4	989.7	988.0	980.0	978.4
52.5°	934.4	932.3	926.8	920.1	919.8
55°	841.4	838.3	830.2	825.4	823.8
57.5°	740.3	734.1	725.1	718.1	719.3
60°	667.7	661.5	648.6	645.4	645.4
62.5°	597.6	590.1	577.2	572.8	575.3
65°	497.2	487.8	476.5	473.3	474.9
67.5°	406.0	397.6	385.3	385.3	384.0
70°	347.4	342.7	333.0	333.0	333.0
72.5°	295.1	292.9	285.9	285.8	284.6
75°	226.3	226.3	223.1	221.5	219.9
77.5°	169.6	170.2	168.6	166.9	164.1
80°	133.9	137.0	135.4	133.8	132.3
82.5°	100.7	103.8	103.6	100.7	100.4
85°	52.6	57.3	57.4	57.4	57.4
87.5°	14.5	20.8	23.7	24.6	25.9
90°	2.3	9.2	16.3	21.0	21.0
92.5°	32.2	137.7	238.6	91.6	75.2
95°	77.0	282.4	915.0	391.3	249.8
97.5°	125.6	313.2	1396.3	1075.9	759.1
100°	161.1	332.2	1547.6	1562.0	1274.5
102.5°	194.7	354.9	1586.8	1937.9	1674.1
105°	254.4	391.4	1568.6	2388.9	2229.1
107.5°	311.4	436.5	1479.4	2609.8	2657.2
110°	352.5	466.6	1412.2	2664.7	2829.0



TEST NUMBER: P563381

CATALOG NUMBER: SQ4-PP3-075U-050D-930-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	389.8	500.3	1345.0	2629.3	2879.5
115°	450.5	548.6	1258.1	2505.3	2843.0
117.5°	508.4	598.8	1203.0	2331.2	2713.3
120°	543.9	630.6	1178.8	2200.8	2595.6
122.5°	575.6	662.3	1162.0	2086.4	2461.2
125°	620.9	707.6	1141.4	1930.9	2261.8
127.5°	663.8	746.5	1127.9	1801.1	2091.4
130°	686.3	770.7	1120.4	1724.0	1988.7
132.5°	712.4	796.8	1114.8	1656.2	1895.4
135°	749.3	831.4	1108.7	1561.6	1767.0
137.5°	783.8	860.0	1103.6	1485.1	1654.5
140°	810.0	880.7	1101.7	1434.3	1587.2
142.5°	832.4	897.6	1098.0	1389.0	1520.0
145°	866.0	925.3	1092.4	1330.5	1433.2
147.5°	901.9	953.1	1089.6	1278.7	1360.8
150°	924.3	970.0	1087.7	1250.2	1314.1
152.5°	944.9	986.9	1085.9	1225.7	1278.7
155°	980.4	1012.3	1085.4	1195.9	1230.1
157.5°	1006.0	1032.1	1085.4	1171.4	1195.1
160°	1024.7	1045.2	1085.4	1158.2	1176.4
162.5°	1039.6	1056.5	1087.3	1146.9	1161.5
165°	1059.7	1073.4	1090.1	1134.6	1141.4
167.5°	1073.7	1084.2	1092.4	1124.2	1126.0
170°	1083.1	1089.9	1092.4	1120.4	1120.4
172.5°	1090.5	1093.7	1092.4	1114.8	1112.9
175°	1097.1	1099.3	1092.4	1106.4	1104.1
177.5°	1098.9	1098.9	1091.5	1102.6	1098.9
180°	1097.1	1097.1	1097.1	1097.1	1097.1

(END OF REPORT)