

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519321

Luminaire Tested: **SQ4-WB-0U-100D-930-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P519321  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2009-966-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 4/29/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-WB-0U-100D-930-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE  
DOWNLIGHT 1000 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3927.5 lumens  
Efficiency: N/A  
Efficacy: 71.0 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: Direct

Input Watts (W): 55.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P519321  
CATALOG NUMBER: SQ4-WB-0U-100D-930-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P519321

CATALOG NUMBER: SQ4-WB-OU-100D-930-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69
4	89	79	72	66	87	78	71	66	76	70	65	74	68	64	71	67	64	62
5	83	72	65	59	81	71	64	59	69	63	58	67	62	58	66	61	57	55
6	78	66	59	53	76	65	58	53	64	57	53	62	56	52	61	56	52	50
7	73	61	53	48	71	60	53	48	59	52	48	58	52	47	56	51	47	45
8	68	57	49	44	67	56	49	44	55	48	44	53	48	43	52	47	43	41
9	64	53	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38
10	61	49	42	37	60	48	42	37	48	41	37	47	41	37	46	41	37	35

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16578	16578	16578
5°	16371	16313	16408
10°	15467	15608	15970
15°	14278	14610	15265
20°	12967	13454	14345
25°	11630	12264	13364
30°	10399	11079	12347
35°	9093	9751	11144
40°	7654	8261	9648
45°	6317	6861	8055
50°	5273	5749	6711
55°	4477	4934	5542
60°	3826	4277	4422
65°	3046	3598	2857
70°	2701	2807	1744
75°	2502	2277	1067
80°	2302	2093	921
85°	2089	1920	748



TEST NUMBER: P519321

CATALOG NUMBER: SQ4-WB-OU-100D-930-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	247.2	6.3
10°-20°	643.0	16.4
20°-30°	832.9	21.2
30°-40°	815.6	20.8
40°-50°	624.3	15.9
50°-60°	416.0	10.6
60°-70°	227.0	5.8
70°-80°	94.6	2.4
80°-90°	26.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1723.2	43.9
0°-40°	2538.8	64.6
0°-60°	3579.1	91.1
0°-90°	3927.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3927.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2695	2695	2695	2695	2695	
5°	2652	2625	2642	2648	2657	247
15°	2242	2234	2294	2357	2397	626
25°	1714	1718	1807	1886	1969	788
35°	1211	1217	1299	1386	1484	753
45°	726	740	789	848	926	566
55°	418	435	460	478	517	379
65°	209	227	247	216	196	218
75°	105	105	96	66	45	112
85°	30	30	27	18	11	34
90°	0	0	0	0	0	



TEST NUMBER: P519321

CATALOG NUMBER: SQ4-WB-OU-100D-930-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2695.3	2695.3	2695.3	2695.3	2695.3
2.5°	2701.9	2677.9	2683.9	2683.8	2676.4
5°	2651.5	2624.9	2642.1	2648.2	2657.4
7.5°	2553.1	2533.0	2564.2	2587.4	2606.1
10°	2476.5	2459.1	2499.0	2532.6	2556.9
12.5°	2387.6	2373.0	2422.3	2467.5	2499.2
15°	2242.3	2234.2	2294.4	2356.8	2397.2
17.5°	2086.9	2083.0	2152.0	2224.8	2276.6
20°	1981.0	1979.8	2055.5	2131.3	2191.5
22.5°	1874.0	1876.6	1956.1	2035.0	2103.5
25°	1713.7	1718.3	1807.1	1885.9	1969.1
27.5°	1565.4	1567.4	1659.3	1742.4	1831.2
30°	1464.1	1469.9	1559.9	1646.0	1738.5
32.5°	1362.9	1369.6	1457.7	1546.7	1641.1
35°	1211.0	1216.8	1298.6	1385.9	1484.2
37.5°	1054.5	1062.3	1134.9	1217.5	1314.2
40°	953.2	964.8	1028.9	1106.8	1201.6
42.5°	855.8	870.1	929.6	1003.4	1089.0
45°	726.2	740.0	788.8	848.5	926.0
47.5°	614.5	630.5	668.0	719.4	785.5
50°	551.1	566.2	600.8	638.9	701.3
52.5°	495.3	510.3	541.2	570.5	623.7
55°	417.5	434.8	460.1	477.5	516.8
57.5°	353.6	370.3	390.3	398.2	422.0
60°	311.0	329.5	347.7	346.8	359.5
62.5°	272.2	288.0	306.1	293.6	294.2
65°	209.3	226.7	247.2	216.0	196.3
67.5°	169.1	172.8	194.0	150.6	127.3
70°	150.2	150.2	156.1	116.6	97.0
72.5°	132.2	132.2	126.8	94.9	74.3
75°	105.3	105.3	95.8	65.8	44.9
77.5°	81.1	80.2	73.3	49.1	32.6
80°	65.0	65.0	59.1	38.7	26.0
82.5°	50.9	50.9	45.9	30.3	19.4
85°	29.6	29.6	27.2	17.6	10.6
87.5°	10.4	10.4	9.5	5.7	4.7
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)