

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563429

Luminaire Tested: **SQ4-PP3-075U-100D-930-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563429  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-075U-100D-930-1D-UNV-STD-W-12  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 16263.1 lumens  
Efficiency: N/A  
Efficacy: 100.3 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 162.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563429  
CATALOG NUMBER: SQ4-PP3-075U-100D-930-1D-UNV-STD-W-12

### Luminous Intensity Polar Plot





TEST NUMBER: P563429

CATALOG NUMBER: SQ4-PP3-075U-100D-930-1D-UNV-STD-W-12

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	55	54	53	48
2	91	83	77	72	84	78	72	68	67	63	60	58	55	52	49	46	45	40
3	83	73	66	60	77	69	62	57	59	54	50	51	47	44	43	40	38	34
4	76	65	57	51	70	61	54	48	53	47	43	46	41	38	39	36	33	30
5	70	58	50	44	65	54	47	42	47	42	37	41	36	33	35	31	29	26
6	64	52	44	38	60	49	42	36	43	37	33	37	32	29	32	28	25	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	29	25	23	20
8	55	43	35	30	51	40	33	28	35	30	26	31	26	23	27	23	20	18
9	51	39	32	26	48	37	30	25	32	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	23	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10951	10951	10951
5°	11031	10963	10925
10°	11012	10934	10886
15°	10940	10880	10820
20°	10867	10806	10724
25°	10738	10664	10558
30°	10539	10484	10351
35°	10263	10193	10064
40°	9935	9872	9760
45°	9664	9596	9501
50°	9317	9257	9168
55°	8835	8718	8651
60°	8043	7812	7774
65°	7085	6790	6768
70°	6117	5864	5864
75°	5265	5191	5118
80°	4642	4699	4587
85°	3634	3963	3963



TEST NUMBER: P563429

CATALOG NUMBER: SQ4-PP3-075U-100D-930-1D-UNV-STD-W-12

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	336.7	2.1
10°-20°	961.4	5.9
20°-30°	1440.0	8.9
30°-40°	1689.1	10.4
40°-50°	1694.3	10.4
50°-60°	1445.4	8.9
60°-70°	942.7	5.8
70°-80°	472.9	2.9
80°-90°	133.7	0.8
90°-100°	517.4	3.2
100°-110°	1423.6	8.8
110°-120°	1469.4	9.0
120°-130°	1177.3	7.2
130°-140°	924.7	5.7
140°-150°	708.6	4.4
150°-160°	509.5	3.1
160°-170°	311.5	1.9
170°-180°	105.0	0.6
0°-30°	2738.1	16.8
0°-40°	4427.2	27.2
0°-60°	7566.9	46.5
0°-90°	9116.2	56.1
90°-120°	3410.4	21.0
90°-150°	6220.9	38.3
90°-180°	7147.0	43.9
0°-180°	16263.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3561	3561	3561	3561	3561	
5°	3573	3540	3551	3539	3539	339
15°	3436	3402	3417	3404	3398	969
25°	3164	3128	3142	3114	3111	1455
35°	2734	2706	2715	2684	2681	1708
45°	2222	2207	2206	2184	2184	1711
55°	1648	1642	1626	1616	1613	1464
65°	974	955	933	927	930	972
75°	443	443	437	434	431	481
85°	103	112	112	112	112	121
90°	2	9	16	21	21	9
95°	77	282	915	391	250	81
105°	254	391	1569	2389	2229	268
115°	450	549	1258	2505	2843	445
125°	621	708	1141	1931	2262	554
135°	749	831	1109	1562	1767	578
145°	866	925	1092	1330	1433	543
155°	980	1012	1085	1196	1230	450
165°	1060	1073	1090	1135	1141	299
175°	1097	1099	1092	1106	1104	104
180°	1097	1097	1097	1097	1097	

TEST NUMBER: P563429

CATALOG NUMBER: SQ4-PP3-075U-100D-930-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3560.7	3560.7	3560.7	3560.7	3560.7
2.5°	3583.2	3553.9	3560.7	3555.4	3540.7
5°	3573.2	3539.6	3551.3	3538.8	3538.8
7.5°	3548.8	3512.2	3523.9	3511.4	3510.8
10°	3526.4	3489.7	3501.4	3488.8	3485.8
12.5°	3493.9	3457.3	3471.4	3456.4	3455.8
15°	3435.9	3402.3	3417.1	3404.5	3398.4
17.5°	3370.3	3333.7	3351.6	3334.1	3331.6
20°	3320.4	3283.8	3301.7	3276.7	3276.7
22.5°	3260.5	3223.9	3244.3	3211.8	3211.8
25°	3164.4	3127.7	3142.5	3114.4	3111.3
27.5°	3050.1	3014.1	3029.5	2997.7	2997.1
30°	2967.8	2934.2	2952.2	2917.8	2914.7
32.5°	2877.9	2846.8	2859.8	2825.4	2822.3
35°	2733.7	2706.2	2715.0	2683.7	2680.7
37.5°	2582.0	2554.0	2563.9	2537.1	2535.9
40°	2474.7	2456.4	2459.1	2437.1	2431.0
42.5°	2374.8	2354.1	2356.7	2334.9	2333.6
45°	2221.9	2206.7	2206.3	2184.5	2184.5
47.5°	2059.6	2048.0	2044.7	2026.6	2025.9
50°	1947.3	1938.1	1934.8	1919.1	1916.1
52.5°	1830.0	1825.7	1815.0	1801.9	1801.3
55°	1647.7	1641.6	1625.9	1616.4	1613.4
57.5°	1449.9	1437.7	1419.9	1406.2	1408.7
60°	1307.6	1295.4	1270.1	1263.9	1263.9
62.5°	1170.3	1155.6	1130.3	1121.7	1126.6
65°	973.6	955.3	933.1	926.9	930.0
67.5°	795.1	778.7	754.6	754.5	752.1
70°	680.3	671.2	652.2	652.2	652.2
72.5°	577.9	573.7	559.8	559.8	557.4
75°	443.1	443.1	436.9	433.7	430.7
77.5°	332.0	333.3	330.2	326.9	321.4
80°	262.1	268.2	265.3	262.1	259.0
82.5°	197.2	203.3	202.8	197.2	196.6
85°	103.0	112.1	112.3	112.3	112.3
87.5°	27.9	39.1	43.2	44.2	46.6
90°	2.3	9.2	16.3	21.0	21.0
92.5°	32.2	137.7	238.6	91.6	75.2
95°	77.0	282.4	915.0	391.3	249.8
97.5°	125.6	313.2	1396.3	1075.9	759.1
100°	161.1	332.2	1547.6	1562.0	1274.5
102.5°	194.7	354.9	1586.8	1937.9	1674.1
105°	254.4	391.4	1568.6	2388.9	2229.1
107.5°	311.4	436.5	1479.4	2609.8	2657.2
110°	352.5	466.6	1412.2	2664.7	2829.0



TEST NUMBER: P563429

CATALOG NUMBER: SQ4-PP3-075U-100D-930-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	389.8	500.3	1345.0	2629.3	2879.5
115°	450.5	548.6	1258.1	2505.3	2843.0
117.5°	508.4	598.8	1203.0	2331.2	2713.3
120°	543.9	630.6	1178.8	2200.8	2595.6
122.5°	575.6	662.3	1162.0	2086.4	2461.2
125°	620.9	707.6	1141.4	1930.9	2261.8
127.5°	663.8	746.5	1127.9	1801.1	2091.4
130°	686.3	770.7	1120.4	1724.0	1988.7
132.5°	712.4	796.8	1114.8	1656.2	1895.4
135°	749.3	831.4	1108.7	1561.6	1767.0
137.5°	783.8	860.0	1103.6	1485.1	1654.5
140°	810.0	880.7	1101.7	1434.3	1587.2
142.5°	832.4	897.6	1098.0	1389.0	1520.0
145°	866.0	925.3	1092.4	1330.5	1433.2
147.5°	901.9	953.1	1089.6	1278.7	1360.8
150°	924.3	970.0	1087.7	1250.2	1314.1
152.5°	944.9	986.9	1085.9	1225.7	1278.7
155°	980.4	1012.3	1085.4	1195.9	1230.1
157.5°	1006.0	1032.1	1085.4	1171.4	1195.1
160°	1024.7	1045.2	1085.4	1158.2	1176.4
162.5°	1039.6	1056.5	1087.3	1146.9	1161.5
165°	1059.7	1073.4	1090.1	1134.6	1141.4
167.5°	1073.7	1084.2	1092.4	1124.2	1126.0
170°	1083.1	1089.9	1092.4	1120.4	1120.4
172.5°	1090.5	1093.7	1092.4	1114.8	1112.9
175°	1097.1	1099.3	1092.4	1106.4	1104.1
177.5°	1098.9	1098.9	1091.5	1102.6	1098.9
180°	1097.1	1097.1	1097.1	1097.1	1097.1

(END OF REPORT)