

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563645

Luminaire Tested: **SQ4-PP3-100U-125D-930-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563645  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-100U-125D-930-1D-UNV-STD-W-12  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 1000 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 21221.0 lumens  
Efficiency: N/A  
Efficacy: 98.8 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 214.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563645  
CATALOG NUMBER: SQ4-PP3-100U-125D-930-1D-UNV-STD-W-12

### Luminous Intensity Polar Plot





TEST NUMBER: P563645

CATALOG NUMBER: SQ4-PP3-100U-125D-930-1D-UNV-STD-W-12

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	52	47
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	48	46	44	39
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	37	34
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32	29
5	69	58	50	44	64	54	47	41	47	41	37	40	36	33	34	31	28	25
6	64	52	44	38	59	49	41	36	42	37	32	37	32	29	31	28	25	22
7	59	47	39	33	55	44	37	32	38	33	28	33	29	25	28	25	22	20
8	55	43	35	29	51	40	33	28	35	29	25	30	26	23	26	22	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	23	20	24	21	18	16
10	48	36	28	24	44	34	27	23	30	24	20	26	21	18	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13974	13974	13974
5°	14077	13991	13942
10°	14053	13953	13891
15°	13960	13884	13808
20°	13868	13790	13685
25°	13703	13608	13473
30°	13449	13378	13209
35°	13097	13008	12843
40°	12678	12598	12455
45°	12332	12246	12124
50°	11889	11813	11699
55°	11274	11125	11039
60°	10263	9969	9921
65°	9042	8665	8636
70°	7807	7484	7484
75°	6720	6624	6531
80°	5924	5995	5853
85°	4637	5060	5060



TEST NUMBER: P563645

CATALOG NUMBER: SQ4-PP3-100U-125D-930-1D-UNV-STD-W-12

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	429.7	2.0
10°-20°	1226.9	5.8
20°-30°	1837.7	8.7
30°-40°	2155.5	10.2
40°-50°	2162.2	10.2
50°-60°	1844.5	8.7
60°-70°	1202.9	5.7
70°-80°	603.5	2.8
80°-90°	170.1	0.8
90°-100°	691.1	3.3
100°-110°	1907.8	9.0
110°-120°	1967.5	9.3
120°-130°	1581.1	7.5
130°-140°	1242.6	5.9
140°-150°	953.0	4.5
150°-160°	684.9	3.2
160°-170°	418.9	2.0
170°-180°	141.2	0.7
0°-30°	3494.2	16.5
0°-40°	5649.7	26.6
0°-60°	9656.4	45.5
0°-90°	11633.0	54.8
90°-120°	4566.4	21.5
90°-150°	8343.0	39.3
90°-180°	9588.0	45.2
0°-180°	21221.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	4544	4544	4544	4544	4544	
5°	4560	4517	4532	4516	4516	433
15°	4385	4342	4361	4345	4337	1237
25°	4038	3991	4010	3974	3970	1857
35°	3489	3454	3465	3425	3421	2179
45°	2836	2816	2816	2788	2788	2183
55°	2103	2095	2075	2063	2059	1869
65°	1242	1219	1191	1183	1187	1240
75°	566	566	558	554	550	613
85°	131	143	143	143	143	155
90°	5	9	19	21	24	12
95°	102	374	1254	515	335	109
105°	340	525	2099	3204	3017	362
115°	609	736	1690	3347	3806	599
125°	836	951	1532	2593	3043	744
135°	1006	1114	1490	2100	2368	778
145°	1166	1247	1471	1788	1924	730
155°	1315	1359	1459	1604	1655	606
165°	1424	1442	1466	1523	1535	401
175°	1476	1478	1469	1490	1485	140
180°	1476	1476	1476	1476	1476	

TEST NUMBER: P563645

CATALOG NUMBER: SQ4-PP3-100U-125D-930-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	4543.9	4543.9	4543.9	4543.9	4543.9
2.5°	4572.6	4535.2	4543.9	4537.1	4518.4
5°	4559.8	4517.0	4532.0	4516.0	4516.0
7.5°	4528.8	4482.1	4496.9	4481.0	4480.2
10°	4500.1	4453.4	4468.2	4452.2	4448.3
12.5°	4458.7	4412.0	4430.0	4410.9	4410.1
15°	4384.6	4341.8	4360.7	4344.6	4336.8
17.5°	4301.0	4254.3	4277.1	4254.7	4251.6
20°	4237.3	4190.5	4213.4	4181.5	4181.5
22.5°	4160.8	4114.1	4140.1	4098.7	4098.7
25°	4038.1	3991.4	4010.3	3974.3	3970.4
27.5°	3892.4	3846.4	3866.1	3825.5	3824.7
30°	3787.3	3744.4	3767.3	3723.5	3719.6
32.5°	3672.6	3632.8	3649.5	3605.6	3601.7
35°	3488.6	3453.5	3464.7	3424.8	3420.9
37.5°	3295.0	3259.2	3271.9	3237.7	3236.1
40°	3158.0	3134.7	3138.1	3110.1	3102.3
42.5°	3030.6	3004.1	3007.5	2979.6	2978.0
45°	2835.5	2816.0	2815.6	2787.7	2787.7
47.5°	2628.4	2613.6	2609.3	2586.1	2585.4
50°	2485.0	2473.3	2469.1	2449.1	2445.2
52.5°	2335.3	2329.8	2316.2	2299.4	2298.6
55°	2102.7	2094.9	2074.8	2062.8	2058.9
57.5°	1850.2	1834.6	1812.0	1794.5	1797.7
60°	1668.6	1653.0	1620.8	1612.9	1612.9
62.5°	1493.4	1474.7	1442.4	1431.4	1437.6
65°	1242.5	1219.1	1190.7	1182.9	1186.8
67.5°	1014.7	993.7	962.9	962.9	959.8
70°	868.2	856.5	832.3	832.3	832.3
72.5°	737.5	732.1	714.4	714.4	711.3
75°	565.5	565.5	557.5	553.5	549.6
77.5°	423.7	425.3	421.3	417.2	410.2
80°	334.5	342.3	338.5	334.4	330.5
82.5°	251.7	259.5	258.9	251.7	250.9
85°	131.4	143.1	143.4	143.4	143.4
87.5°	36.0	49.4	54.8	55.3	58.9
90°	4.7	9.3	18.9	21.3	23.6
92.5°	42.5	176.4	315.4	115.1	89.7
95°	101.5	373.9	1253.7	515.3	335.3
97.5°	168.1	418.8	1857.2	1429.9	1035.6
100°	217.2	445.8	2080.1	2094.8	1702.3
102.5°	264.4	476.4	2123.5	2588.2	2216.1
105°	340.0	524.7	2099.0	3204.4	3017.4
107.5°	420.3	584.6	1981.9	3501.6	3569.9
110°	476.9	624.7	1891.2	3565.5	3787.1



TEST NUMBER: P563645

CATALOG NUMBER: SQ4-PP3-100U-125D-930-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	527.9	670.1	1806.2	3515.0	3841.9
115°	609.1	736.1	1690.5	3346.6	3806.0
117.5°	680.0	806.5	1614.5	3109.6	3632.2
120°	727.2	851.9	1584.3	2949.1	3475.5
122.5°	772.5	891.7	1559.7	2799.3	3297.9
125°	835.8	951.2	1532.3	2593.2	3043.4
127.5°	889.6	1005.1	1516.3	2419.0	2807.3
130°	925.5	1041.0	1508.7	2312.4	2665.6
132.5°	959.5	1069.4	1501.2	2222.9	2542.8
135°	1005.8	1114.3	1489.8	2100.3	2368.1
137.5°	1057.7	1156.6	1484.2	1997.4	2226.0
140°	1086.1	1183.0	1480.4	1928.8	2129.7
142.5°	1118.2	1207.8	1476.6	1867.8	2044.7
145°	1166.4	1247.2	1470.9	1788.0	1924.3
147.5°	1212.6	1283.3	1465.7	1720.8	1826.5
150°	1246.6	1304.3	1463.8	1680.6	1766.1
152.5°	1273.1	1327.1	1462.0	1646.3	1717.0
155°	1315.1	1359.0	1459.1	1604.3	1655.1
157.5°	1353.8	1387.5	1459.6	1573.7	1608.3
160°	1376.5	1406.5	1461.5	1556.5	1581.9
162.5°	1395.4	1421.7	1463.4	1541.3	1561.1
165°	1423.7	1442.2	1466.2	1523.1	1534.7
167.5°	1445.4	1456.5	1468.6	1512.1	1515.8
170°	1456.8	1466.0	1468.6	1506.3	1506.3
172.5°	1466.2	1471.7	1468.6	1498.7	1496.9
175°	1475.7	1478.0	1468.6	1489.7	1485.1
177.5°	1479.4	1477.6	1468.1	1481.2	1477.5
180°	1475.7	1475.7	1475.7	1475.7	1475.7

(END OF REPORT)