

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519682

Luminaire Tested: **SQ4-050U-0D-930-1D-UNV-STD-W-8**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519682
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-050U-0D-930-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3170.1 lumens
Efficiency: N/A
Efficacy: 133.8 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Indirect

Input Watts (W): 23.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519682
CATALOG NUMBER: SQ4-050U-0D-930-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P519682

CATALOG NUMBER: SQ4-050U-0D-930-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20	
RC	80								50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	1815	21484	6283
100°	1907	18291	14972
105°	2003	12411	17781
110°	2127	8443	16951
115°	2181	6083	13786
120°	2218	4811	10587
125°	2210	4056	8061
130°	2185	3563	6308
135°	2159	3198	5093
140°	2153	2933	4221
145°	2154	2726	3561
150°	2187	2570	3094
155°	2201	2447	2765
160°	2222	2360	2560
165°	2237	2304	2408
170°	2245	2267	2318
175°	2248	2241	2263



TEST NUMBER: P519682

CATALOG NUMBER: SQ4-050U-0D-930-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	233.1	7.4
100°-110°	633.2	20.0
110°-120°	651.0	20.5
120°-130°	520.5	16.4
130°-140°	409.0	12.9
140°-150°	313.6	9.9
150°-160°	225.5	7.1
160°-170°	137.9	4.4
170°-180°	46.5	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	1517.2	47.9
90°-150°	2760.3	87.1
90°-180°	3170.0	100.0
0°-180°	3170.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	2	6	11	14	14	
95°	34	128	406	177	119	39
105°	112	175	696	1060	998	119
115°	200	243	557	1109	1263	197
125°	275	313	504	850	1002	245
135°	331	368	490	692	781	256
145°	382	410	484	588	632	240
155°	432	448	481	528	543	199
165°	468	474	482	503	504	132
175°	486	487	484	490	489	46
180°	486	486	486	486	486	

TEST NUMBER: P519682

CATALOG NUMBER: SQ4-050U-0D-930-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	1.6	6.1	10.9	14.1	14.1
92.5°	14.1	63.8	110.8	47.6	40.3
95°	34.3	127.5	405.9	176.7	118.7
97.5°	56.8	140.8	622.3	484.1	340.0
100°	71.8	149.7	688.5	697.9	563.6
102.5°	86.8	158.5	706.0	863.1	744.7
105°	112.4	175.0	696.3	1060.2	997.6
107.5°	138.9	194.2	656.0	1161.9	1179.3
110°	157.7	208.1	626.0	1182.0	1256.8
112.5°	173.9	221.8	596.1	1165.3	1278.0
115°	199.8	242.6	557.3	1108.8	1263.0
117.5°	224.2	265.1	532.7	1028.7	1202.4
120°	240.4	280.1	521.4	975.0	1147.5
122.5°	254.2	293.8	513.9	921.1	1087.5
125°	274.8	312.9	504.3	849.6	1002.3
127.5°	293.2	331.0	499.0	795.4	926.4
130°	304.4	341.1	496.5	761.4	878.9
132.5°	315.7	352.3	494.0	732.4	836.5
135°	331.0	367.6	490.2	692.1	780.6
137.5°	347.5	380.8	488.3	656.5	730.9
140°	357.5	389.6	487.1	633.8	701.0
142.5°	367.5	397.1	485.8	616.1	672.2
145°	382.5	410.0	484.0	588.0	632.3
147.5°	399.4	422.9	482.4	565.9	600.7
150°	410.6	430.4	482.4	553.3	580.8
152.5°	419.3	436.7	481.2	541.9	564.5
155°	432.4	447.7	480.8	528.0	543.3
157.5°	445.3	457.2	480.8	518.6	530.2
160°	452.7	463.4	480.8	512.3	521.4
162.5°	460.2	468.5	482.1	507.2	513.9
165°	468.4	474.5	482.4	502.7	504.3
167.5°	476.8	479.8	484.0	497.4	498.6
170°	479.3	482.3	484.0	494.9	494.9
172.5°	481.8	483.6	484.0	492.4	492.4
175°	485.5	487.1	484.0	490.2	488.7
177.5°	486.8	486.8	483.0	488.0	485.5
180°	485.5	485.5	485.5	485.5	485.5

(END OF REPORT)