

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563789

Luminaire Tested: **SQ4-PP3-150U-075D-930-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563789
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-150U-075D-930-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 21244.3 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 194.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563789
CATALOG NUMBER: SQ4-PP3-150U-075D-930-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P563789

CATALOG NUMBER: SQ4-PP3-150U-075D-930-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	32
1	94	90	86	83	84	81	78	75	65	62	60	49	48	47	35	35	34	27
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	30	29	23
3	78	69	62	56	70	62	56	52	50	46	42	38	36	33	28	26	25	20
4	71	61	53	48	64	55	49	44	44	40	36	34	31	28	25	23	21	17
5	65	54	46	41	59	49	42	37	40	35	31	31	27	25	22	20	18	15
6	60	49	41	35	54	44	37	32	36	31	27	28	24	21	20	18	16	13
7	56	44	36	31	50	40	33	28	32	27	24	25	22	19	19	16	14	12
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13	10
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	13	12	9
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8241	8241	8241
5°	8302	8251	8222
10°	8288	8229	8193
15°	8233	8188	8143
20°	8179	8133	8071
25°	8081	8026	7946
30°	7932	7890	7790
35°	7724	7671	7574
40°	7477	7430	7345
45°	7273	7222	7151
50°	7012	6967	6900
55°	6649	6561	6511
60°	6053	5880	5851
65°	5333	5110	5093
70°	4604	4414	4414
75°	3963	3907	3851
80°	3494	3535	3452
85°	2735	2985	2985



TEST NUMBER: P563789

CATALOG NUMBER: SQ4-PP3-150U-075D-930-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	253.4	1.2
10°-20°	723.6	3.4
20°-30°	1083.8	5.1
30°-40°	1271.2	6.0
40°-50°	1275.2	6.0
50°-60°	1087.8	5.1
60°-70°	709.5	3.3
70°-80°	355.9	1.7
80°-90°	103.2	0.5
90°-100°	1036.6	4.9
100°-110°	2802.7	13.2
110°-120°	2946.7	13.9
120°-130°	2393.5	11.3
130°-140°	1877.5	8.8
140°-150°	1441.0	6.8
150°-160°	1036.3	4.9
160°-170°	633.1	3.0
170°-180°	213.4	1.0
0°-30°	2060.7	9.7
0°-40°	3331.9	15.7
0°-60°	5695.0	26.8
0°-90°	6863.5	32.3
90°-120°	6786.0	31.9
90°-150°	12497.9	58.8
90°-180°	14381.0	67.7
0°-180°	21244.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2680	2680	2680	2680	2680	
5°	2689	2664	2673	2663	2663	255
15°	2586	2561	2572	2562	2558	730
25°	2382	2354	2365	2344	2342	1095
35°	2057	2037	2043	2020	2018	1285
45°	1672	1661	1660	1644	1644	1288
55°	1240	1236	1224	1217	1214	1102
65°	733	719	702	698	700	731
75°	334	334	329	326	324	362
85°	78	84	85	85	85	91
90°	5	14	31	34	31	14
95°	161	565	1724	892	531	168
105°	521	805	3109	4586	4398	549
115°	917	1121	2579	4992	5635	906
125°	1256	1439	2324	3922	4607	1119
135°	1505	1684	2262	3167	3585	1163
145°	1750	1882	2230	2711	2917	1095
155°	1976	2054	2211	2432	2511	911
165°	2151	2172	2221	2308	2319	606
175°	2233	2230	2223	2252	2247	212
180°	2230	2230	2230	2230	2230	



TEST NUMBER: P563789

CATALOG NUMBER: SQ4-PP3-150U-075D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2679.8	2679.8	2679.8	2679.8	2679.8
2.5°	2696.7	2674.7	2679.8	2675.8	2664.8
5°	2689.2	2664.0	2672.8	2663.4	2663.4
7.5°	2670.9	2643.3	2652.1	2642.7	2642.2
10°	2654.0	2626.4	2635.2	2625.8	2623.5
12.5°	2629.6	2602.0	2612.7	2601.4	2600.9
15°	2585.9	2560.6	2571.8	2562.3	2557.7
17.5°	2536.6	2509.0	2522.5	2509.3	2507.4
20°	2499.0	2471.4	2484.9	2466.1	2466.1
22.5°	2453.9	2426.3	2441.7	2417.2	2417.2
25°	2381.5	2354.0	2365.1	2343.9	2341.6
27.5°	2295.6	2268.5	2280.1	2256.1	2255.7
30°	2233.6	2208.3	2221.8	2195.9	2193.6
32.5°	2165.9	2142.5	2152.3	2126.4	2124.1
35°	2057.4	2036.8	2043.3	2019.8	2017.5
37.5°	1943.3	1922.2	1929.7	1909.4	1908.5
40°	1862.5	1848.7	1850.7	1834.2	1829.6
42.5°	1787.3	1771.7	1773.7	1757.2	1756.3
45°	1672.2	1660.8	1660.5	1644.1	1644.1
47.5°	1550.1	1541.4	1538.8	1525.2	1524.8
50°	1465.6	1458.7	1456.2	1444.4	1442.1
52.5°	1377.3	1374.0	1366.0	1356.1	1355.6
55°	1240.1	1235.5	1223.7	1216.6	1214.3
57.5°	1091.2	1082.0	1068.6	1058.3	1060.2
60°	984.1	974.9	955.9	951.2	951.2
62.5°	880.7	869.7	850.7	844.2	847.9
65°	732.8	719.0	702.2	697.6	699.9
67.5°	598.4	586.0	567.9	567.9	566.0
70°	512.0	505.1	490.9	490.9	490.9
72.5°	435.0	431.8	421.3	421.3	419.5
75°	333.5	333.5	328.8	326.4	324.1
77.5°	249.9	250.8	248.5	246.0	241.9
80°	197.3	201.9	199.6	197.2	194.9
82.5°	148.4	153.0	152.7	148.4	148.0
85°	77.5	84.4	84.6	84.6	84.6
87.5°	21.6	30.9	36.3	36.8	38.2
90°	4.8	14.2	31.2	33.6	31.2
92.5°	68.2	248.5	490.3	212.8	154.1
95°	160.9	564.7	1723.9	892.1	530.6
97.5°	258.3	647.6	2687.1	2223.8	1633.1
100°	331.3	681.1	2986.8	3114.9	2518.6
102.5°	398.6	727.7	3092.4	3790.6	3344.5
105°	521.0	805.1	3109.2	4586.4	4398.5
107.5°	634.3	893.5	2973.3	5082.8	5145.2
110°	722.7	957.4	2852.3	5216.1	5481.4



TEST NUMBER: P563789

CATALOG NUMBER: SQ4-PP3-150U-075D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	801.4	1021.2	2740.9	5189.5	5635.0
115°	917.2	1121.4	2578.6	4991.8	5635.0
117.5°	1030.5	1222.1	2471.5	4689.8	5419.0
120°	1099.6	1287.4	2408.2	4473.1	5217.3
122.5°	1164.9	1349.0	2369.7	4240.8	4990.6
125°	1255.7	1438.8	2324.1	3921.9	4607.4
127.5°	1339.3	1519.1	2297.2	3661.7	4264.6
130°	1385.4	1570.8	2285.7	3501.0	4045.6
132.5°	1433.4	1617.0	2274.2	3355.9	3857.4
135°	1505.4	1683.8	2261.7	3166.8	3584.6
137.5°	1577.9	1746.5	2251.1	3013.2	3353.7
140°	1627.8	1785.1	2247.3	2914.4	3217.3
142.5°	1675.9	1823.8	2239.6	2825.2	3090.5
145°	1750.3	1881.8	2230.5	2710.6	2917.2
147.5°	1818.0	1934.4	2219.9	2606.7	2765.4
150°	1867.9	1971.2	2216.1	2550.3	2677.1
152.5°	1914.0	2004.2	2214.2	2497.9	2602.2
155°	1976.0	2053.5	2211.3	2431.6	2511.4
157.5°	2040.3	2094.3	2211.8	2385.3	2437.9
160°	2076.8	2121.4	2213.7	2356.2	2393.8
162.5°	2105.6	2142.7	2215.6	2332.9	2361.1
165°	2151.3	2172.4	2220.9	2307.6	2319.3
167.5°	2182.5	2197.0	2221.4	2285.8	2291.5
170°	2201.7	2208.7	2223.3	2276.1	2276.1
172.5°	2217.0	2218.4	2223.3	2264.5	2262.7
175°	2232.9	2230.5	2223.3	2252.0	2247.3
177.5°	2238.2	2232.5	2222.8	2241.9	2236.2
180°	2230.5	2230.5	2230.5	2230.5	2230.5

(END OF REPORT)