

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: CORELITE

Report Number: P563885

Luminaire Tested: **SQ4-PR1-025U-075D-930-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563885  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PR1-025U-075D-930-1D-UNV-STD-W-12  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9126.1 lumens  
Efficiency: N/A  
Efficacy: 96.3 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35  
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 94.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563885

CATALOG NUMBER: SQ4-PR1-025U-075D-930-1D-UNV-STD-W-12

### Luminous Intensity Polar Plot





TEST NUMBER: P563885

CATALOG NUMBER: SQ4-PR1-025U-075D-930-1D-UNV-STD-W-12

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	113	113	113	113	107	107	107	107	97	97	97	88	88	88	79	79	79	75				
1	104	99	96	92	99	95	91	88	86	83	81	78	76	74	70	69	67	64				
2	95	87	81	76	90	83	78	73	76	71	68	69	65	62	62	60	58	54				
3	87	77	70	64	82	74	67	62	67	62	57	61	57	53	56	52	49	46				
4	80	69	61	54	76	66	58	53	60	54	49	55	50	46	50	46	43	40				
5	73	62	53	47	70	59	51	46	54	48	43	50	44	40	45	41	38	35				
6	68	55	47	41	64	53	46	40	49	43	38	45	40	35	41	37	33	31				
7	63	50	42	36	60	48	41	35	45	38	33	41	36	32	38	33	30	27				
8	58	46	38	32	56	44	37	32	41	34	30	38	32	28	35	30	27	25				
9	55	42	34	29	52	40	33	28	37	31	27	35	29	26	32	27	24	22				
10	51	39	31	26	49	37	30	26	35	29	24	32	27	23	30	25	22	20				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8388	8388	8388
5°	8463	8398	8355
10°	8437	8378	8334
15°	8400	8347	8302
20°	8357	8303	8242
25°	8298	8243	8147
30°	8209	8151	8034
35°	8088	8017	7903
40°	7903	7819	7677
45°	7581	7449	7295
50°	7014	6845	6710
55°	6122	5983	5857
60°	5159	5115	5014
65°	4462	4479	4445
70°	4098	4119	4119
75°	3935	3935	3964
80°	3703	3744	3703
85°	2985	3317	3317



TEST NUMBER: P563885

CATALOG NUMBER: SQ4-PR1-025U-075D-930-1D-UNV-STD-W-12

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	257.9	2.8
10°-20°	737.9	8.1
20°-30°	1113.0	12.2
30°-40°	1326.2	14.5
40°-50°	1307.5	14.3
50°-60°	999.3	10.9
60°-70°	618.4	6.8
70°-80°	351.2	3.8
80°-90°	108.8	1.2
90°-100°	173.4	1.9
100°-110°	455.8	5.0
110°-120°	472.7	5.2
120°-130°	379.1	4.2
130°-140°	297.5	3.3
140°-150°	228.3	2.5
150°-160°	164.5	1.8
160°-170°	100.6	1.1
170°-180°	34.0	0.4
0°-30°	2108.9	23.1
0°-40°	3435.1	37.6
0°-60°	5741.8	62.9
0°-90°	6820.2	74.7
90°-120°	1101.9	12.1
90°-150°	2006.9	22.0
90°-180°	2306.0	25.3
0°-180°	9126.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2727	2727	2727	2727	2727	
5°	2742	2712	2720	2711	2706	260
15°	2638	2611	2622	2612	2608	744
25°	2446	2416	2429	2403	2401	1125
35°	2154	2129	2135	2107	2105	1344
45°	1743	1720	1713	1682	1677	1335
55°	1142	1123	1116	1097	1092	1023
65°	613	609	616	611	611	621
75°	331	331	331	334	334	350
85°	85	89	94	94	94	98
90°	2	7	18	9	9	5
95°	23	90	299	154	105	25
105°	82	124	504	765	714	87
115°	146	177	404	805	919	144
125°	203	228	367	621	732	180
135°	242	266	356	501	568	187
145°	280	298	351	427	461	176
155°	317	326	351	386	397	146
165°	342	346	351	365	369	97
175°	356	356	354	358	358	34
180°	356	356	356	356	356	

TEST NUMBER: P563885

CATALOG NUMBER: SQ4-PR1-025U-075D-930-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2727.4	2727.4	2727.4	2727.4	2727.4
2.5°	2744.3	2720.5	2727.4	2721.5	2708.6
5°	2741.5	2711.7	2720.4	2710.9	2706.3
7.5°	2720.4	2691.0	2699.7	2690.3	2687.5
10°	2701.6	2674.0	2682.8	2673.3	2668.7
12.5°	2680.9	2651.5	2662.1	2650.7	2646.2
15°	2638.2	2610.6	2621.7	2612.2	2607.6
17.5°	2591.2	2561.8	2572.9	2561.9	2555.9
20°	2553.6	2526.0	2537.1	2520.7	2518.4
22.5°	2512.2	2484.7	2495.8	2473.7	2473.3
25°	2445.5	2415.7	2429.1	2403.2	2400.9
27.5°	2366.1	2338.6	2349.7	2323.3	2320.6
30°	2311.6	2284.1	2295.2	2266.9	2262.3
32.5°	2249.6	2223.9	2233.2	2204.9	2202.2
35°	2154.2	2129.0	2135.4	2107.2	2104.9
37.5°	2045.7	2022.7	2026.4	1995.4	1993.1
40°	1968.6	1945.7	1947.5	1914.6	1912.3
42.5°	1884.1	1861.1	1859.2	1826.2	1823.9
45°	1743.1	1720.1	1712.6	1681.9	1677.3
47.5°	1582.4	1559.5	1545.3	1520.3	1517.1
50°	1465.9	1442.9	1430.7	1409.4	1402.5
52.5°	1340.0	1317.0	1306.6	1287.2	1280.3
55°	1141.7	1123.3	1115.9	1097.0	1092.4
57.5°	953.3	940.9	938.7	920.4	918.5
60°	838.7	831.8	831.6	815.2	815.2
62.5°	740.9	735.9	739.5	728.7	726.8
65°	613.1	608.6	615.5	610.8	610.8
67.5°	512.1	512.1	516.4	514.5	514.5
70°	455.7	455.7	458.1	458.1	458.1
72.5°	405.0	403.2	409.2	409.2	407.4
75°	331.2	331.2	331.2	333.6	333.6
77.5°	257.9	258.4	260.3	259.8	257.9
80°	209.1	211.4	211.4	209.1	209.1
82.5°	160.2	162.5	162.6	162.1	160.2
85°	84.6	89.2	94.0	94.0	94.0
87.5°	24.9	33.1	41.2	39.4	37.5
90°	2.3	6.7	18.2	9.1	9.1
92.5°	9.6	46.1	102.2	45.2	29.2
95°	22.8	89.7	298.7	154.0	104.9
97.5°	39.7	98.5	447.0	355.5	261.8
100°	52.5	106.0	492.6	499.2	387.7
102.5°	63.4	113.3	505.4	621.8	526.3
105°	82.1	124.5	504.0	765.1	713.8
107.5°	101.3	140.5	475.3	839.5	852.0
110°	114.0	149.7	451.5	858.7	912.2

TEST NUMBER: P563885

CATALOG NUMBER: SQ4-PR1-025U-075D-930-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	126.8	160.7	429.7	846.6	928.6
115°	146.0	177.2	403.7	805.3	919.1
117.5°	164.7	193.2	385.9	748.1	874.4
120°	175.6	202.4	378.6	709.7	832.4
122.5°	186.5	213.3	373.1	671.4	792.3
125°	203.0	227.5	367.2	620.6	732.0
127.5°	216.2	241.2	362.1	579.6	673.7
130°	223.5	250.2	360.3	553.9	640.8
132.5°	230.8	257.5	358.5	531.8	609.8
135°	241.7	266.3	355.8	501.0	567.9
137.5°	253.1	277.2	355.3	477.9	532.7
140°	262.3	284.6	353.5	459.6	510.8
142.5°	269.6	290.1	353.5	446.6	490.8
145°	280.5	298.3	351.2	427.2	460.7
147.5°	291.5	308.8	351.2	411.1	438.8
150°	298.7	314.4	351.2	401.9	424.2
152.5°	306.0	318.1	351.2	394.5	411.4
155°	317.0	325.9	351.2	385.7	396.8
157.5°	325.2	333.7	351.2	377.8	385.9
160°	330.7	337.4	351.2	374.1	378.6
162.5°	336.1	341.1	351.2	370.5	374.9
165°	342.1	346.5	351.2	365.0	369.4
167.5°	347.6	349.8	353.5	362.6	364.4
170°	351.2	353.4	353.5	362.6	362.6
172.5°	353.0	353.5	353.5	360.7	359.0
175°	355.8	355.8	353.5	358.0	358.0
177.5°	355.8	355.8	353.9	357.5	355.8
180°	355.8	355.8	355.8	355.8	355.8

(END OF REPORT)