

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564317

Luminaire Tested: **SQ4-PR1-100U-125D-930-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564317
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-100U-125D-930-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 21152.1 lumens
Efficiency: N/A
Efficacy: 98.5 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 214.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564317
CATALOG NUMBER: SQ4-PR1-100U-125D-930-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P564317

CATALOG NUMBER: SQ4-PR1-100U-125D-930-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	55
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	52	47
2	91	83	77	72	84	78	72	68	67	63	60	57	54	52	48	46	44	40
3	83	73	66	60	77	69	62	57	59	54	50	51	47	44	43	40	38	34
4	76	65	57	51	70	61	54	49	53	47	43	45	41	38	38	35	33	29
5	70	58	50	44	65	54	47	42	47	42	37	41	36	33	35	31	29	26
6	64	52	44	38	60	49	42	37	43	37	33	37	32	29	31	28	25	23
7	60	47	39	34	55	44	37	32	39	33	29	34	29	26	29	25	23	20
8	55	43	35	30	51	40	33	29	35	30	26	31	26	23	26	23	20	18
9	51	39	32	27	48	37	30	26	33	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14222	14222	14222
5°	14351	14240	14166
10°	14305	14206	14131
15°	14242	14154	14078
20°	14171	14079	13975
25°	14071	13976	13814
30°	13919	13820	13622
35°	13714	13594	13400
40°	13401	13257	13017
45°	12855	12629	12370
50°	11892	11606	11377
55°	10380	10145	9931
60°	8746	8673	8502
65°	7565	7594	7537
70°	6949	6984	6984
75°	6673	6673	6721
80°	6278	6349	6278
85°	5060	5621	5621



TEST NUMBER: P564317

CATALOG NUMBER: SQ4-PR1-100U-125D-930-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	437.3	2.1
10°-20°	1251.2	5.9
20°-30°	1887.3	8.9
30°-40°	2248.7	10.6
40°-50°	2217.0	10.5
50°-60°	1694.3	8.0
60°-70°	1048.5	5.0
70°-80°	595.5	2.8
80°-90°	184.2	0.9
90°-100°	691.1	3.3
100°-110°	1907.8	9.0
110°-120°	1967.5	9.3
120°-130°	1581.1	7.5
130°-140°	1242.6	5.9
140°-150°	953.0	4.5
150°-160°	684.9	3.2
160°-170°	418.9	2.0
170°-180°	141.2	0.7
0°-30°	3575.8	16.9
0°-40°	5824.5	27.5
0°-60°	9735.9	46.0
0°-90°	11564.1	54.7
90°-120°	4566.4	21.6
90°-150°	8343.0	39.4
90°-180°	9588.0	45.3
0°-180°	21152.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4625	4625	4625	4625	4625	
5°	4648	4598	4613	4597	4589	441
15°	4473	4426	4445	4429	4422	1262
25°	4147	4096	4119	4075	4071	1908
35°	3653	3610	3621	3573	3569	2280
45°	2956	2917	2904	2852	2844	2264
55°	1936	1905	1892	1860	1852	1735
65°	1040	1032	1044	1036	1036	1053
75°	562	562	562	566	566	593
85°	143	151	159	159	159	167
90°	5	9	19	21	24	13
95°	102	374	1254	515	335	109
105°	340	525	2099	3204	3017	362
115°	609	736	1690	3347	3806	599
125°	836	951	1532	2593	3043	744
135°	1006	1114	1490	2100	2368	778
145°	1166	1247	1471	1788	1924	730
155°	1315	1359	1459	1604	1655	606
165°	1424	1442	1466	1523	1535	401
175°	1476	1478	1469	1490	1485	140
180°	1476	1476	1476	1476	1476	

TEST NUMBER: P564317

CATALOG NUMBER: SQ4-PR1-100U-125D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4624.6	4624.6	4624.6	4624.6	4624.6
2.5°	4653.3	4612.8	4624.6	4614.6	4592.8
5°	4648.5	4597.9	4612.7	4596.6	4588.8
7.5°	4612.7	4562.8	4577.6	4561.6	4556.9
10°	4580.8	4534.1	4549.0	4532.9	4525.1
12.5°	4545.8	4495.9	4513.9	4494.6	4486.8
15°	4473.3	4426.5	4445.4	4429.3	4421.5
17.5°	4393.6	4343.8	4362.5	4344.0	4333.9
20°	4329.9	4283.1	4302.0	4274.0	4270.1
22.5°	4259.8	4213.0	4231.9	4194.4	4193.6
25°	4146.6	4096.0	4118.8	4074.9	4071.0
27.5°	4012.0	3965.3	3984.1	3939.4	3934.7
30°	3919.6	3872.9	3891.7	3843.7	3835.9
32.5°	3814.4	3770.8	3786.6	3738.6	3734.0
35°	3652.7	3609.9	3620.8	3573.0	3569.1
37.5°	3468.7	3429.7	3436.0	3383.4	3379.5
40°	3338.0	3299.1	3302.2	3246.3	3242.4
42.5°	3194.6	3155.7	3152.4	3096.6	3092.7
45°	2955.6	2916.7	2903.8	2851.9	2844.1
47.5°	2683.2	2644.2	2620.2	2577.9	2572.4
50°	2485.6	2446.6	2425.8	2389.7	2378.0
52.5°	2272.1	2233.1	2215.5	2182.6	2170.9
55°	1935.9	1904.7	1892.1	1860.0	1852.2
57.5°	1616.4	1595.4	1591.7	1560.6	1557.5
60°	1422.0	1410.4	1410.1	1382.2	1382.2
62.5°	1256.3	1247.8	1254.0	1235.6	1232.4
65°	1039.6	1031.9	1043.6	1035.7	1035.7
67.5°	868.4	868.4	875.5	872.3	872.3
70°	772.8	772.8	776.7	776.7	776.7
72.5°	686.7	683.6	693.9	693.8	690.7
75°	561.6	561.6	561.6	565.6	565.6
77.5°	437.4	438.1	441.4	440.5	437.4
80°	354.5	358.4	358.5	354.5	354.5
82.5°	271.7	275.6	275.6	274.8	271.7
85°	143.4	151.2	159.3	159.3	159.3
87.5°	42.4	55.8	67.5	67.9	65.3
90°	4.7	9.3	18.9	21.3	23.6
92.5°	42.5	176.4	315.4	115.1	89.7
95°	101.5	373.9	1253.7	515.3	335.3
97.5°	168.1	418.8	1857.2	1429.9	1035.6
100°	217.2	445.8	2080.1	2094.8	1702.3
102.5°	264.4	476.4	2123.5	2588.2	2216.1
105°	340.0	524.7	2099.0	3204.4	3017.4
107.5°	420.3	584.6	1981.9	3501.6	3569.9
110°	476.9	624.7	1891.2	3565.5	3787.1



TEST NUMBER: P564317

CATALOG NUMBER: SQ4-PR1-100U-125D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	527.9	670.1	1806.2	3515.0	3841.9
115°	609.1	736.1	1690.5	3346.6	3806.0
117.5°	680.0	806.5	1614.5	3109.6	3632.2
120°	727.2	851.9	1584.3	2949.1	3475.5
122.5°	772.5	891.7	1559.7	2799.3	3297.9
125°	835.8	951.2	1532.3	2593.2	3043.4
127.5°	889.6	1005.1	1516.3	2419.0	2807.3
130°	925.5	1041.0	1508.7	2312.4	2665.6
132.5°	959.5	1069.4	1501.2	2222.9	2542.8
135°	1005.8	1114.3	1489.8	2100.3	2368.1
137.5°	1057.7	1156.6	1484.2	1997.4	2226.0
140°	1086.1	1183.0	1480.4	1928.8	2129.7
142.5°	1118.2	1207.8	1476.6	1867.8	2044.7
145°	1166.4	1247.2	1470.9	1788.0	1924.3
147.5°	1212.6	1283.3	1465.7	1720.8	1826.5
150°	1246.6	1304.3	1463.8	1680.6	1766.1
152.5°	1273.1	1327.1	1462.0	1646.3	1717.0
155°	1315.1	1359.0	1459.1	1604.3	1655.1
157.5°	1353.8	1387.5	1459.6	1573.7	1608.3
160°	1376.5	1406.5	1461.5	1556.5	1581.9
162.5°	1395.4	1421.7	1463.4	1541.3	1561.1
165°	1423.7	1442.2	1466.2	1523.1	1534.7
167.5°	1445.4	1456.5	1468.6	1512.1	1515.8
170°	1456.8	1466.0	1468.6	1506.3	1506.3
172.5°	1466.2	1471.7	1468.6	1498.7	1496.9
175°	1475.7	1478.0	1468.6	1489.7	1485.1
177.5°	1479.4	1477.6	1468.1	1481.2	1477.5
180°	1475.7	1475.7	1475.7	1475.7	1475.7

(END OF REPORT)