

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564389

Luminaire Tested: **SQ4-PR1-125U-100D-930-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564389
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-125U-100D-930-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 20998.6 lumens
Efficiency: N/A
Efficacy: 104.4 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 201.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564389
CATALOG NUMBER: SQ4-PR1-125U-100D-930-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P564389

CATALOG NUMBER: SQ4-PR1-125U-100D-930-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50	43
1	96	92	89	85	88	85	81	78	70	68	66	57	55	54	44	43	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	39	38	36	31
3	80	71	64	59	73	65	59	54	55	50	46	44	41	39	35	33	31	27
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	31	29	27	23
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	28	26	24	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	19	16
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17	14
9	50	38	30	25	45	35	28	24	30	25	21	25	21	18	20	17	15	13
10	46	35	27	23	42	32	26	21	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11145	11145	11145
5°	11246	11159	11101
10°	11210	11132	11073
15°	11160	11091	11032
20°	11105	11033	10951
25°	11026	10952	10825
30°	10907	10830	10674
35°	10746	10653	10500
40°	10501	10388	10200
45°	10073	9897	9693
50°	9319	9095	8916
55°	8134	7950	7783
60°	6854	6797	6662
65°	5929	5951	5906
70°	5445	5473	5473
75°	5229	5229	5266
80°	4920	4975	4920
85°	3966	4407	4407



TEST NUMBER: P564389

CATALOG NUMBER: SQ4-PR1-125U-100D-930-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	342.7	1.6
10°-20°	980.5	4.7
20°-30°	1478.9	7.0
30°-40°	1762.1	8.4
40°-50°	1737.3	8.3
50°-60°	1327.7	6.3
60°-70°	821.7	3.9
70°-80°	466.7	2.2
80°-90°	146.3	0.7
90°-100°	864.9	4.1
100°-110°	2329.7	11.1
110°-120°	2444.9	11.6
120°-130°	1984.0	9.4
130°-140°	1556.0	7.4
140°-150°	1194.6	5.7
150°-160°	858.9	4.1
160°-170°	524.8	2.5
170°-180°	177.0	0.8
0°-30°	2802.1	13.3
0°-40°	4564.2	21.7
0°-60°	7629.2	36.3
0°-90°	9063.8	43.2
90°-120°	5639.5	26.9
90°-150°	10374.1	49.4
90°-180°	11935.0	56.8
0°-180°	20998.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3624	3624	3624	3624	3624	
5°	3643	3603	3615	3602	3596	346
15°	3505	3469	3484	3471	3465	989
25°	3249	3210	3228	3193	3190	1495
35°	2862	2829	2837	2800	2797	1786
45°	2316	2286	2276	2235	2229	1774
55°	1517	1493	1483	1458	1452	1359
65°	815	809	818	812	812	825
75°	440	440	440	443	443	465
85°	112	118	125	125	125	131
90°	5	14	28	31	31	14
95°	132	470	1418	725	502	138
105°	431	670	2576	3855	3617	453
115°	761	931	2146	4146	4689	749
125°	1039	1193	1926	3256	3832	927
135°	1251	1396	1872	2627	2974	965
145°	1446	1559	1849	2246	2412	907
155°	1642	1701	1832	2015	2080	756
165°	1780	1801	1839	1912	1922	502
175°	1851	1849	1842	1868	1863	176
180°	1849	1849	1849	1849	1849	

TEST NUMBER: P564389

CATALOG NUMBER: SQ4-PR1-125U-100D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3624.0	3624.0	3624.0	3624.0	3624.0
2.5°	3646.4	3614.7	3624.0	3616.1	3599.0
5°	3642.7	3603.0	3614.6	3602.0	3595.9
7.5°	3614.6	3575.5	3587.1	3574.5	3570.9
10°	3589.6	3553.0	3564.6	3552.0	3545.9
12.5°	3562.1	3523.1	3537.2	3522.1	3515.9
15°	3505.3	3468.7	3483.5	3470.9	3464.8
17.5°	3442.9	3403.8	3418.6	3404.0	3396.1
20°	3393.0	3356.3	3371.1	3349.2	3346.1
22.5°	3338.0	3301.4	3316.2	3286.8	3286.2
25°	3249.4	3209.7	3227.5	3193.1	3190.1
27.5°	3143.9	3107.3	3122.0	3087.0	3083.3
30°	3071.5	3034.8	3049.6	3012.0	3005.9
32.5°	2989.1	2954.9	2967.2	2929.7	2926.0
35°	2862.3	2828.8	2837.4	2799.8	2796.8
37.5°	2718.1	2687.6	2692.5	2651.3	2648.2
40°	2615.7	2585.2	2587.6	2543.9	2540.8
42.5°	2503.4	2472.8	2470.3	2426.5	2423.5
45°	2316.1	2285.6	2275.5	2234.8	2228.7
47.5°	2102.6	2072.1	2053.3	2020.1	2015.8
50°	1947.8	1917.2	1900.9	1872.6	1863.5
52.5°	1780.4	1749.9	1736.1	1710.3	1701.2
55°	1517.0	1492.6	1482.7	1457.6	1451.5
57.5°	1266.7	1250.2	1247.3	1222.9	1220.5
60°	1114.3	1105.2	1105.0	1083.1	1083.1
62.5°	984.5	977.8	982.6	968.2	965.8
65°	814.7	808.6	817.8	811.6	811.6
67.5°	680.5	680.5	686.1	683.6	683.6
70°	605.6	605.6	608.7	608.7	608.7
72.5°	538.1	535.7	543.7	543.7	541.3
75°	440.1	440.1	440.1	443.2	443.2
77.5°	342.7	343.3	345.9	345.2	342.7
80°	277.8	280.9	280.9	277.8	277.8
82.5°	212.9	215.9	216.0	215.3	212.9
85°	112.4	118.5	124.9	124.9	124.9
87.5°	33.4	45.0	55.6	56.0	53.6
90°	4.7	13.9	28.3	30.6	30.6
92.5°	57.5	203.0	401.3	193.2	134.2
95°	131.9	470.4	1417.8	725.0	501.6
97.5°	210.5	538.5	2223.7	1857.7	1400.8
100°	270.8	565.6	2479.9	2594.7	2152.5
102.5°	329.2	603.7	2564.7	3146.6	2783.7
105°	431.0	670.5	2576.5	3854.6	3617.4
107.5°	527.1	740.8	2466.7	4218.4	4279.7
110°	591.1	793.8	2366.9	4331.4	4554.7

TEST NUMBER: P564389

CATALOG NUMBER: SQ4-PR1-125U-100D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	659.0	846.9	2270.8	4306.4	4673.4
115°	760.7	931.1	2145.5	4145.5	4689.0
117.5°	853.5	1013.3	2048.5	3888.8	4494.0
120°	913.8	1068.1	1999.5	3704.5	4326.3
122.5°	966.5	1119.0	1963.7	3516.1	4136.0
125°	1038.6	1192.9	1926.5	3256.0	3831.7
127.5°	1107.8	1259.8	1902.9	3026.7	3540.6
130°	1149.3	1301.3	1893.5	2895.2	3346.6
132.5°	1190.7	1340.9	1884.1	2779.5	3194.0
135°	1250.6	1395.6	1872.3	2626.8	2974.5
137.5°	1307.5	1446.6	1866.2	2497.2	2782.8
140°	1347.1	1480.7	1860.5	2417.5	2675.4
142.5°	1388.6	1512.9	1856.7	2343.1	2560.4
145°	1446.0	1558.9	1848.7	2245.8	2411.6
147.5°	1508.2	1606.3	1840.7	2164.0	2294.3
150°	1549.6	1634.8	1837.0	2112.6	2220.8
152.5°	1587.3	1661.5	1835.1	2070.7	2158.7
155°	1641.5	1701.4	1832.3	2015.1	2079.5
157.5°	1689.1	1735.6	1832.7	1976.0	2019.2
160°	1719.2	1758.4	1834.6	1953.1	1985.3
162.5°	1745.6	1777.4	1836.5	1934.0	1957.1
165°	1780.4	1801.2	1839.3	1912.5	1921.7
167.5°	1808.7	1820.7	1841.7	1895.9	1899.6
170°	1827.5	1832.2	1841.7	1886.4	1886.4
172.5°	1838.9	1839.8	1843.6	1877.0	1877.0
175°	1851.1	1848.8	1841.7	1867.5	1862.9
177.5°	1856.3	1852.6	1843.1	1858.1	1854.4
180°	1848.7	1848.7	1848.7	1848.7	1848.7

(END OF REPORT)