

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562664

Luminaire Tested: **SQ4-PC3-050U-100D-930-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562664
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-050U-100D-930-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9305.6 lumens
Efficiency: N/A
Efficacy: 97.5 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 95.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562664

CATALOG NUMBER: SQ4-PC3-050U-100D-930-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P562664

CATALOG NUMBER: SQ4-PC3-050U-100D-930-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66
1	101	97	93	90	95	91	88	85	81	78	76	72	70	68	63	61	60	56
2	92	85	78	73	87	80	74	70	71	67	63	63	60	57	55	53	51	47
3	84	75	67	61	79	70	64	58	63	57	53	56	51	48	49	46	43	39
4	77	66	58	52	72	62	55	49	56	50	45	49	45	41	44	40	37	34
5	71	59	50	44	66	56	48	42	50	44	39	44	39	36	39	35	32	29
6	65	53	44	38	61	50	43	37	45	39	34	40	35	31	36	32	28	26
7	60	48	40	34	57	45	38	33	41	35	30	37	31	28	32	28	25	23
8	56	43	35	30	53	41	34	29	37	31	27	33	28	25	30	26	22	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	23	20	18
10	49	36	29	24	46	35	28	23	32	26	22	28	23	20	26	21	18	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10367	10367	10367
5°	10446	10378	10339
10°	10420	10371	10342
15°	10365	10365	10355
20°	10297	10328	10328
25°	10200	10274	10243
30°	10076	10198	10153
35°	9926	10078	10008
40°	9762	9900	9800
45°	9584	9652	9503
50°	9334	9334	9185
55°	9038	8920	8787
60°	8602	8428	8294
65°	7950	7792	7723
70°	6961	7016	6989
75°	5600	6194	6231
80°	3980	5252	5308
85°	2424	4404	4404



TEST NUMBER: P562664

CATALOG NUMBER: SQ4-PC3-050U-100D-930-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	212.7	2.3
10°-20°	610.4	6.6
20°-30°	924.3	9.9
30°-40°	1108.1	11.9
40°-50°	1129.9	12.1
50°-60°	986.3	10.6
60°-70°	706.2	7.6
70°-80°	363.7	3.9
80°-90°	93.8	1.0
90°-100°	233.1	2.5
100°-110°	633.2	6.8
110°-120°	651.0	7.0
120°-130°	520.5	5.6
130°-140°	409.0	4.4
140°-150°	313.6	3.4
150°-160°	225.5	2.4
160°-170°	137.9	1.5
170°-180°	46.5	0.5
0°-30°	1747.4	18.8
0°-40°	2855.5	30.7
0°-60°	4971.8	53.4
0°-90°	6135.5	65.9
90°-120°	1517.2	16.3
90°-150°	2760.3	29.7
90°-180°	3170.0	34.1
0°-180°	9305.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2247	2247	2247	2247	2247	
5°	2256	2233	2241	2235	2233	214
15°	2170	2152	2170	2170	2168	612
25°	2004	1990	2018	2012	2012	922
35°	1763	1758	1790	1777	1777	1102
45°	1469	1465	1480	1461	1457	1131
55°	1124	1110	1109	1092	1092	1002
65°	728	712	714	708	708	720
75°	314	328	348	350	350	340
85°	46	70	83	85	83	62
90°	2	6	11	14	14	4
95°	34	128	406	177	119	36
105°	112	175	696	1060	998	119
115°	200	243	557	1109	1263	197
125°	275	313	504	850	1002	245
135°	331	368	490	692	781	256
145°	382	410	484	588	632	240
155°	432	448	481	528	543	199
165°	468	474	482	503	504	132
175°	486	487	484	490	489	46
180°	486	486	486	486	486	

TEST NUMBER: P562664

CATALOG NUMBER: SQ4-PC3-050U-100D-930-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2247.4	2247.4	2247.4	2247.4	2247.4
2.5°	2260.7	2241.2	2247.4	2242.2	2234.1
5°	2255.7	2233.4	2241.2	2234.9	2232.8
7.5°	2239.5	2217.1	2227.4	2223.2	2221.2
10°	2224.5	2202.1	2214.1	2209.9	2207.9
12.5°	2204.5	2183.8	2197.5	2193.3	2192.9
15°	2170.4	2152.1	2170.4	2170.4	2168.3
17.5°	2127.6	2110.9	2130.5	2131.7	2130.5
20°	2097.6	2079.3	2103.8	2101.8	2103.8
22.5°	2061.0	2045.9	2072.2	2066.8	2068.9
25°	2003.9	1989.7	2018.5	2012.3	2012.3
27.5°	1936.5	1926.3	1957.7	1951.1	1951.1
30°	1891.6	1881.4	1914.5	1906.1	1906.1
32.5°	1841.6	1834.7	1866.2	1856.2	1856.2
35°	1762.6	1758.5	1789.6	1777.1	1777.1
37.5°	1681.0	1677.3	1705.5	1690.4	1685.6
40°	1621.1	1619.0	1643.9	1627.3	1627.3
42.5°	1561.1	1559.1	1580.7	1560.7	1560.7
45°	1469.1	1465.1	1479.5	1460.7	1456.7
47.5°	1368.8	1364.8	1373.8	1353.4	1351.4
50°	1300.6	1296.5	1300.6	1281.8	1279.8
52.5°	1230.7	1223.3	1224.0	1205.3	1204.9
55°	1123.7	1109.5	1109.1	1092.5	1092.5
57.5°	1010.5	991.8	993.4	979.2	977.2
60°	932.3	911.9	913.5	901.0	899.0
62.5°	855.7	832.1	837.0	822.8	822.4
65°	728.3	712.1	713.8	707.5	707.5
67.5°	606.0	590.9	601.8	596.8	596.4
70°	516.1	505.9	520.2	520.2	518.2
72.5°	432.8	432.4	450.3	450.3	451.6
75°	314.2	328.5	347.5	349.6	349.6
77.5°	209.8	235.0	256.0	256.8	256.4
80°	149.8	178.3	197.7	201.8	199.8
82.5°	101.5	131.7	147.7	151.9	149.8
85°	45.8	70.2	83.2	85.3	83.2
87.5°	13.6	29.2	35.5	36.0	32.8
90°	1.6	6.1	10.9	14.1	14.1
92.5°	14.1	63.8	110.8	47.6	40.3
95°	34.3	127.5	405.9	176.7	118.7
97.5°	56.8	140.8	622.3	484.1	340.0
100°	71.8	149.7	688.5	697.9	563.6
102.5°	86.8	158.5	706.0	863.1	744.7
105°	112.4	175.0	696.3	1060.2	997.6
107.5°	138.9	194.2	656.0	1161.9	1179.3
110°	157.7	208.1	626.0	1182.0	1256.8



TEST NUMBER: P562664

CATALOG NUMBER: SQ4-PC3-050U-100D-930-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	173.9	221.8	596.1	1165.3	1278.0
115°	199.8	242.6	557.3	1108.8	1263.0
117.5°	224.2	265.1	532.7	1028.7	1202.4
120°	240.4	280.1	521.4	975.0	1147.5
122.5°	254.2	293.8	513.9	921.1	1087.5
125°	274.8	312.9	504.3	849.6	1002.3
127.5°	293.2	331.0	499.0	795.4	926.4
130°	304.4	341.1	496.5	761.4	878.9
132.5°	315.7	352.3	494.0	732.4	836.5
135°	331.0	367.6	490.2	692.1	780.6
137.5°	347.5	380.8	488.3	656.5	730.9
140°	357.5	389.6	487.1	633.8	701.0
142.5°	367.5	397.1	485.8	616.1	672.2
145°	382.5	410.0	484.0	588.0	632.3
147.5°	399.4	422.9	482.4	565.9	600.7
150°	410.6	430.4	482.4	553.3	580.8
152.5°	419.3	436.7	481.2	541.9	564.5
155°	432.4	447.7	480.8	528.0	543.3
157.5°	445.3	457.2	480.8	518.6	530.2
160°	452.7	463.4	480.8	512.3	521.4
162.5°	460.2	468.5	482.1	507.2	513.9
165°	468.4	474.5	482.4	502.7	504.3
167.5°	476.8	479.8	484.0	497.4	498.6
170°	479.3	482.3	484.0	494.9	494.9
172.5°	481.8	483.6	484.0	492.4	492.4
175°	485.5	487.1	484.0	490.2	488.7
177.5°	486.8	486.8	483.0	488.0	485.5
180°	485.5	485.5	485.5	485.5	485.5

(END OF REPORT)