

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: CORELITE

Report Number: P564797

Luminaire Tested: **SQ4-PW1-075U-125D-930-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P564797  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2106-289-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PW1-075U-125D-930-1D-UNV-STD-W-12  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 18652.6 lumens  
Efficiency: N/A  
Efficacy: 95.8 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31  
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 194.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P564797

CATALOG NUMBER: SQ4-PW1-075U-125D-930-1D-UNV-STD-W-12

### Luminous Intensity Polar Plot





TEST NUMBER: P564797

CATALOG NUMBER: SQ4-PW1-075U-125D-930-1D-UNV-STD-W-12

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	59	58	57	52
2	92	84	78	73	86	79	74	69	69	65	62	61	57	55	52	50	48	44
3	84	74	67	61	78	70	63	58	61	56	52	54	50	46	46	43	41	37
4	77	66	58	51	71	62	55	49	55	49	44	48	43	40	42	38	35	32
5	70	59	50	44	66	55	48	42	49	43	38	43	38	35	37	34	31	28
6	65	53	44	38	61	50	42	37	44	38	34	39	34	30	34	30	27	24
7	60	48	39	34	56	45	38	32	40	34	30	35	31	27	31	27	24	22
8	56	43	35	30	52	41	34	29	37	31	26	32	28	24	29	25	22	19
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	22	20	18
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	24	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13904	13904	13904
5°	13994	13884	13822
10°	13882	13770	13696
15°	13735	13583	13532
20°	13571	13362	13337
25°	13382	13138	13098
30°	13099	12901	12816
35°	12727	12547	12472
40°	12330	12138	12090
45°	11850	11694	11642
50°	11359	11264	11187
55°	10829	10829	10658
60°	10168	10364	9996
65°	9305	9769	9073
70°	8202	8990	7987
75°	7005	8047	6816
80°	5432	6773	5503
85°	3515	5201	4640



TEST NUMBER: P564797

CATALOG NUMBER: SQ4-PW1-075U-125D-930-1D-UNV-STD-W-12

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	425.7	2.3
10°-20°	1202.0	6.4
20°-30°	1782.9	9.6
30°-40°	2086.2	11.2
40°-50°	2076.9	11.1
50°-60°	1793.5	9.6
60°-70°	1291.0	6.9
70°-80°	677.0	3.6
80°-90°	170.6	0.9
90°-100°	517.4	2.8
100°-110°	1423.6	7.6
110°-120°	1469.4	7.9
120°-130°	1177.3	6.3
130°-140°	924.7	5.0
140°-150°	708.6	3.8
150°-160°	509.5	2.7
160°-170°	311.5	1.7
170°-180°	105.0	0.6
0°-30°	3410.6	18.3
0°-40°	5496.8	29.5
0°-60°	9367.1	50.2
0°-90°	11505.7	61.7
90°-120°	3410.4	18.3
90°-150°	6220.9	33.4
90°-180°	7147.0	38.3
0°-180°	18652.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	4521	4521	4521	4521	4521	
5°	4533	4482	4497	4485	4477	429
15°	4314	4259	4266	4258	4250	1216
25°	3944	3877	3872	3848	3860	1813
35°	3390	3343	3342	3310	3322	2119
45°	2725	2701	2689	2681	2677	2102
55°	2020	2016	2020	1992	1988	1802
65°	1279	1318	1342	1290	1247	1267
75°	590	644	677	632	574	632
85°	100	131	147	139	132	131
90°	2	9	16	21	21	9
95°	77	282	915	391	250	81
105°	254	391	1569	2389	2229	268
115°	450	549	1258	2505	2843	445
125°	621	708	1141	1931	2262	554
135°	749	831	1109	1562	1767	578
145°	866	925	1092	1330	1433	543
155°	980	1012	1085	1196	1230	450
165°	1060	1073	1090	1135	1141	299
175°	1097	1099	1092	1106	1104	104
180°	1097	1097	1097	1097	1097	

TEST NUMBER: P564797

CATALOG NUMBER: SQ4-PW1-075U-125D-930-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	4521.1	4521.1	4521.1	4521.1	4521.1
2.5°	4546.6	4509.2	4521.1	4511.0	4489.2
5°	4533.0	4482.4	4497.2	4485.1	4477.3
7.5°	4486.8	4440.1	4451.0	4438.1	4433.5
10°	4445.4	4398.7	4409.6	4393.4	4385.7
12.5°	4397.6	4347.8	4358.6	4342.5	4337.9
15°	4314.0	4259.4	4266.2	4258.0	4250.2
17.5°	4216.8	4161.5	4162.6	4149.8	4148.3
20°	4146.7	4088.2	4082.9	4067.2	4075.0
22.5°	4070.2	4008.6	4003.3	3981.2	3992.1
25°	3943.5	3877.3	3871.8	3848.2	3859.9
27.5°	3796.9	3731.5	3731.6	3698.4	3710.9
30°	3688.6	3626.3	3632.8	3593.3	3608.9
32.5°	3573.9	3517.8	3521.3	3481.8	3497.4
35°	3389.8	3343.1	3342.0	3310.4	3322.1
37.5°	3201.8	3160.5	3154.0	3135.8	3138.9
40°	3071.2	3036.1	3023.4	3011.4	3011.4
42.5°	2934.1	2902.2	2889.5	2880.7	2877.6
45°	2724.6	2701.2	2688.8	2680.7	2676.8
47.5°	2517.5	2495.7	2484.8	2479.1	2475.2
50°	2374.1	2358.5	2354.2	2342.1	2338.2
52.5°	2230.7	2221.3	2217.1	2201.9	2198.0
55°	2019.6	2015.7	2019.6	1991.6	1987.7
57.5°	1799.7	1805.9	1818.8	1781.1	1771.8
60°	1653.1	1668.7	1685.0	1640.8	1625.2
62.5°	1503.3	1528.2	1551.1	1500.4	1478.6
65°	1278.7	1317.6	1342.4	1289.6	1246.8
67.5°	1062.0	1110.3	1140.0	1083.2	1034.9
70°	912.2	966.7	999.8	942.8	888.3
72.5°	781.5	842.3	869.2	815.3	760.8
75°	589.5	644.1	677.2	632.0	573.6
77.5°	418.3	469.7	497.1	457.8	409.5
80°	306.7	361.2	382.4	349.6	310.7
82.5°	217.5	262.7	277.2	257.5	231.0
85°	99.6	130.7	147.4	139.2	131.5
87.5°	26.0	49.1	63.8	64.8	67.9
90°	2.3	9.2	16.3	21.0	21.0
92.5°	32.2	137.7	238.6	91.6	75.2
95°	77.0	282.4	915.0	391.3	249.8
97.5°	125.6	313.2	1396.3	1075.9	759.1
100°	161.1	332.2	1547.6	1562.0	1274.5
102.5°	194.7	354.9	1586.8	1937.9	1674.1
105°	254.4	391.4	1568.6	2388.9	2229.1
107.5°	311.4	436.5	1479.4	2609.8	2657.2
110°	352.5	466.6	1412.2	2664.7	2829.0

TEST NUMBER: P564797

CATALOG NUMBER: SQ4-PW1-075U-125D-930-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	389.8	500.3	1345.0	2629.3	2879.5
115°	450.5	548.6	1258.1	2505.3	2843.0
117.5°	508.4	598.8	1203.0	2331.2	2713.3
120°	543.9	630.6	1178.8	2200.8	2595.6
122.5°	575.6	662.3	1162.0	2086.4	2461.2
125°	620.9	707.6	1141.4	1930.9	2261.8
127.5°	663.8	746.5	1127.9	1801.1	2091.4
130°	686.3	770.7	1120.4	1724.0	1988.7
132.5°	712.4	796.8	1114.8	1656.2	1895.4
135°	749.3	831.4	1108.7	1561.6	1767.0
137.5°	783.8	860.0	1103.6	1485.1	1654.5
140°	810.0	880.7	1101.7	1434.3	1587.2
142.5°	832.4	897.6	1098.0	1389.0	1520.0
145°	866.0	925.3	1092.4	1330.5	1433.2
147.5°	901.9	953.1	1089.6	1278.7	1360.8
150°	924.3	970.0	1087.7	1250.2	1314.1
152.5°	944.9	986.9	1085.9	1225.7	1278.7
155°	980.4	1012.3	1085.4	1195.9	1230.1
157.5°	1006.0	1032.1	1085.4	1171.4	1195.1
160°	1024.7	1045.2	1085.4	1158.2	1176.4
162.5°	1039.6	1056.5	1087.3	1146.9	1161.5
165°	1059.7	1073.4	1090.1	1134.6	1141.4
167.5°	1073.7	1084.2	1092.4	1124.2	1126.0
170°	1083.1	1089.9	1092.4	1120.4	1120.4
172.5°	1090.5	1093.7	1092.4	1114.8	1112.9
175°	1097.1	1099.3	1092.4	1106.4	1104.1
177.5°	1098.9	1098.9	1091.5	1102.6	1098.9
180°	1097.1	1097.1	1097.1	1097.1	1097.1

(END OF REPORT)