

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P563408

Luminaire Tested: **SQ4-PP3-075U-075D-930-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563408
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-075U-075D-930-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9339.1 lumens
Efficiency: N/A
Efficacy: 102.6 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 91
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563408
CATALOG NUMBER: SQ4-PP3-075U-075D-930-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P563408

CATALOG NUMBER: SQ4-PP3-075U-075D-930-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	98	94	90	86	90	86	83	80	73	71	68	61	59	57	49	48	47	42
2	89	82	76	71	82	76	70	66	64	60	57	53	51	48	43	42	40	35
3	81	72	65	59	75	67	60	55	57	52	48	47	44	41	39	36	34	30
4	75	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29	26
5	68	57	49	43	63	53	46	40	45	40	35	38	34	30	31	28	26	22
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	28	25	23	20
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	28	24	21	24	20	18	16
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8241	8241	8241
5°	8302	8251	8222
10°	8288	8229	8193
15°	8233	8188	8143
20°	8179	8133	8071
25°	8081	8025	7946
30°	7932	7890	7790
35°	7724	7671	7574
40°	7477	7430	7345
45°	7273	7222	7150
50°	7012	6967	6900
55°	6649	6561	6511
60°	6053	5880	5850
65°	5332	5111	5093
70°	4603	4413	4413
75°	3962	3907	3852
80°	3493	3536	3454
85°	2736	2985	2985



TEST NUMBER: P563408

CATALOG NUMBER: SQ4-PP3-075U-075D-930-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.9	1.8
10°-20°	482.4	5.2
20°-30°	722.5	7.7
30°-40°	847.5	9.1
40°-50°	850.1	9.1
50°-60°	725.2	7.8
60°-70°	473.0	5.1
70°-80°	237.3	2.5
80°-90°	67.5	0.7
90°-100°	344.9	3.7
100°-110°	949.1	10.2
110°-120°	979.6	10.5
120°-130°	784.8	8.4
130°-140°	616.4	6.6
140°-150°	472.4	5.1
150°-160°	339.7	3.6
160°-170°	207.7	2.2
170°-180°	70.0	0.7
0°-30°	1373.8	14.7
0°-40°	2221.3	23.8
0°-60°	3796.6	40.7
0°-90°	4574.4	49.0
90°-120°	2273.6	24.3
90°-150°	4147.3	44.4
90°-180°	4765.0	51.0
0°-180°	9339.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1786	1786	1786	1786	1786	
5°	1793	1776	1782	1776	1776	170
15°	1724	1707	1714	1708	1705	486
25°	1588	1569	1577	1563	1561	730
35°	1372	1358	1362	1346	1345	857
45°	1115	1107	1107	1096	1096	858
55°	827	824	816	811	810	735
65°	488	479	468	465	467	488
75°	222	222	219	218	216	241
85°	52	56	56	56	56	61
90°	2	6	11	14	14	5
95°	51	188	610	261	166	54
105°	170	261	1046	1593	1486	179
115°	300	366	839	1670	1895	296
125°	414	472	761	1287	1508	369
135°	500	554	739	1041	1178	385
145°	577	617	728	887	956	362
155°	654	675	724	797	820	300
165°	706	716	727	756	761	199
175°	731	733	728	738	736	69
180°	731	731	731	731	731	

TEST NUMBER: P563408

CATALOG NUMBER: SQ4-PP3-075U-075D-930-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1786.5	1786.5	1786.5	1786.5	1786.5
2.5°	1797.8	1783.1	1786.5	1783.9	1776.5
5°	1792.8	1776.0	1781.9	1775.6	1775.6
7.5°	1780.6	1762.2	1768.1	1761.8	1761.5
10°	1769.3	1751.0	1756.8	1750.5	1749.0
12.5°	1753.0	1734.7	1741.8	1734.2	1733.9
15°	1723.9	1707.1	1714.5	1708.2	1705.1
17.5°	1691.0	1672.7	1681.6	1672.8	1671.6
20°	1666.0	1647.6	1656.6	1644.1	1644.1
22.5°	1635.9	1617.5	1627.8	1611.5	1611.5
25°	1587.7	1569.3	1576.7	1562.6	1561.1
27.5°	1530.4	1512.3	1520.1	1504.1	1503.8
30°	1489.1	1472.2	1481.2	1464.0	1462.4
32.5°	1444.0	1428.3	1434.9	1417.6	1416.1
35°	1371.6	1357.8	1362.2	1346.5	1345.0
37.5°	1295.5	1281.4	1286.4	1273.0	1272.3
40°	1241.7	1232.5	1233.8	1222.8	1219.7
42.5°	1191.6	1181.1	1182.5	1171.5	1170.9
45°	1114.8	1107.2	1107.0	1096.0	1096.0
47.5°	1033.4	1027.6	1025.9	1016.8	1016.5
50°	977.0	972.4	970.8	962.9	961.4
52.5°	918.2	916.0	910.7	904.1	903.8
55°	826.7	823.7	815.8	811.0	809.5
57.5°	727.5	721.3	712.4	705.6	706.8
60°	656.1	649.9	637.3	634.1	634.1
62.5°	587.2	579.8	567.1	562.8	565.2
65°	488.5	479.3	468.2	465.1	466.6
67.5°	399.0	390.7	378.6	378.6	377.4
70°	341.3	336.7	327.2	327.2	327.2
72.5°	290.0	287.8	280.9	280.9	279.6
75°	222.3	222.3	219.2	217.6	216.1
77.5°	166.6	167.2	165.7	164.0	161.3
80°	131.5	134.6	133.1	131.5	130.0
82.5°	99.0	102.0	101.8	98.9	98.6
85°	51.7	56.3	56.4	56.4	56.4
87.5°	14.1	19.9	22.2	22.9	24.1
90°	1.6	6.1	10.9	14.0	14.0
92.5°	21.5	91.8	159.0	61.1	50.1
95°	51.4	188.3	610.0	260.8	166.5
97.5°	83.7	208.8	930.9	717.2	506.1
100°	107.4	221.5	1031.7	1041.4	849.6
102.5°	129.8	236.6	1057.9	1291.9	1116.1
105°	169.6	260.9	1045.7	1592.6	1486.1
107.5°	207.6	291.0	986.3	1739.8	1771.5
110°	235.0	311.1	941.5	1776.5	1886.0



TEST NUMBER: P563408

CATALOG NUMBER: SQ4-PP3-075U-075D-930-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	259.9	333.5	896.6	1752.9	1919.6
115°	300.3	365.8	838.8	1670.2	1895.4
117.5°	338.9	399.2	802.0	1554.1	1808.8
120°	362.6	420.4	785.8	1467.2	1730.4
122.5°	383.7	441.6	774.6	1390.9	1640.8
125°	413.9	471.7	760.9	1287.3	1507.9
127.5°	442.6	497.6	751.9	1200.7	1394.3
130°	457.5	513.8	746.9	1149.3	1325.8
132.5°	474.9	531.2	743.2	1104.1	1263.6
135°	499.5	554.3	739.2	1041.0	1178.0
137.5°	522.5	573.4	735.7	990.1	1103.0
140°	540.0	587.1	734.5	956.2	1058.2
142.5°	554.9	598.4	732.0	926.0	1013.3
145°	577.3	616.9	728.3	887.0	955.5
147.5°	601.3	635.4	726.4	852.4	907.2
150°	616.2	646.7	725.2	833.5	876.1
152.5°	629.9	657.9	723.9	817.1	852.4
155°	653.6	674.9	723.6	797.3	820.1
157.5°	670.7	688.0	723.6	780.9	796.7
160°	683.1	696.8	723.6	772.1	784.3
162.5°	693.1	704.4	724.8	764.6	774.3
165°	706.5	715.6	726.7	756.4	760.9
167.5°	715.8	722.8	728.3	749.5	750.7
170°	722.0	726.6	728.3	746.9	746.9
172.5°	727.0	729.2	728.3	743.2	742.0
175°	731.4	732.9	728.3	737.6	736.0
177.5°	732.6	732.6	727.6	735.1	732.6
180°	731.4	731.4	731.4	731.4	731.4

(END OF REPORT)