

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564941

Luminaire Tested: **SQ4-PW1-100U-075D-930-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564941
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-100U-075D-930-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 16375.0 lumens
Efficiency: N/A
Efficacy: 106.7 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 153.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564941

CATALOG NUMBER: SQ4-PW1-100U-075D-930-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P564941

CATALOG NUMBER: SQ4-PW1-100U-075D-930-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	41
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	43	42	41	35
2	87	80	74	69	79	73	68	64	60	57	54	49	46	44	38	36	35	30
3	80	70	63	58	72	65	58	53	53	49	45	43	40	37	33	31	29	25
4	73	62	55	49	66	57	50	45	47	42	38	38	35	32	30	27	25	22
5	67	55	48	42	61	51	44	39	42	37	33	34	31	28	27	24	22	19
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	22	19	16
7	57	45	37	32	52	41	34	29	35	29	25	28	24	21	22	19	17	15
8	53	41	33	28	48	37	31	26	31	26	22	26	22	19	20	18	15	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8200	8200	8200
5°	8253	8188	8152
10°	8187	8121	8077
15°	8100	8011	7981
20°	8004	7881	7865
25°	7892	7748	7725
30°	7725	7608	7558
35°	7506	7400	7356
40°	7271	7159	7130
45°	6989	6897	6866
50°	6699	6643	6598
55°	6386	6386	6286
60°	5996	6112	5896
65°	5488	5761	5351
70°	4838	5303	4711
75°	4132	4746	4020
80°	3204	3994	3245
85°	2071	3066	2735



TEST NUMBER: P564941

CATALOG NUMBER: SQ4-PW1-100U-075D-930-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	251.1	1.5
10°-20°	708.9	4.3
20°-30°	1051.5	6.4
30°-40°	1230.3	7.5
40°-50°	1224.8	7.5
50°-60°	1057.7	6.5
60°-70°	761.4	4.6
70°-80°	399.3	2.4
80°-90°	102.0	0.6
90°-100°	691.1	4.2
100°-110°	1907.8	11.7
110°-120°	1967.5	12.0
120°-130°	1581.1	9.7
130°-140°	1242.6	7.6
140°-150°	953.0	5.8
150°-160°	684.9	4.2
160°-170°	418.9	2.6
170°-180°	141.2	0.9
0°-30°	2011.4	12.3
0°-40°	3241.8	19.8
0°-60°	5524.3	33.7
0°-90°	6787.0	41.4
90°-120°	4566.4	27.9
90°-150°	8343.0	50.9
90°-180°	9588.0	58.6
0°-180°	16375.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2666	2666	2666	2666	2666	
5°	2673	2644	2652	2645	2640	253
15°	2544	2512	2516	2511	2507	717
25°	2326	2287	2283	2270	2276	1069
35°	1999	1972	1971	1952	1959	1250
45°	1607	1593	1586	1581	1579	1240
55°	1191	1189	1191	1175	1172	1063
65°	754	777	792	761	735	747
75°	348	380	399	373	338	373
85°	59	77	87	82	78	78
90°	5	9	19	21	24	9
95°	102	374	1254	515	335	109
105°	340	525	2099	3204	3017	362
115°	609	736	1690	3347	3806	599
125°	836	951	1532	2593	3043	744
135°	1006	1114	1490	2100	2368	778
145°	1166	1247	1471	1788	1924	730
155°	1315	1359	1459	1604	1655	606
165°	1424	1442	1466	1523	1535	401
175°	1476	1478	1469	1490	1485	140
180°	1476	1476	1476	1476	1476	

TEST NUMBER: P564941

CATALOG NUMBER: SQ4-PW1-100U-075D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2666.4	2666.4	2666.4	2666.4	2666.4
2.5°	2681.4	2659.3	2666.4	2660.4	2647.6
5°	2673.4	2643.5	2652.3	2645.1	2640.5
7.5°	2646.2	2618.6	2625.0	2617.4	2614.7
10°	2621.7	2594.2	2600.6	2591.1	2586.5
12.5°	2593.5	2564.1	2570.5	2561.1	2558.3
15°	2544.2	2512.0	2516.0	2511.2	2506.6
17.5°	2486.9	2454.3	2454.9	2447.4	2446.5
20°	2445.5	2411.1	2407.9	2398.7	2403.3
22.5°	2400.4	2364.1	2361.0	2348.0	2354.4
25°	2325.7	2286.7	2283.4	2269.5	2276.4
27.5°	2239.3	2200.7	2200.7	2181.2	2188.5
30°	2175.4	2138.6	2142.5	2119.2	2128.4
32.5°	2107.7	2074.6	2076.7	2053.4	2062.6
35°	1999.2	1971.6	1971.0	1952.4	1959.2
37.5°	1888.3	1864.0	1860.1	1849.3	1851.2
40°	1811.2	1790.6	1783.1	1776.0	1776.0
42.5°	1730.4	1711.6	1704.1	1698.9	1697.1
45°	1606.9	1593.1	1585.7	1581.0	1578.7
47.5°	1484.7	1471.8	1465.4	1462.1	1459.8
50°	1400.1	1390.9	1388.4	1381.3	1379.0
52.5°	1315.6	1310.0	1307.6	1298.6	1296.3
55°	1191.1	1188.8	1191.1	1174.6	1172.3
57.5°	1061.4	1065.1	1072.7	1050.4	1044.9
60°	974.9	984.1	993.7	967.7	958.5
62.5°	886.6	901.3	914.8	884.9	872.0
65°	754.1	777.1	791.7	760.6	735.3
67.5°	626.3	654.8	672.3	638.8	610.3
70°	538.0	570.1	589.7	556.0	523.9
72.5°	460.9	496.8	512.6	480.9	448.7
75°	347.7	379.8	399.4	372.7	338.3
77.5°	246.7	277.0	293.2	270.0	241.5
80°	180.9	213.0	225.5	206.2	183.2
82.5°	128.3	154.9	163.5	151.9	136.3
85°	58.7	77.1	86.9	82.1	77.5
87.5°	16.0	29.8	39.5	40.0	42.3
90°	4.7	9.3	18.9	21.3	23.6
92.5°	42.5	176.4	315.4	115.1	89.7
95°	101.5	373.9	1253.7	515.3	335.3
97.5°	168.1	418.8	1857.2	1429.9	1035.6
100°	217.2	445.8	2080.1	2094.8	1702.3
102.5°	264.4	476.4	2123.5	2588.2	2216.1
105°	340.0	524.7	2099.0	3204.4	3017.4
107.5°	420.3	584.6	1981.9	3501.6	3569.9
110°	476.9	624.7	1891.2	3565.5	3787.1

TEST NUMBER: P564941

CATALOG NUMBER: SQ4-PW1-100U-075D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	527.9	670.1	1806.2	3515.0	3841.9
115°	609.1	736.1	1690.5	3346.6	3806.0
117.5°	680.0	806.5	1614.5	3109.6	3632.2
120°	727.2	851.9	1584.3	2949.1	3475.5
122.5°	772.5	891.7	1559.7	2799.3	3297.9
125°	835.8	951.2	1532.3	2593.2	3043.4
127.5°	889.6	1005.1	1516.3	2419.0	2807.3
130°	925.5	1041.0	1508.7	2312.4	2665.6
132.5°	959.5	1069.4	1501.2	2222.9	2542.8
135°	1005.8	1114.3	1489.8	2100.3	2368.1
137.5°	1057.7	1156.6	1484.2	1997.4	2226.0
140°	1086.1	1183.0	1480.4	1928.8	2129.7
142.5°	1118.2	1207.8	1476.6	1867.8	2044.7
145°	1166.4	1247.2	1470.9	1788.0	1924.3
147.5°	1212.6	1283.3	1465.7	1720.8	1826.5
150°	1246.6	1304.3	1463.8	1680.6	1766.1
152.5°	1273.1	1327.1	1462.0	1646.3	1717.0
155°	1315.1	1359.0	1459.1	1604.3	1655.1
157.5°	1353.8	1387.5	1459.6	1573.7	1608.3
160°	1376.5	1406.5	1461.5	1556.5	1581.9
162.5°	1395.4	1421.7	1463.4	1541.3	1561.1
165°	1423.7	1442.2	1466.2	1523.1	1534.7
167.5°	1445.4	1456.5	1468.6	1512.1	1515.8
170°	1456.8	1466.0	1468.6	1506.3	1506.3
172.5°	1466.2	1471.7	1468.6	1498.7	1496.9
175°	1475.7	1478.0	1468.6	1489.7	1485.1
177.5°	1479.4	1477.6	1468.1	1481.2	1477.5
180°	1475.7	1475.7	1475.7	1475.7	1475.7

(END OF REPORT)