

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563480

Luminaire Tested: **SQ4-PP3-0U-050D-930-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563480  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-0U-050D-930-1D-UNV-STD-W-8  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3102.4 lumens  
Efficiency: N/A  
Efficacy: 88.1 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')  
CIE Type: Direct

Input Watts (W): 35.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563480  
CATALOG NUMBER: SQ4-PP3-0U-050D-930-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P563480

CATALOG NUMBER: SQ4-PP3-OU-050D-930-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	109	105	101	97	107	103	99	96	98	95	93	95	92	90	91	89	87	85				85
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72				72
3	92	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63	61				61
4	84	72	64	57	82	71	63	57	69	62	56	66	60	56	64	59	55	53				53
5	77	65	56	50	75	64	56	49	62	54	49	60	53	48	58	52	48	46				46
6	72	59	50	44	70	58	49	43	56	49	43	54	48	43	53	47	42	40				40
7	66	53	45	39	65	52	44	39	51	44	38	49	43	38	48	42	38	36				36
8	62	49	40	35	60	48	40	34	47	39	34	45	39	34	44	38	34	32				32
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29				29
10	54	41	34	28	53	41	33	28	40	33	28	39	33	28	38	32	28	26				26

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5592	5592	5592
5°	5633	5598	5579
10°	5623	5584	5558
15°	5586	5556	5525
20°	5549	5518	5476
25°	5483	5445	5391
30°	5382	5353	5285
35°	5241	5205	5139
40°	5073	5041	4984
45°	4935	4900	4851
50°	4757	4727	4681
55°	4511	4452	4417
60°	4107	3989	3969
65°	3618	3467	3456
70°	3124	2994	2994
75°	2690	2650	2613
80°	2370	2399	2343
85°	1858	2022	2022



TEST NUMBER: P563480

CATALOG NUMBER: SQ4-PP3-0U-050D-930-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	114.6	3.7
10°-20°	327.3	10.5
20°-30°	490.2	15.8
30°-40°	575.0	18.5
40°-50°	576.8	18.6
50°-60°	492.1	15.9
60°-70°	320.9	10.3
70°-80°	161.0	5.2
80°-90°	44.5	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	932.1	30.0
0°-40°	1507.1	48.6
0°-60°	2576.0	83.0
0°-90°	3102.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3102.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1212	1212	1212	1212	1212	
5°	1216	1205	1209	1205	1205	116
15°	1170	1158	1163	1159	1157	330
25°	1077	1065	1070	1060	1059	495
35°	931	921	924	914	913	581
45°	756	751	751	744	744	582
55°	561	559	554	550	549	498
65°	332	325	318	316	317	331
75°	151	151	149	148	147	164
85°	35	38	38	38	38	42
90°	0	0	0	0	0	



TEST NUMBER: P563480

CATALOG NUMBER: SQ4-PP3-0U-050D-930-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1212.1	1212.1	1212.1	1212.1	1212.1
2.5°	1219.8	1209.8	1212.1	1210.3	1205.3
5°	1216.4	1205.0	1208.9	1204.7	1204.7
7.5°	1208.1	1195.6	1199.6	1195.3	1195.1
10°	1200.5	1188.0	1192.0	1187.7	1186.6
12.5°	1189.4	1176.9	1181.8	1176.6	1176.4
15°	1169.6	1158.2	1163.3	1159.0	1156.9
17.5°	1147.3	1134.9	1141.0	1135.0	1134.2
20°	1130.3	1117.9	1124.0	1115.5	1115.5
22.5°	1109.9	1097.5	1104.4	1093.4	1093.4
25°	1077.2	1064.8	1069.8	1060.2	1059.2
27.5°	1038.3	1026.1	1031.3	1020.5	1020.3
30°	1010.3	998.9	1005.0	993.3	992.2
32.5°	979.7	969.1	973.5	961.8	960.8
35°	930.6	921.3	924.2	913.6	912.6
37.5°	879.0	869.4	872.8	863.7	863.3
40°	842.4	836.2	837.1	829.6	827.6
42.5°	808.4	801.4	802.3	794.8	794.4
45°	756.4	751.2	751.1	743.6	743.6
47.5°	701.1	697.2	696.0	689.9	689.7
50°	662.9	659.8	658.7	653.3	652.3
52.5°	623.0	621.5	617.9	613.4	613.2
55°	560.9	558.8	553.5	550.3	549.2
57.5°	493.6	489.4	483.4	478.7	479.5
60°	445.1	441.0	432.4	430.2	430.2
62.5°	398.4	393.4	384.8	381.8	383.5
65°	331.5	325.2	317.6	315.5	316.6
67.5°	270.7	265.1	256.9	256.9	256.0
70°	231.6	228.5	222.0	222.0	222.0
72.5°	196.7	195.3	190.6	190.6	189.7
75°	150.9	150.9	148.7	147.6	146.6
77.5°	113.0	113.4	112.4	111.3	109.4
80°	89.2	91.3	90.3	89.2	88.2
82.5°	67.1	69.2	69.1	67.1	66.9
85°	35.1	38.2	38.2	38.2	38.2
87.5°	9.3	12.7	13.6	13.6	14.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)