

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563720

Luminaire Tested: **SQ4-PP3-125U-100D-930-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563720
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-125U-100D-930-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14034.9 lumens
Efficiency: N/A
Efficacy: 105.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 133.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563720
CATALOG NUMBER: SQ4-PP3-125U-100D-930-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P563720

CATALOG NUMBER: SQ4-PP3-125U-100D-930-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	96	92	88	85	88	85	81	78	70	68	66	57	55	54	44	43	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	47	45	39	38	36	31
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31	26
4	73	63	55	49	67	58	51	46	48	43	39	39	36	33	31	29	27	23
5	67	56	48	42	61	52	45	39	43	38	34	35	32	28	28	25	23	20
6	62	50	42	37	57	46	39	34	39	34	30	32	28	25	26	23	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	21	18	16	14
9	49	37	30	25	45	35	28	24	29	24	21	24	20	18	20	17	15	12
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10951	10951	10951
5°	11031	10963	10925
10°	11012	10934	10886
15°	10940	10880	10820
20°	10867	10806	10724
25°	10738	10664	10558
30°	10539	10484	10350
35°	10264	10193	10064
40°	9935	9872	9760
45°	9664	9596	9501
50°	9317	9257	9168
55°	8835	8717	8651
60°	8042	7812	7774
65°	7085	6791	6768
70°	6117	5864	5864
75°	5265	5192	5117
80°	4644	4697	4588
85°	3636	3964	3964



TEST NUMBER: P563720

CATALOG NUMBER: SQ4-PP3-125U-100D-930-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	224.5	1.6
10°-20°	640.9	4.6
20°-30°	960.0	6.8
30°-40°	1126.0	8.0
40°-50°	1129.6	8.0
50°-60°	963.6	6.9
60°-70°	628.4	4.5
70°-80°	315.3	2.2
80°-90°	90.2	0.6
90°-100°	576.6	4.1
100°-110°	1553.1	11.1
110°-120°	1629.9	11.6
120°-130°	1322.7	9.4
130°-140°	1037.3	7.4
140°-150°	796.4	5.7
150°-160°	572.6	4.1
160°-170°	349.8	2.5
170°-180°	118.0	0.8
0°-30°	1825.4	13.0
0°-40°	2951.4	21.0
0°-60°	5044.6	35.9
0°-90°	6078.5	43.3
90°-120°	3759.6	26.8
90°-150°	6916.0	49.3
90°-180°	7956.0	56.7
0°-180°	14034.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2374	2374	2374	2374	2374	
5°	2382	2360	2368	2359	2359	226
15°	2291	2268	2278	2270	2266	646
25°	2110	2085	2095	2076	2074	970
35°	1822	1804	1810	1789	1787	1138
45°	1481	1471	1471	1456	1456	1141
55°	1098	1094	1084	1078	1076	976
65°	649	637	622	618	620	648
75°	295	295	291	289	287	321
85°	69	75	75	75	75	81
90°	3	9	19	20	20	9
95°	88	314	945	483	334	92
105°	287	447	1718	2570	2412	302
115°	507	621	1430	2764	3126	499
125°	692	795	1284	2171	2554	618
135°	834	930	1248	1751	1983	643
145°	964	1039	1232	1497	1608	605
155°	1094	1134	1222	1343	1386	504
165°	1187	1201	1226	1275	1281	335
175°	1234	1232	1228	1245	1242	117
180°	1232	1232	1232	1232	1232	

TEST NUMBER: P563720

CATALOG NUMBER: SQ4-PP3-125U-100D-930-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2373.8	2373.8	2373.8	2373.8	2373.8
2.5°	2388.8	2369.2	2373.8	2370.2	2360.5
5°	2382.1	2359.7	2367.5	2359.2	2359.2
7.5°	2365.9	2341.5	2349.2	2340.9	2340.5
10°	2350.9	2326.5	2334.3	2325.9	2323.9
12.5°	2329.3	2304.9	2314.3	2304.3	2303.9
15°	2290.6	2268.2	2278.1	2269.7	2265.6
17.5°	2246.9	2222.5	2234.4	2222.7	2221.1
20°	2213.6	2189.2	2201.1	2184.5	2184.5
22.5°	2173.7	2149.2	2162.8	2141.2	2141.2
25°	2109.6	2085.2	2095.0	2076.2	2074.2
27.5°	2033.4	2009.4	2019.7	1998.5	1998.1
30°	1978.5	1956.1	1968.1	1945.2	1943.1
32.5°	1918.6	1897.8	1906.5	1883.6	1881.6
35°	1822.5	1804.2	1810.0	1789.1	1787.1
37.5°	1721.4	1702.6	1709.3	1691.4	1690.6
40°	1649.8	1637.6	1639.4	1624.7	1620.7
42.5°	1583.2	1569.4	1571.2	1556.6	1555.8
45°	1481.3	1471.1	1470.9	1456.3	1456.3
47.5°	1373.1	1365.4	1363.1	1351.0	1350.6
50°	1298.2	1292.1	1289.9	1279.4	1277.4
52.5°	1220.0	1217.1	1210.0	1201.2	1200.8
55°	1098.5	1094.4	1083.9	1077.6	1075.6
57.5°	966.6	958.4	946.6	937.5	939.1
60°	871.7	863.6	846.7	842.6	842.6
62.5°	780.2	770.4	753.5	747.8	751.0
65°	649.1	636.9	622.1	617.9	620.0
67.5°	530.1	519.1	503.1	503.0	501.4
70°	453.5	447.4	434.8	434.8	434.8
72.5°	385.3	382.5	373.2	373.2	371.6
75°	295.4	295.4	291.3	289.1	287.1
77.5°	221.4	222.2	220.1	217.9	214.3
80°	174.8	178.8	176.8	174.7	172.7
82.5°	131.5	135.6	135.2	131.5	131.1
85°	68.7	74.8	74.9	74.9	74.9
87.5°	18.9	26.7	30.4	30.7	32.4
90°	3.1	9.3	18.8	20.4	20.4
92.5°	38.3	135.3	267.5	128.8	89.5
95°	87.9	313.6	945.2	483.3	334.4
97.5°	140.4	359.0	1482.4	1238.4	933.9
100°	180.6	377.1	1653.3	1729.8	1435.0
102.5°	219.5	402.5	1709.8	2097.7	1855.8
105°	287.3	447.0	1717.6	2569.7	2411.6
107.5°	351.4	493.8	1644.5	2812.3	2853.1
110°	394.1	529.2	1577.9	2887.6	3036.5



TEST NUMBER: P563720

CATALOG NUMBER: SQ4-PP3-125U-100D-930-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	439.3	564.6	1513.8	2870.9	3115.6
115°	507.1	620.7	1430.3	2763.7	3126.0
117.5°	569.0	675.5	1365.6	2592.5	2996.0
120°	609.2	712.0	1333.0	2469.7	2884.2
122.5°	644.4	746.0	1309.1	2344.1	2757.3
125°	692.4	795.3	1284.3	2170.7	2554.5
127.5°	738.6	839.9	1268.6	2017.8	2360.4
130°	766.2	867.5	1262.3	1930.2	2231.1
132.5°	793.8	893.9	1256.0	1853.0	2129.3
135°	833.7	930.4	1248.2	1751.2	1983.0
137.5°	871.7	964.4	1244.1	1664.8	1855.2
140°	898.1	987.1	1240.3	1611.6	1783.6
142.5°	925.7	1008.6	1237.8	1562.0	1707.0
145°	964.0	1039.2	1232.5	1497.2	1607.7
147.5°	1005.5	1070.9	1227.2	1442.7	1529.5
150°	1033.1	1089.9	1224.6	1408.4	1480.6
152.5°	1058.2	1107.7	1223.4	1380.5	1439.1
155°	1094.3	1134.2	1221.5	1343.4	1386.4
157.5°	1126.0	1157.1	1221.8	1317.3	1346.2
160°	1146.1	1172.2	1223.1	1302.1	1323.6
162.5°	1163.7	1184.9	1224.3	1289.4	1304.7
165°	1187.0	1200.8	1226.2	1275.0	1281.2
167.5°	1205.8	1213.8	1227.8	1264.0	1266.4
170°	1218.4	1221.4	1227.8	1257.6	1257.6
172.5°	1225.9	1226.5	1229.0	1251.3	1251.3
175°	1234.1	1232.5	1227.8	1245.0	1241.9
177.5°	1237.5	1235.1	1228.7	1238.7	1236.3
180°	1232.5	1232.5	1232.5	1232.5	1232.5

(END OF REPORT)