

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563984

Luminaire Tested: **SQ4-PR1-050U-075D-930-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563984
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-050U-075D-930-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7717.5 lumens
Efficiency: N/A
Efficacy: 98.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 78.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563984
CATALOG NUMBER: SQ4-PR1-050U-075D-930-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P563984

CATALOG NUMBER: SQ4-PR1-050U-075D-930-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	96	92	89	93	90	86	83	78	76	73	67	65	64	57	56	55	50
2	91	84	78	73	85	79	73	69	69	65	61	59	56	54	51	49	47	43
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	45	43	40	37
4	77	66	58	52	71	62	55	49	54	49	44	47	43	40	41	38	35	32
5	71	59	51	45	66	55	48	43	49	43	39	43	38	35	37	33	31	28
6	65	53	45	39	61	50	43	37	44	38	34	39	34	30	33	30	27	24
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	31	27	24	22
8	56	44	36	30	52	41	34	29	37	31	27	32	28	24	28	24	22	19
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	22	20	17
10	49	37	29	25	46	35	28	24	31	25	22	27	23	20	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8388	8388	8388
5°	8464	8398	8355
10°	8437	8378	8334
15°	8400	8347	8302
20°	8357	8303	8242
25°	8299	8243	8147
30°	8209	8150	8034
35°	8088	8017	7903
40°	7903	7818	7677
45°	7581	7448	7295
50°	7014	6845	6710
55°	6121	5983	5857
60°	5158	5115	5014
65°	4462	4479	4445
70°	4098	4119	4119
75°	3935	3935	3964
80°	3703	3746	3703
85°	2985	3313	3313



TEST NUMBER: P563984

CATALOG NUMBER: SQ4-PR1-050U-075D-930-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.9	2.2
10°-20°	492.0	6.4
20°-30°	742.0	9.6
30°-40°	884.1	11.5
40°-50°	871.7	11.3
50°-60°	666.2	8.6
60°-70°	412.3	5.3
70°-80°	234.2	3.0
80°-90°	73.1	0.9
90°-100°	233.1	3.0
100°-110°	633.2	8.2
110°-120°	651.0	8.4
120°-130°	520.5	6.7
130°-140°	409.0	5.3
140°-150°	313.6	4.1
150°-160°	225.5	2.9
160°-170°	137.9	1.8
170°-180°	46.5	0.6
0°-30°	1405.9	18.2
0°-40°	2290.1	29.7
0°-60°	3827.9	49.6
0°-90°	4547.4	58.9
90°-120°	1517.2	19.7
90°-150°	2760.3	35.8
90°-180°	3170.0	41.1
0°-180°	7717.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1818	1818	1818	1818	1818	
5°	1828	1808	1814	1807	1804	173
15°	1759	1740	1748	1742	1738	496
25°	1630	1610	1619	1602	1601	750
35°	1436	1419	1424	1405	1403	896
45°	1162	1147	1142	1121	1118	890
55°	761	749	744	731	728	682
65°	409	406	410	407	407	414
75°	221	221	221	222	222	233
85°	56	59	63	63	63	66
90°	2	6	11	14	14	5
95°	34	128	406	177	119	36
105°	112	175	696	1060	998	119
115°	200	243	557	1109	1263	197
125°	275	313	504	850	1002	245
135°	331	368	490	692	781	256
145°	382	410	484	588	632	240
155°	432	448	481	528	543	199
165°	468	474	482	503	504	132
175°	486	487	484	490	489	46
180°	486	486	486	486	486	

TEST NUMBER: P563984

CATALOG NUMBER: SQ4-PR1-050U-075D-930-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1818.3	1818.3	1818.3	1818.3	1818.3
2.5°	1829.6	1813.6	1818.3	1814.3	1805.8
5°	1827.7	1807.8	1813.6	1807.3	1804.2
7.5°	1813.6	1794.0	1799.8	1793.5	1791.7
10°	1801.1	1782.7	1788.5	1782.2	1779.1
12.5°	1787.3	1767.7	1774.8	1767.2	1764.1
15°	1758.8	1740.4	1747.8	1741.5	1738.4
17.5°	1727.5	1707.9	1715.2	1707.9	1704.0
20°	1702.4	1684.0	1691.4	1680.4	1678.9
22.5°	1674.8	1656.5	1663.9	1649.1	1648.8
25°	1630.4	1610.4	1619.4	1602.1	1600.6
27.5°	1577.4	1559.0	1566.5	1548.9	1547.0
30°	1541.1	1522.7	1530.1	1511.3	1508.2
32.5°	1499.7	1482.6	1488.8	1469.9	1468.1
35°	1436.2	1419.3	1423.6	1404.8	1403.3
37.5°	1363.8	1348.5	1351.0	1330.2	1328.7
40°	1312.4	1297.1	1298.3	1276.4	1274.8
42.5°	1256.0	1240.7	1239.4	1217.5	1216.0
45°	1162.1	1146.8	1141.7	1121.3	1118.2
47.5°	1055.0	1039.6	1030.2	1013.6	1011.4
50°	977.3	962.0	953.8	939.6	935.0
52.5°	893.3	878.0	871.1	858.1	853.5
55°	761.1	748.9	743.9	731.3	728.3
57.5°	635.5	627.3	625.8	613.6	612.4
60°	559.1	554.5	554.4	543.5	543.5
62.5°	494.0	490.6	493.0	485.8	484.6
65°	408.8	405.7	410.3	407.2	407.2
67.5°	341.4	341.4	344.2	343.0	343.0
70°	303.8	303.8	305.4	305.4	305.4
72.5°	270.0	268.8	272.8	272.8	271.6
75°	220.8	220.8	220.8	222.4	222.4
77.5°	172.0	172.3	173.5	173.2	172.0
80°	139.4	140.9	141.0	139.4	139.4
82.5°	106.8	108.3	108.4	108.0	106.8
85°	56.4	59.4	62.6	62.6	62.6
87.5°	16.6	22.4	27.2	27.8	26.6
90°	1.6	6.1	10.9	14.1	14.1
92.5°	14.1	63.8	110.8	47.6	40.3
95°	34.3	127.5	405.9	176.7	118.7
97.5°	56.8	140.8	622.3	484.1	340.0
100°	71.8	149.7	688.5	697.9	563.6
102.5°	86.8	158.5	706.0	863.1	744.7
105°	112.4	175.0	696.3	1060.2	997.6
107.5°	138.9	194.2	656.0	1161.9	1179.3
110°	157.7	208.1	626.0	1182.0	1256.8

TEST NUMBER: P563984

CATALOG NUMBER: SQ4-PR1-050U-075D-930-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	173.9	221.8	596.1	1165.3	1278.0
115°	199.8	242.6	557.3	1108.8	1263.0
117.5°	224.2	265.1	532.7	1028.7	1202.4
120°	240.4	280.1	521.4	975.0	1147.5
122.5°	254.2	293.8	513.9	921.1	1087.5
125°	274.8	312.9	504.3	849.6	1002.3
127.5°	293.2	331.0	499.0	795.4	926.4
130°	304.4	341.1	496.5	761.4	878.9
132.5°	315.7	352.3	494.0	732.4	836.5
135°	331.0	367.6	490.2	692.1	780.6
137.5°	347.5	380.8	488.3	656.5	730.9
140°	357.5	389.6	487.1	633.8	701.0
142.5°	367.5	397.1	485.8	616.1	672.2
145°	382.5	410.0	484.0	588.0	632.3
147.5°	399.4	422.9	482.4	565.9	600.7
150°	410.6	430.4	482.4	553.3	580.8
152.5°	419.3	436.7	481.2	541.9	564.5
155°	432.4	447.7	480.8	528.0	543.3
157.5°	445.3	457.2	480.8	518.6	530.2
160°	452.7	463.4	480.8	512.3	521.4
162.5°	460.2	468.5	482.1	507.2	513.9
165°	468.4	474.5	482.4	502.7	504.3
167.5°	476.8	479.8	484.0	497.4	498.6
170°	479.3	482.3	484.0	494.9	494.9
172.5°	481.8	483.6	484.0	492.4	492.4
175°	485.5	487.1	484.0	490.2	488.7
177.5°	486.8	486.8	483.0	488.0	485.5
180°	485.5	485.5	485.5	485.5	485.5

(END OF REPORT)