

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564104

Luminaire Tested: **SQ4-PR1-075U-100D-930-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P564104  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2106-289-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PR1-075U-100D-930-1D-UNV-STD-W-8  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 10806.1 lumens  
Efficiency: N/A  
Efficacy: 99.8 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35  
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 108.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P564104  
CATALOG NUMBER: SQ4-PR1-075U-100D-930-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P564104

CATALOG NUMBER: SQ4-PR1-075U-100D-930-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56
1	99	95	91	88	92	89	85	82	76	74	72	65	64	62	55	54	53	48
2	91	84	77	72	84	78	73	68	67	63	60	58	55	52	49	47	45	41
3	83	74	66	61	77	69	62	57	60	55	51	51	48	45	43	41	38	35
4	76	65	58	52	71	61	54	49	53	48	44	46	42	38	39	36	33	30
5	70	58	50	44	65	55	48	42	48	42	38	41	37	33	35	32	29	26
6	65	53	44	39	60	49	42	37	43	37	33	37	33	29	32	29	26	23
7	60	47	40	34	55	45	37	32	39	33	29	34	30	26	29	26	23	21
8	55	43	35	30	52	41	34	29	36	30	26	31	27	23	27	23	21	18
9	52	39	32	27	48	37	30	26	33	27	23	29	24	21	25	21	19	17
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11145	11145	11145
5°	11246	11159	11101
10°	11210	11132	11073
15°	11161	11091	11031
20°	11105	11033	10951
25°	11026	10952	10825
30°	10907	10830	10674
35°	10746	10653	10500
40°	10501	10389	10201
45°	10074	9897	9693
50°	9319	9095	8916
55°	8134	7949	7782
60°	6854	6797	6662
65°	5928	5951	5905
70°	5445	5473	5473
75°	5229	5229	5267
80°	4920	4976	4920
85°	3964	4404	4404



TEST NUMBER: P564104

CATALOG NUMBER: SQ4-PR1-075U-100D-930-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	228.5	2.1
10°-20°	653.7	6.0
20°-30°	985.9	9.1
30°-40°	1174.7	10.9
40°-50°	1158.2	10.7
50°-60°	885.1	8.2
60°-70°	547.8	5.1
70°-80°	311.1	2.9
80°-90°	96.5	0.9
90°-100°	344.9	3.2
100°-110°	949.1	8.8
110°-120°	979.6	9.1
120°-130°	784.8	7.3
130°-140°	616.4	5.7
140°-150°	472.4	4.4
150°-160°	339.7	3.1
160°-170°	207.7	1.9
170°-180°	70.0	0.6
0°-30°	1868.1	17.3
0°-40°	3042.8	28.2
0°-60°	5086.1	47.1
0°-90°	6041.5	55.9
90°-120°	2273.6	21.0
90°-150°	4147.3	38.4
90°-180°	4765.0	44.1
0°-180°	10806.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2416	2416	2416	2416	2416	
5°	2428	2402	2410	2401	2397	230
15°	2337	2312	2322	2314	2310	659
25°	2166	2140	2152	2129	2127	997
35°	1908	1886	1892	1867	1864	1191
45°	1544	1524	1517	1490	1486	1183
55°	1011	995	988	972	968	906
65°	543	539	545	541	541	550
75°	293	293	293	296	296	310
85°	75	79	83	83	83	87
90°	2	6	11	14	14	6
95°	51	188	610	261	166	54
105°	170	261	1046	1593	1486	179
115°	300	366	839	1670	1895	296
125°	414	472	761	1287	1508	369
135°	500	554	739	1041	1178	385
145°	577	617	728	887	956	362
155°	654	675	724	797	820	300
165°	706	716	727	756	761	199
175°	731	733	728	738	736	69
180°	731	731	731	731	731	



TEST NUMBER: P564104

CATALOG NUMBER: SQ4-PR1-075U-100D-930-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2416.0	2416.0	2416.0	2416.0	2416.0
2.5°	2430.9	2409.8	2416.0	2410.7	2399.3
5°	2428.5	2402.0	2409.7	2401.3	2397.2
7.5°	2409.7	2383.7	2391.4	2383.0	2380.6
10°	2393.1	2368.7	2376.4	2368.0	2363.9
12.5°	2374.8	2348.7	2358.1	2348.0	2344.0
15°	2336.9	2312.5	2322.3	2313.9	2309.8
17.5°	2295.3	2269.2	2279.0	2269.3	2264.1
20°	2262.0	2237.6	2247.4	2232.8	2230.8
22.5°	2225.4	2200.9	2210.8	2191.2	2190.8
25°	2166.3	2139.8	2151.7	2128.8	2126.7
27.5°	2095.9	2071.5	2081.4	2058.0	2055.5
30°	2047.6	2023.2	2033.1	2008.0	2003.9
32.5°	1992.7	1969.9	1978.1	1953.1	1950.7
35°	1908.2	1885.8	1891.6	1866.6	1864.5
37.5°	1812.1	1791.7	1795.0	1767.5	1765.5
40°	1743.8	1723.5	1725.1	1695.9	1693.9
42.5°	1668.9	1648.6	1646.9	1617.7	1615.6
45°	1544.1	1523.7	1517.0	1489.9	1485.8
47.5°	1401.7	1381.4	1368.8	1346.7	1343.9
50°	1298.5	1278.2	1267.3	1248.4	1242.3
52.5°	1187.0	1166.6	1157.4	1140.2	1134.1
55°	1011.3	995.1	988.4	971.7	967.6
57.5°	844.4	833.5	831.5	815.3	813.6
60°	742.9	736.8	736.7	722.1	722.1
62.5°	656.3	651.9	655.1	645.5	643.8
65°	543.1	539.1	545.2	541.0	541.0
67.5°	453.6	453.6	457.4	455.7	455.7
70°	403.7	403.7	405.8	405.8	405.8
72.5°	358.8	357.1	362.5	362.5	360.8
75°	293.4	293.4	293.4	295.5	295.5
77.5°	228.5	228.9	230.6	230.1	228.5
80°	185.2	187.2	187.3	185.2	185.2
82.5°	141.9	144.0	144.0	143.5	141.9
85°	74.9	79.0	83.2	83.2	83.2
87.5°	22.0	29.4	35.5	36.1	34.4
90°	1.6	6.1	10.9	14.0	14.0
92.5°	21.5	91.8	159.0	61.1	50.1
95°	51.4	188.3	610.0	260.8	166.5
97.5°	83.7	208.8	930.9	717.2	506.1
100°	107.4	221.5	1031.7	1041.4	849.6
102.5°	129.8	236.6	1057.9	1291.9	1116.1
105°	169.6	260.9	1045.7	1592.6	1486.1
107.5°	207.6	291.0	986.3	1739.8	1771.5
110°	235.0	311.1	941.5	1776.5	1886.0

TEST NUMBER: P564104

CATALOG NUMBER: SQ4-PR1-075U-100D-930-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	259.9	333.5	896.6	1752.9	1919.6
115°	300.3	365.8	838.8	1670.2	1895.4
117.5°	338.9	399.2	802.0	1554.1	1808.8
120°	362.6	420.4	785.8	1467.2	1730.4
122.5°	383.7	441.6	774.6	1390.9	1640.8
125°	413.9	471.7	760.9	1287.3	1507.9
127.5°	442.6	497.6	751.9	1200.7	1394.3
130°	457.5	513.8	746.9	1149.3	1325.8
132.5°	474.9	531.2	743.2	1104.1	1263.6
135°	499.5	554.3	739.2	1041.0	1178.0
137.5°	522.5	573.4	735.7	990.1	1103.0
140°	540.0	587.1	734.5	956.2	1058.2
142.5°	554.9	598.4	732.0	926.0	1013.3
145°	577.3	616.9	728.3	887.0	955.5
147.5°	601.3	635.4	726.4	852.4	907.2
150°	616.2	646.7	725.2	833.5	876.1
152.5°	629.9	657.9	723.9	817.1	852.4
155°	653.6	674.9	723.6	797.3	820.1
157.5°	670.7	688.0	723.6	780.9	796.7
160°	683.1	696.8	723.6	772.1	784.3
162.5°	693.1	704.4	724.8	764.6	774.3
165°	706.5	715.6	726.7	756.4	760.9
167.5°	715.8	722.8	728.3	749.5	750.7
170°	722.0	726.6	728.3	746.9	746.9
172.5°	727.0	729.2	728.3	743.2	742.0
175°	731.4	732.9	728.3	737.6	736.0
177.5°	732.6	732.6	727.6	735.1	732.6
180°	731.4	731.4	731.4	731.4	731.4

(END OF REPORT)