

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519672

Luminaire Tested: **SQ4-050U-0D-835-1D-UNV-STD-W-4**

Issue Date: 4/29/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P519672  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21)  
Test Lab: INNOVATION CENTER  
Issue Date: 4/29/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-050U-0D-835-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 3500K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1991.9 lumens  
Efficiency: N/A  
Efficacy: 161.9 lumens/watt  
N/A  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Indirect

Input Watts (W): 12.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P519672  
CATALOG NUMBER: SQ4-050U-0D-835-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P519672

CATALOG NUMBER: SQ4-050U-0D-835-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20								20				20				20				20
RC	80								50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10				0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10				0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8				0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7				0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6				0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5				0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4				0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4				0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3				0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3				0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3				0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2				0

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
95°	2287	26994	7897
100°	2396	22985	18814
105°	2517	15596	22344
110°	2673	10612	21303
115°	2742	7645	17325
120°	2788	6045	13304
125°	2776	5096	10131
130°	2746	4477	7927
135°	2714	4019	6400
140°	2705	3687	5304
145°	2707	3425	4475
150°	2749	3229	3887
155°	2766	3075	3475
160°	2793	2966	3216
165°	2811	2895	3026
170°	2822	2849	2914
175°	2826	2816	2843



TEST NUMBER: P519672

CATALOG NUMBER: SQ4-050U-0D-835-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	146.4	7.4
100°-110°	397.8	20.0
110°-120°	409.0	20.5
120°-130°	327.0	16.4
130°-140°	257.0	12.9
140°-150°	197.0	9.9
150°-160°	141.7	7.1
160°-170°	86.7	4.4
170°-180°	29.2	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	953.3	47.9
90°-150°	1734.4	87.1
90°-180°	1992.0	100.0
0°-180°	1991.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
90°	1	4	7	9	9	
95°	22	80	255	111	75	24
105°	71	110	438	666	627	75
115°	126	152	350	697	794	124
125°	173	197	317	534	630	154
135°	208	231	308	435	490	161
145°	240	258	304	370	397	151
155°	272	281	302	332	341	125
165°	294	298	303	316	317	83
175°	305	306	304	308	307	29
180°	305	305	305	305	305	



TEST NUMBER: P519672

CATALOG NUMBER: SQ4-050U-0D-835-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
90°	1.0	3.9	6.9	8.8	8.8
92.5°	8.8	40.1	69.6	29.9	25.3
95°	21.6	80.1	255.0	111.0	74.6
97.5°	35.7	88.5	391.0	304.2	213.7
100°	45.1	94.0	432.6	438.5	354.1
102.5°	54.5	99.6	443.6	542.3	467.9
105°	70.6	110.0	437.5	666.1	626.8
107.5°	87.3	122.0	412.2	730.1	741.0
110°	99.1	130.7	393.4	742.7	789.7
112.5°	109.3	139.4	374.5	732.2	803.0
115°	125.6	152.4	350.2	696.7	793.6
117.5°	140.9	166.6	334.7	646.4	755.5
120°	151.1	176.0	327.6	612.6	721.0
122.5°	159.7	184.6	322.9	578.8	683.3
125°	172.6	196.6	316.8	533.9	629.8
127.5°	184.2	208.0	313.5	499.8	582.1
130°	191.3	214.3	311.9	478.4	552.3
132.5°	198.3	221.4	310.4	460.2	525.6
135°	208.0	231.0	308.0	434.8	490.5
137.5°	218.4	239.3	306.8	412.5	459.3
140°	224.6	244.8	306.1	398.2	440.4
142.5°	230.9	249.5	305.3	387.1	422.4
145°	240.3	257.6	304.1	369.5	397.3
147.5°	250.9	265.7	303.1	355.6	377.5
150°	258.0	270.5	303.1	347.6	364.9
152.5°	263.5	274.4	302.3	340.5	354.7
155°	271.7	281.3	302.1	331.8	341.4
157.5°	279.8	287.2	302.1	325.8	333.1
160°	284.5	291.2	302.1	321.9	327.6
162.5°	289.2	294.4	302.9	318.7	322.9
165°	294.3	298.1	303.1	315.9	316.8
167.5°	299.6	301.5	304.1	312.5	313.3
170°	301.2	303.1	304.1	311.0	311.0
172.5°	302.7	303.9	304.1	309.4	309.4
175°	305.1	306.0	304.1	308.0	307.0
177.5°	305.9	305.9	303.5	306.6	305.1
180°	305.1	305.1	305.1	305.1	305.1

(END OF REPORT)