

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564320

Luminaire Tested: **SQ4-PR1-100U-125D-930-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564320
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-100U-125D-930-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14101.5 lumens
Efficiency: N/A
Efficacy: 100.3 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 140.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564320
CATALOG NUMBER: SQ4-PR1-100U-125D-930-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P564320

CATALOG NUMBER: SQ4-PR1-100U-125D-930-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	55				
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	52	47				
2	91	83	77	72	84	78	72	68	67	63	60	57	54	52	48	46	44	40				
3	83	73	66	60	77	69	62	57	59	54	50	51	47	44	43	40	38	34				
4	76	65	57	51	70	61	54	49	53	47	43	45	41	38	38	35	33	29				
5	70	58	50	44	65	54	47	42	47	42	37	41	36	33	35	31	29	26				
6	64	52	44	38	60	49	42	37	43	37	33	37	32	29	31	28	25	23				
7	60	47	39	34	55	44	37	32	39	33	29	34	29	26	29	25	23	20				
8	55	43	35	30	51	40	33	29	35	30	26	31	26	23	26	23	20	18				
9	51	39	32	27	48	37	30	26	33	27	23	28	24	21	24	21	18	16				
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	23	19	17	15				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14223	14223	14223
5°	14351	14240	14166
10°	14305	14206	14131
15°	14242	14154	14078
20°	14171	14079	13975
25°	14071	13976	13814
30°	13919	13820	13622
35°	13713	13594	13400
40°	13401	13257	13017
45°	12855	12630	12370
50°	11893	11606	11378
55°	10380	10145	9931
60°	8746	8674	8502
65°	7566	7595	7536
70°	6949	6984	6984
75°	6673	6673	6721
80°	6277	6349	6277
85°	5060	5621	5621



TEST NUMBER: P564320

CATALOG NUMBER: SQ4-PR1-100U-125D-930-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	291.6	2.1
10°-20°	834.2	5.9
20°-30°	1258.2	8.9
30°-40°	1499.1	10.6
40°-50°	1478.0	10.5
50°-60°	1129.6	8.0
60°-70°	699.0	5.0
70°-80°	397.0	2.8
80°-90°	122.8	0.9
90°-100°	460.7	3.3
100°-110°	1271.9	9.0
110°-120°	1311.7	9.3
120°-130°	1054.1	7.5
130°-140°	828.4	5.9
140°-150°	635.3	4.5
150°-160°	456.6	3.2
160°-170°	279.2	2.0
170°-180°	94.1	0.7
0°-30°	2383.9	16.9
0°-40°	3883.0	27.5
0°-60°	6490.6	46.0
0°-90°	7709.5	54.7
90°-120°	3044.3	21.6
90°-150°	5562.0	39.4
90°-180°	6392.0	45.3
0°-180°	14101.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3083	3083	3083	3083	3083	
5°	3099	3065	3075	3064	3059	294
15°	2982	2951	2964	2953	2948	842
25°	2764	2731	2746	2717	2714	1272
35°	2435	2407	2414	2382	2379	1520
45°	1970	1944	1936	1901	1896	1510
55°	1291	1270	1261	1240	1235	1156
65°	693	688	696	690	690	702
75°	374	374	374	377	377	395
85°	96	101	106	106	106	111
90°	3	6	13	14	16	9
95°	68	249	836	344	224	72
105°	227	350	1399	2136	2012	241
115°	406	491	1127	2231	2537	399
125°	557	634	1022	1729	2029	496
135°	670	743	993	1400	1579	519
145°	778	831	981	1192	1283	487
155°	877	906	973	1070	1103	404
165°	949	962	978	1015	1023	268
175°	984	985	979	993	990	93
180°	984	984	984	984	984	

TEST NUMBER: P564320

CATALOG NUMBER: SQ4-PR1-100U-125D-930-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3083.1	3083.1	3083.1	3083.1	3083.1
2.5°	3102.2	3075.2	3083.1	3076.4	3061.9
5°	3099.0	3065.3	3075.1	3064.4	3059.2
7.5°	3075.1	3041.9	3051.8	3041.1	3038.0
10°	3053.9	3022.7	3032.6	3021.9	3016.7
12.5°	3030.5	2997.3	3009.3	2996.4	2991.2
15°	2982.2	2951.0	2963.6	2952.9	2947.7
17.5°	2929.1	2895.8	2908.4	2896.0	2889.2
20°	2886.6	2855.4	2868.0	2849.3	2846.8
22.5°	2839.8	2808.7	2821.3	2796.3	2795.8
25°	2764.4	2730.7	2745.8	2716.6	2714.0
27.5°	2674.7	2643.5	2656.1	2626.3	2623.2
30°	2613.1	2581.9	2594.5	2562.5	2557.3
32.5°	2543.0	2513.9	2524.4	2492.4	2489.3
35°	2435.1	2406.6	2413.9	2382.0	2379.4
37.5°	2312.5	2286.5	2290.7	2255.6	2253.0
40°	2225.4	2199.4	2201.5	2164.2	2161.6
42.5°	2129.8	2103.8	2101.6	2064.4	2061.8
45°	1970.4	1944.5	1935.9	1901.3	1896.1
47.5°	1788.8	1762.8	1746.8	1718.6	1715.0
50°	1657.1	1631.1	1617.2	1593.2	1585.4
52.5°	1514.7	1488.8	1477.0	1455.1	1447.3
55°	1290.6	1269.8	1261.4	1240.0	1234.8
57.5°	1077.6	1063.6	1061.2	1040.4	1038.3
60°	948.0	940.2	940.1	921.5	921.5
62.5°	837.6	831.8	836.0	823.7	821.6
65°	693.1	687.9	695.8	690.4	690.4
67.5°	578.9	578.9	583.7	581.6	581.6
70°	515.2	515.2	517.8	517.8	517.8
72.5°	457.8	455.7	462.6	462.6	460.5
75°	374.4	374.4	374.4	377.1	377.1
77.5°	291.6	292.1	294.2	293.7	291.6
80°	236.3	238.9	239.0	236.3	236.3
82.5°	181.1	183.7	183.8	183.2	181.1
85°	95.6	100.8	106.2	106.2	106.2
87.5°	28.2	37.2	45.0	45.3	43.5
90°	3.1	6.2	12.6	14.2	15.7
92.5°	28.3	117.6	210.3	76.7	59.8
95°	67.7	249.3	835.8	343.6	223.5
97.5°	112.1	279.2	1238.1	953.2	690.4
100°	144.8	297.2	1386.7	1396.5	1134.9
102.5°	176.3	317.6	1415.7	1725.5	1477.4
105°	226.7	349.8	1399.3	2136.3	2011.6
107.5°	280.2	389.8	1321.2	2334.4	2379.9
110°	318.0	416.5	1260.8	2377.0	2524.7



TEST NUMBER: P564320

CATALOG NUMBER: SQ4-PR1-100U-125D-930-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	352.0	446.8	1204.1	2343.3	2561.3
115°	406.1	490.7	1127.0	2231.1	2537.3
117.5°	453.3	537.7	1076.3	2073.0	2421.5
120°	484.8	567.9	1056.2	1966.1	2317.0
122.5°	515.0	594.4	1039.8	1866.2	2198.6
125°	557.2	634.2	1021.5	1728.8	2028.9
127.5°	593.1	670.0	1010.8	1612.7	1871.5
130°	617.0	694.0	1005.8	1541.6	1777.1
132.5°	639.7	712.9	1000.8	1481.9	1695.2
135°	670.5	742.9	993.2	1400.2	1578.8
137.5°	705.2	771.0	989.4	1331.6	1484.0
140°	724.1	788.7	986.9	1285.9	1419.8
142.5°	745.5	805.2	984.4	1245.2	1363.1
145°	777.6	831.4	980.6	1192.0	1282.8
147.5°	808.4	855.5	977.2	1147.2	1217.7
150°	831.1	869.6	975.9	1120.4	1177.4
152.5°	848.7	884.7	974.6	1097.5	1144.6
155°	876.7	906.0	972.7	1069.5	1103.4
157.5°	902.5	925.0	973.1	1049.1	1072.2
160°	917.7	937.7	974.3	1037.7	1054.6
162.5°	930.3	947.8	975.6	1027.5	1040.7
165°	949.1	961.5	977.5	1015.4	1023.1
167.5°	963.6	971.0	979.0	1008.1	1010.5
170°	971.2	977.3	979.0	1004.2	1004.2
172.5°	977.5	981.2	979.0	999.2	997.9
175°	983.8	985.3	979.0	993.1	990.1
177.5°	986.3	985.1	978.7	987.5	985.0
180°	983.8	983.8	983.8	983.8	983.8

(END OF REPORT)