

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519720

Luminaire Tested: **SQ4-100U-0D-835-1D-UNV-STD-W-4**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519720
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-100U-0D-835-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4016.3 lumens
Efficiency: N/A
Efficacy: 160.0 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 25.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519720
CATALOG NUMBER: SQ4-100U-0D-835-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P519720

CATALOG NUMBER: SQ4-100U-0D-835-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20	
RC	80								50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	4499	55597	14863
100°	4835	46294	37888
105°	5076	31341	45058
110°	5390	21370	42794
115°	5571	15459	34805
120°	5621	12245	26863
125°	5631	10325	20506
130°	5565	9071	16027
135°	5497	8143	12943
140°	5479	7468	10744
145°	5503	6940	9078
150°	5563	6533	7881
155°	5608	6222	7058
160°	5661	6011	6506
165°	5697	5867	6141
170°	5717	5764	5912
175°	5724	5698	5762



TEST NUMBER: P519720

CATALOG NUMBER: SQ4-100U-0D-835-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	289.5	7.2
100°-110°	799.1	19.9
110°-120°	824.2	20.5
120°-130°	662.3	16.5
130°-140°	520.5	13.0
140°-150°	399.2	9.9
150°-160°	286.9	7.1
160°-170°	175.5	4.4
170°-180°	59.2	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	1912.8	47.6
90°-150°	3494.8	87.0
90°-180°	4016.0	100.0
0°-180°	4016.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	2	4	8	9	10	
95°	42	157	525	216	140	48
105°	142	220	879	1342	1264	152
115°	255	308	708	1402	1594	251
125°	350	398	642	1086	1275	312
135°	421	467	624	880	992	326
145°	489	522	616	749	806	306
155°	551	569	611	672	693	254
165°	596	604	614	638	643	168
175°	618	619	615	624	622	59
180°	618	618	618	618	618	



TEST NUMBER: P519720

CATALOG NUMBER: SQ4-100U-OD-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	2.0	3.9	7.9	8.9	9.9
92.5°	17.8	73.9	132.1	48.2	37.6
95°	42.5	156.6	525.2	215.9	140.4
97.5°	70.4	175.4	778.0	599.0	433.8
100°	91.0	186.7	871.3	877.5	713.1
102.5°	110.8	199.5	889.5	1084.2	928.3
105°	142.4	219.8	879.2	1342.3	1264.0
107.5°	176.0	244.9	830.2	1466.8	1495.4
110°	199.8	261.7	792.2	1493.5	1586.4
112.5°	221.1	280.7	756.6	1472.4	1609.3
115°	255.2	308.4	708.1	1401.9	1594.3
117.5°	284.8	337.8	676.3	1302.6	1521.5
120°	304.6	356.8	663.6	1235.3	1455.8
122.5°	323.6	373.5	653.3	1172.6	1381.5
125°	350.1	398.5	641.9	1086.3	1274.8
127.5°	372.7	421.0	635.1	1013.3	1175.9
130°	387.7	436.0	632.0	968.6	1116.6
132.5°	401.9	448.0	628.8	931.1	1065.2
135°	421.3	466.8	624.1	879.8	992.0
137.5°	443.1	484.5	621.7	836.7	932.4
140°	454.9	495.6	620.1	808.0	892.1
142.5°	468.4	505.9	618.5	782.4	856.5
145°	488.6	522.4	616.2	749.0	806.0
147.5°	508.0	537.5	614.0	720.8	765.1
150°	522.2	546.4	613.2	704.0	739.8
152.5°	533.3	555.9	612.4	689.6	719.2
155°	550.9	569.3	611.2	672.0	693.3
157.5°	567.1	581.2	611.4	659.2	673.7
160°	576.6	589.2	612.2	652.0	662.6
162.5°	584.5	595.5	613.0	645.6	653.9
165°	596.4	604.1	614.2	638.0	642.9
167.5°	605.5	610.1	615.2	633.4	634.9
170°	610.2	614.1	615.2	631.0	631.0
172.5°	614.2	616.5	615.2	627.8	627.0
175°	618.1	619.1	615.2	624.0	622.1
177.5°	619.7	618.9	615.0	620.5	618.9
180°	618.1	618.1	618.1	618.1	618.1

(END OF REPORT)