

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519655

Luminaire Tested: **SQ4-025U-0D-930-1D-UNV-STD-W-12**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519655
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-025U-0D-930-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2305.9 lumens
Efficiency: N/A
Efficacy: 149.7 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Indirect

Input Watts (W): 15.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519655
CATALOG NUMBER: SQ4-025U-0D-930-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P519655

CATALOG NUMBER: SQ4-025U-0D-930-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20	
RC	80								50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	805	10540	3702
100°	930	8724	6866
105°	976	5989	8482
110°	1025	4060	8202
115°	1062	2938	6688
120°	1080	2329	5120
125°	1088	1969	3925
130°	1069	1724	3066
135°	1051	1547	2470
140°	1053	1419	2051
145°	1053	1319	1730
150°	1061	1247	1506
155°	1076	1192	1346
160°	1082	1149	1239
165°	1089	1118	1176
170°	1097	1104	1132
175°	1098	1091	1105



TEST NUMBER: P519655

CATALOG NUMBER: SQ4-025U-0D-930-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	173.4	7.5
100°-110°	455.8	19.8
110°-120°	472.7	20.5
120°-130°	379.1	16.4
130°-140°	297.5	12.9
140°-150°	228.3	9.9
150°-160°	164.5	7.1
160°-170°	100.6	4.4
170°-180°	34.0	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	1101.9	47.8
90°-150°	2006.9	87.0
90°-180°	2306.0	100.0
0°-180°	2305.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	2	7	18	9	9	
95°	23	90	299	154	105	27
105°	82	124	504	765	714	87
115°	146	177	404	805	919	144
125°	203	228	367	621	732	180
135°	242	266	356	501	568	187
145°	280	298	351	427	461	176
155°	317	326	351	386	397	146
165°	342	346	351	365	369	97
175°	356	356	354	358	358	34
180°	356	356	356	356	356	



TEST NUMBER: P519655

CATALOG NUMBER: SQ4-025U-0D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	2.3	6.7	18.2	9.1	9.1
92.5°	9.6	46.1	102.2	45.2	29.2
95°	22.8	89.7	298.7	154.0	104.9
97.5°	39.7	98.5	447.0	355.5	261.8
100°	52.5	106.0	492.6	499.2	387.7
102.5°	63.4	113.3	505.4	621.8	526.3
105°	82.1	124.5	504.0	765.1	713.8
107.5°	101.3	140.5	475.3	839.5	852.0
110°	114.0	149.7	451.5	858.7	912.2
112.5°	126.8	160.7	429.7	846.6	928.6
115°	146.0	177.2	403.7	805.3	919.1
117.5°	164.7	193.2	385.9	748.1	874.4
120°	175.6	202.4	378.6	709.7	832.4
122.5°	186.5	213.3	373.1	671.4	792.3
125°	203.0	227.5	367.2	620.6	732.0
127.5°	216.2	241.2	362.1	579.6	673.7
130°	223.5	250.2	360.3	553.9	640.8
132.5°	230.8	257.5	358.5	531.8	609.8
135°	241.7	266.3	355.8	501.0	567.9
137.5°	253.1	277.2	355.3	477.9	532.7
140°	262.3	284.6	353.5	459.6	510.8
142.5°	269.6	290.1	353.5	446.6	490.8
145°	280.5	298.3	351.2	427.2	460.7
147.5°	291.5	308.8	351.2	411.1	438.8
150°	298.7	314.4	351.2	401.9	424.2
152.5°	306.0	318.1	351.2	394.5	411.4
155°	317.0	325.9	351.2	385.7	396.8
157.5°	325.2	333.7	351.2	377.8	385.9
160°	330.7	337.4	351.2	374.1	378.6
162.5°	336.1	341.1	351.2	370.5	374.9
165°	342.1	346.5	351.2	365.0	369.4
167.5°	347.6	349.8	353.5	362.6	364.4
170°	351.2	353.4	353.5	362.6	362.6
172.5°	353.0	353.5	353.5	360.7	359.0
175°	355.8	355.8	353.5	358.0	358.0
177.5°	355.8	355.8	353.9	357.5	355.8
180°	355.8	355.8	355.8	355.8	355.8

(END OF REPORT)