

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519775

Luminaire Tested: **SQ4-150U-0D-930-1D-UNV-STD-W-12**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519775
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-150U-0D-930-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14380.8 lumens
Efficiency: N/A
Efficacy: 124.5 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Indirect

Input Watts (W): 115.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519775
CATALOG NUMBER: SQ4-150U-0D-930-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P519775

CATALOG NUMBER: SQ4-150U-0D-930-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	5678	60830	18723
100°	5867	52898	44606
105°	6191	36945	52265
110°	6498	25648	49288
115°	6674	18765	41006
120°	6763	14812	32091
125°	6733	12461	24704
130°	6628	10936	19356
135°	6547	9837	15590
140°	6535	9022	12916
145°	6571	8374	10952
150°	6633	7870	9507
155°	6705	7504	8522
160°	6797	7245	7834
165°	6850	7071	7384
170°	6876	6943	7108
175°	6893	6864	6938



TEST NUMBER: P519775

CATALOG NUMBER: SQ4-150U-0D-930-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	1036.6	7.2
100°-110°	2802.7	19.5
110°-120°	2946.7	20.5
120°-130°	2393.5	16.6
130°-140°	1877.5	13.1
140°-150°	1441.0	10.0
150°-160°	1036.3	7.2
160°-170°	633.1	4.4
170°-180°	213.4	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	6786.0	47.2
90°-150°	12497.9	86.9
90°-180°	14381.0	100.0
0°-180°	14380.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	5	14	31	34	31	
95°	161	565	1724	892	531	178
105°	521	805	3109	4586	4398	549
115°	917	1121	2579	4992	5635	906
125°	1256	1439	2324	3922	4607	1119
135°	1505	1684	2262	3167	3585	1163
145°	1750	1882	2230	2711	2917	1095
155°	1976	2054	2211	2432	2511	911
165°	2151	2172	2221	2308	2319	606
175°	2233	2230	2223	2252	2247	212
180°	2230	2230	2230	2230	2230	



TEST NUMBER: P519775

CATALOG NUMBER: SQ4-150U-0D-930-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	4.8	14.2	31.2	33.6	31.2
92.5°	68.2	248.5	490.3	212.8	154.1
95°	160.9	564.7	1723.9	892.1	530.6
97.5°	258.3	647.6	2687.1	2223.8	1633.1
100°	331.3	681.1	2986.8	3114.9	2518.6
102.5°	398.6	727.7	3092.4	3790.6	3344.5
105°	521.0	805.1	3109.2	4586.4	4398.5
107.5°	634.3	893.5	2973.3	5082.8	5145.2
110°	722.7	957.4	2852.3	5216.1	5481.4
112.5°	801.4	1021.2	2740.9	5189.5	5635.0
115°	917.2	1121.4	2578.6	4991.8	5635.0
117.5°	1030.5	1222.1	2471.5	4689.8	5419.0
120°	1099.6	1287.4	2408.2	4473.1	5217.3
122.5°	1164.9	1349.0	2369.7	4240.8	4990.6
125°	1255.7	1438.8	2324.1	3921.9	4607.4
127.5°	1339.3	1519.1	2297.2	3661.7	4264.6
130°	1385.4	1570.8	2285.7	3501.0	4045.6
132.5°	1433.4	1617.0	2274.2	3355.9	3857.4
135°	1505.4	1683.8	2261.7	3166.8	3584.6
137.5°	1577.9	1746.5	2251.1	3013.2	3353.7
140°	1627.8	1785.1	2247.3	2914.4	3217.3
142.5°	1675.9	1823.8	2239.6	2825.2	3090.5
145°	1750.3	1881.8	2230.5	2710.6	2917.2
147.5°	1818.0	1934.4	2219.9	2606.7	2765.4
150°	1867.9	1971.2	2216.1	2550.3	2677.1
152.5°	1914.0	2004.2	2214.2	2497.9	2602.2
155°	1976.0	2053.5	2211.3	2431.6	2511.4
157.5°	2040.3	2094.3	2211.8	2385.3	2437.9
160°	2076.8	2121.4	2213.7	2356.2	2393.8
162.5°	2105.6	2142.7	2215.6	2332.9	2361.1
165°	2151.3	2172.4	2220.9	2307.6	2319.3
167.5°	2182.5	2197.0	2221.4	2285.8	2291.5
170°	2201.7	2208.7	2223.3	2276.1	2276.1
172.5°	2217.0	2218.4	2223.3	2264.5	2262.7
175°	2232.9	2230.5	2223.3	2252.0	2247.3
177.5°	2238.2	2232.5	2222.8	2241.9	2236.2
180°	2230.5	2230.5	2230.5	2230.5	2230.5

(END OF REPORT)