

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562606

Luminaire Tested: **SQ4-PC3-050U-050D-835-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562606
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-050U-050D-835-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3961.0 lumens
Efficiency: N/A
Efficacy: 139.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 28.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562606
CATALOG NUMBER: SQ4-PC3-050U-050D-835-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P562606

CATALOG NUMBER: SQ4-PC3-050U-050D-835-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50		
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	49	48	47	42		
2	89	82	76	70	82	75	70	66	64	60	57	53	51	48	44	42	40	35		
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34	30		
4	74	63	56	49	68	59	52	46	50	45	41	42	38	35	34	32	29	25		
5	68	56	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25	22		
6	63	51	42	37	58	47	40	35	40	35	30	34	30	26	28	25	22	19		
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	26	22	20	17		
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18	15		
9	50	38	30	25	46	35	28	24	30	25	21	26	22	19	22	18	16	14		
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6653	6653	6653
5°	6703	6660	6635
10°	6686	6655	6637
15°	6652	6652	6645
20°	6608	6627	6627
25°	6546	6593	6572
30°	6466	6544	6516
35°	6369	6467	6422
40°	6264	6353	6288
45°	6151	6194	6099
50°	5990	5990	5894
55°	5799	5725	5638
60°	5519	5408	5322
65°	5102	4999	4956
70°	4467	4502	4483
75°	3593	3975	4000
80°	2556	3369	3406
85°	1556	2826	2826



TEST NUMBER: P562606

CATALOG NUMBER: SQ4-PC3-050U-050D-835-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.2	1.7
10°-20°	195.8	4.9
20°-30°	296.6	7.5
30°-40°	355.6	9.0
40°-50°	362.5	9.2
50°-60°	316.5	8.0
60°-70°	226.6	5.7
70°-80°	116.7	2.9
80°-90°	30.7	0.8
90°-100°	146.4	3.7
100°-110°	397.8	10.0
110°-120°	409.0	10.3
120°-130°	327.0	8.3
130°-140°	257.0	6.5
140°-150°	197.0	5.0
150°-160°	141.7	3.6
160°-170°	86.7	2.2
170°-180°	29.2	0.7
0°-30°	560.6	14.2
0°-40°	916.2	23.1
0°-60°	1595.2	40.3
0°-90°	1969.1	49.7
90°-120°	953.3	24.1
90°-150°	1734.4	43.8
90°-180°	1992.0	50.3
0°-180°	3961.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	721	721	721	721	721	
5°	724	717	719	717	716	69
15°	696	690	696	696	696	196
25°	643	638	648	646	646	296
35°	566	564	574	570	570	354
45°	471	470	475	469	467	363
55°	360	356	356	350	350	321
65°	234	228	229	227	227	231
75°	101	105	112	112	112	109
85°	15	22	27	27	27	20
90°	1	4	7	9	9	2
95°	22	80	255	111	75	23
105°	71	110	438	666	627	75
115°	126	152	350	697	794	124
125°	173	197	317	534	630	154
135°	208	231	308	435	490	161
145°	240	258	304	370	397	151
155°	272	281	302	332	341	125
165°	294	298	303	316	317	83
175°	305	306	304	308	307	29
180°	305	305	305	305	305	

TEST NUMBER: P562606

CATALOG NUMBER: SQ4-PC3-050U-050D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	721.1	721.1	721.1	721.1	721.1
2.5°	725.4	719.1	721.1	719.4	716.8
5°	723.7	716.6	719.1	717.1	716.4
7.5°	718.5	711.4	714.7	713.3	712.7
10°	713.7	706.6	710.4	709.0	708.4
12.5°	707.3	700.7	705.1	703.7	703.6
15°	696.4	690.5	696.4	696.4	695.7
17.5°	682.6	677.3	683.6	683.9	683.6
20°	673.0	667.1	675.0	674.4	675.0
22.5°	661.3	656.4	664.9	663.1	663.8
25°	643.0	638.4	647.6	645.6	645.6
27.5°	621.3	618.1	628.1	626.0	626.0
30°	606.9	603.6	614.3	611.6	611.6
32.5°	590.9	588.7	598.8	595.6	595.6
35°	565.5	564.2	574.2	570.2	570.2
37.5°	539.3	538.2	547.2	542.4	540.8
40°	520.1	519.5	527.5	522.1	522.1
42.5°	500.9	500.2	507.2	500.7	500.7
45°	471.4	470.1	474.7	468.7	467.4
47.5°	439.2	437.9	440.8	434.2	433.6
50°	417.3	416.0	417.3	411.3	410.6
52.5°	394.9	392.5	392.7	386.7	386.6
55°	360.5	356.0	355.9	350.5	350.5
57.5°	324.2	318.2	318.7	314.2	313.5
60°	299.1	292.6	293.1	289.1	288.4
62.5°	274.5	267.0	268.5	264.0	263.9
65°	233.7	228.5	229.0	227.0	227.0
67.5°	194.4	189.6	193.1	191.5	191.4
70°	165.6	162.3	166.9	166.9	166.2
72.5°	138.9	138.7	144.5	144.5	144.9
75°	100.8	105.4	111.5	112.2	112.2
77.5°	67.3	75.4	82.1	82.4	82.3
80°	48.1	57.2	63.4	64.7	64.1
82.5°	32.6	42.2	47.4	48.7	48.1
85°	14.7	22.5	26.7	27.4	26.7
87.5°	4.5	9.7	12.1	12.4	11.4
90°	1.0	3.9	6.9	8.8	8.8
92.5°	8.8	40.1	69.6	29.9	25.3
95°	21.6	80.1	255.0	111.0	74.6
97.5°	35.7	88.5	391.0	304.2	213.7
100°	45.1	94.0	432.6	438.5	354.1
102.5°	54.5	99.6	443.6	542.3	467.9
105°	70.6	110.0	437.5	666.1	626.8
107.5°	87.3	122.0	412.2	730.1	741.0
110°	99.1	130.7	393.4	742.7	789.7



TEST NUMBER: P562606

CATALOG NUMBER: SQ4-PC3-050U-050D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	109.3	139.4	374.5	732.2	803.0
115°	125.6	152.4	350.2	696.7	793.6
117.5°	140.9	166.6	334.7	646.4	755.5
120°	151.1	176.0	327.6	612.6	721.0
122.5°	159.7	184.6	322.9	578.8	683.3
125°	172.6	196.6	316.8	533.9	629.8
127.5°	184.2	208.0	313.5	499.8	582.1
130°	191.3	214.3	311.9	478.4	552.3
132.5°	198.3	221.4	310.4	460.2	525.6
135°	208.0	231.0	308.0	434.8	490.5
137.5°	218.4	239.3	306.8	412.5	459.3
140°	224.6	244.8	306.1	398.2	440.4
142.5°	230.9	249.5	305.3	387.1	422.4
145°	240.3	257.6	304.1	369.5	397.3
147.5°	250.9	265.7	303.1	355.6	377.5
150°	258.0	270.5	303.1	347.6	364.9
152.5°	263.5	274.4	302.3	340.5	354.7
155°	271.7	281.3	302.1	331.8	341.4
157.5°	279.8	287.2	302.1	325.8	333.1
160°	284.5	291.2	302.1	321.9	327.6
162.5°	289.2	294.4	302.9	318.7	322.9
165°	294.3	298.1	303.1	315.9	316.8
167.5°	299.6	301.5	304.1	312.5	313.3
170°	301.2	303.1	304.1	311.0	311.0
172.5°	302.7	303.9	304.1	309.4	309.4
175°	305.1	306.0	304.1	308.0	307.0
177.5°	305.9	305.9	303.5	306.6	305.1
180°	305.1	305.1	305.1	305.1	305.1

(END OF REPORT)