

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562798

Luminaire Tested: **SQ4-PC3-0U-050D-835-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562798  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-0U-050D-835-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 3500K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1968.0 lumens  
Efficiency: N/A  
Efficacy: 121.5 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 16.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562798  
CATALOG NUMBER: SQ4-PC3-0U-050D-835-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P562798

CATALOG NUMBER: SQ4-PC3-0U-050D-835-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6653	6653	6653
5°	6703	6660	6635
10°	6686	6655	6637
15°	6652	6652	6645
20°	6608	6627	6627
25°	6546	6593	6572
30°	6466	6544	6516
35°	6369	6467	6422
40°	6264	6353	6288
45°	6151	6194	6099
50°	5990	5990	5894
55°	5799	5725	5638
60°	5519	5408	5322
65°	5102	4999	4956
70°	4467	4502	4483
75°	3593	3975	4000
80°	2556	3369	3406
85°	1556	2826	2826



TEST NUMBER: P562798

CATALOG NUMBER: SQ4-PC3-OU-050D-835-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	68.2	3.5
10°-20°	195.8	10.0
20°-30°	296.6	15.1
30°-40°	355.6	18.1
40°-50°	362.5	18.4
50°-60°	316.5	16.1
60°-70°	226.6	11.5
70°-80°	116.7	5.9
80°-90°	29.5	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	560.6	28.5
0°-40°	916.2	46.6
0°-60°	1595.2	81.1
0°-90°	1968.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1968.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	721	721	721	721	721	
5°	724	717	719	717	716	69
15°	696	690	696	696	696	196
25°	643	638	648	646	646	296
35°	566	564	574	570	570	354
45°	471	470	475	469	467	363
55°	360	356	356	350	350	321
65°	234	228	229	227	227	231
75°	101	105	112	112	112	109
85°	15	22	27	27	27	21
90°	0	0	0	0	0	



TEST NUMBER: P562798

CATALOG NUMBER: SQ4-PC3-0U-050D-835-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	721.1	721.1	721.1	721.1	721.1
2.5°	725.4	719.1	721.1	719.4	716.8
5°	723.7	716.6	719.1	717.1	716.4
7.5°	718.5	711.4	714.7	713.3	712.7
10°	713.7	706.6	710.4	709.0	708.4
12.5°	707.3	700.7	705.1	703.7	703.6
15°	696.4	690.5	696.4	696.4	695.7
17.5°	682.6	677.3	683.6	683.9	683.6
20°	673.0	667.1	675.0	674.4	675.0
22.5°	661.3	656.4	664.9	663.1	663.8
25°	643.0	638.4	647.6	645.6	645.6
27.5°	621.3	618.1	628.1	626.0	626.0
30°	606.9	603.6	614.3	611.6	611.6
32.5°	590.9	588.7	598.8	595.6	595.6
35°	565.5	564.2	574.2	570.2	570.2
37.5°	539.3	538.2	547.2	542.4	540.8
40°	520.1	519.5	527.5	522.1	522.1
42.5°	500.9	500.2	507.2	500.7	500.7
45°	471.4	470.1	474.7	468.7	467.4
47.5°	439.2	437.9	440.8	434.2	433.6
50°	417.3	416.0	417.3	411.3	410.6
52.5°	394.9	392.5	392.7	386.7	386.6
55°	360.5	356.0	355.9	350.5	350.5
57.5°	324.2	318.2	318.7	314.2	313.5
60°	299.1	292.6	293.1	289.1	288.4
62.5°	274.5	267.0	268.5	264.0	263.9
65°	233.7	228.5	229.0	227.0	227.0
67.5°	194.4	189.6	193.1	191.5	191.4
70°	165.6	162.3	166.9	166.9	166.2
72.5°	138.9	138.7	144.5	144.5	144.9
75°	100.8	105.4	111.5	112.2	112.2
77.5°	67.3	75.4	82.1	82.4	82.3
80°	48.1	57.2	63.4	64.7	64.1
82.5°	32.6	42.2	47.4	48.7	48.1
85°	14.7	22.5	26.7	27.4	26.7
87.5°	4.3	9.0	10.7	10.7	9.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)