

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562822

Luminaire Tested: **SQ4-PC3-0U-075D-835-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562822  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-0U-075D-835-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 750 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 3500K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2900.5 lumens  
Efficiency: N/A  
Efficacy: 120.9 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 24  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562822  
CATALOG NUMBER: SQ4-PC3-0U-075D-835-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P562822

CATALOG NUMBER: SQ4-PC3-0U-075D-835-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9806	9806	9806
5°	9879	9815	9779
10°	9856	9809	9782
15°	9804	9804	9794
20°	9739	9768	9768
25°	9648	9717	9687
30°	9530	9645	9603
35°	9388	9532	9466
40°	9233	9363	9268
45°	9064	9130	8987
50°	8827	8827	8687
55°	8548	8437	8310
60°	8136	7971	7844
65°	7519	7368	7305
70°	6582	6636	6609
75°	5297	5857	5893
80°	3767	4968	5021
85°	2287	4171	4171



TEST NUMBER: P562822

CATALOG NUMBER: SQ4-PC3-0U-075D-835-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	100.6	3.5
10°-20°	288.6	10.0
20°-30°	437.1	15.1
30°-40°	524.0	18.1
40°-50°	534.3	18.4
50°-60°	466.4	16.1
60°-70°	333.9	11.5
70°-80°	172.0	5.9
80°-90°	43.5	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	826.3	28.5
0°-40°	1350.4	46.6
0°-60°	2351.1	81.1
0°-90°	2900.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2900.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1063	1063	1063	1063	1063	
5°	1067	1056	1060	1057	1056	101
15°	1026	1018	1026	1026	1025	289
25°	948	941	954	952	952	436
35°	834	832	846	840	840	521
45°	695	693	700	691	689	535
55°	531	525	524	517	517	474
65°	344	337	338	335	335	341
75°	149	155	164	165	165	161
85°	22	33	39	40	39	30
90°	0	0	0	0	0	



TEST NUMBER: P562822

CATALOG NUMBER: SQ4-PC3-OU-075D-835-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1062.8	1062.8	1062.8	1062.8	1062.8
2.5°	1069.1	1059.8	1062.8	1060.3	1056.5
5°	1066.7	1056.1	1059.8	1056.9	1055.9
7.5°	1059.0	1048.5	1053.3	1051.4	1050.4
10°	1052.0	1041.4	1047.0	1045.1	1044.1
12.5°	1042.5	1032.7	1039.2	1037.2	1037.0
15°	1026.4	1017.7	1026.4	1026.4	1025.4
17.5°	1006.1	998.2	1007.5	1008.1	1007.5
20°	991.9	983.3	994.9	993.9	994.9
22.5°	974.6	967.5	979.9	977.4	978.4
25°	947.7	940.9	954.5	951.6	951.6
27.5°	915.8	911.0	925.8	922.7	922.7
30°	894.5	889.7	905.3	901.4	901.4
32.5°	870.9	867.6	882.5	877.8	877.8
35°	833.5	831.6	846.3	840.4	840.4
37.5°	794.9	793.2	806.5	799.4	797.1
40°	766.6	765.6	777.4	769.5	769.5
42.5°	738.2	737.3	747.5	738.0	738.0
45°	694.7	692.8	699.7	690.8	688.8
47.5°	647.3	645.4	649.7	640.0	639.0
50°	615.0	613.1	615.0	606.2	605.2
52.5°	582.0	578.5	578.8	570.0	569.8
55°	531.4	524.7	524.5	516.6	516.6
57.5°	477.9	469.0	469.8	463.1	462.1
60°	440.9	431.2	432.0	426.1	425.1
62.5°	404.6	393.5	395.8	389.1	388.9
65°	344.4	336.7	337.5	334.6	334.6
67.5°	286.6	279.4	284.6	282.2	282.0
70°	244.0	239.2	246.0	246.0	245.0
72.5°	204.7	204.5	213.0	213.0	213.5
75°	148.6	155.3	164.3	165.3	165.3
77.5°	99.2	111.1	121.0	121.4	121.2
80°	70.9	84.3	93.5	95.4	94.5
82.5°	48.0	62.3	69.9	71.8	70.9
85°	21.6	33.2	39.4	40.3	39.4
87.5°	6.3	13.2	15.7	15.7	14.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)