

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562846

Luminaire Tested: **SQ4-PC3-0U-100D-835-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562846
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-0U-100D-835-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3854.0 lumens
Efficiency: N/A
Efficacy: 117.5 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562846
CATALOG NUMBER: SQ4-PC3-0U-100D-835-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P562846

CATALOG NUMBER: SQ4-PC3-0U-100D-835-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13028	13028	13028
5°	13127	13042	12994
10°	13094	13034	12997
15°	13026	13026	13013
20°	12941	12979	12979
25°	12818	12911	12872
30°	12662	12815	12760
35°	12474	12665	12576
40°	12268	12440	12315
45°	12044	12131	11943
50°	11730	11730	11542
55°	11358	11210	11043
60°	10809	10592	10424
65°	9990	9791	9706
70°	8748	8818	8783
75°	7037	7785	7832
80°	5000	6599	6668
85°	3049	5536	5536



TEST NUMBER: P562846

CATALOG NUMBER: SQ4-PC3-0U-100D-835-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.6	3.5
10°-20°	383.5	10.0
20°-30°	580.8	15.1
30°-40°	696.3	18.1
40°-50°	710.0	18.4
50°-60°	619.8	16.1
60°-70°	443.7	11.5
70°-80°	228.5	5.9
80°-90°	57.8	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1097.9	28.5
0°-40°	1794.2	46.6
0°-60°	3123.9	81.1
0°-90°	3854.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3854.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1412	1412	1412	1412	1412	
5°	1417	1403	1408	1404	1403	135
15°	1364	1352	1364	1364	1362	385
25°	1259	1250	1268	1264	1264	579
35°	1108	1105	1124	1117	1117	693
45°	923	921	930	918	915	711
55°	706	697	697	686	686	629
65°	458	447	448	445	445	453
75°	197	206	218	220	220	213
85°	29	44	52	54	52	40
90°	0	0	0	0	0	



TEST NUMBER: P562846

CATALOG NUMBER: SQ4-PC3-0U-100D-835-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1412.1	1412.1	1412.1	1412.1	1412.1
2.5°	1420.5	1408.2	1412.1	1408.9	1403.8
5°	1417.4	1403.3	1408.2	1404.3	1403.0
7.5°	1407.2	1393.1	1399.6	1396.9	1395.7
10°	1397.7	1383.7	1391.2	1388.6	1387.3
12.5°	1385.2	1372.2	1380.7	1378.1	1377.9
15°	1363.7	1352.2	1363.7	1363.7	1362.4
17.5°	1336.8	1326.3	1338.6	1339.4	1338.6
20°	1318.0	1306.5	1321.9	1320.6	1321.9
22.5°	1295.0	1285.5	1302.0	1298.7	1299.9
25°	1259.1	1250.2	1268.3	1264.4	1264.4
27.5°	1216.8	1210.4	1230.1	1225.9	1225.9
30°	1188.5	1182.1	1202.9	1197.7	1197.7
32.5°	1157.2	1152.8	1172.6	1166.3	1166.3
35°	1107.5	1104.9	1124.5	1116.6	1116.6
37.5°	1056.2	1053.9	1071.6	1062.2	1059.1
40°	1018.6	1017.3	1032.9	1022.5	1022.5
42.5°	980.9	979.6	993.2	980.6	980.6
45°	923.1	920.6	929.7	917.8	915.3
47.5°	860.1	857.5	863.2	850.4	849.1
50°	817.2	814.6	817.2	805.4	804.1
52.5°	773.3	768.7	769.1	757.3	757.1
55°	706.1	697.1	696.9	686.5	686.5
57.5°	634.9	623.2	624.2	615.3	614.0
60°	585.8	573.0	574.0	566.1	564.9
62.5°	537.7	522.8	525.9	517.0	516.7
65°	457.6	447.4	448.5	444.6	444.6
67.5°	380.8	371.3	378.1	375.0	374.7
70°	324.3	317.9	326.9	326.9	325.6
72.5°	272.0	271.7	282.9	283.0	283.7
75°	197.4	206.4	218.4	219.7	219.7
77.5°	131.8	147.7	160.8	161.3	161.1
80°	94.1	112.0	124.2	126.8	125.5
82.5°	63.8	82.7	92.8	95.4	94.1
85°	28.8	44.1	52.3	53.6	52.3
87.5°	8.4	17.6	20.9	20.9	18.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)